

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563059

Luminaire Tested: **SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563059
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14044.1 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 117.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563059
CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563059

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	50	48	43	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15693	15693	15693
5°	15812	15709	15651
10°	15773	15699	15655
15°	15690	15690	15676
20°	15587	15633	15633
25°	15440	15552	15504
30°	15252	15436	15369
35°	15025	15256	15149
40°	14776	14985	14833
45°	14508	14611	14385
50°	14129	14129	13903
55°	13680	13503	13300
60°	13020	12758	12555
65°	12035	11793	11690
70°	10537	10621	10578
75°	8477	9375	9432
80°	6025	7948	8033
85°	3670	6669	6669



TEST NUMBER: P563059

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.5	1.7
10°-20°	692.9	4.9
20°-30°	1049.4	7.5
30°-40°	1258.0	9.0
40°-50°	1282.8	9.1
50°-60°	1119.8	8.0
60°-70°	801.7	5.7
70°-80°	412.9	2.9
80°-90°	107.0	0.8
90°-100°	512.9	3.7
100°-110°	1381.7	9.8
110°-120°	1450.0	10.3
120°-130°	1176.7	8.4
130°-140°	922.8	6.6
140°-150°	708.5	5.0
150°-160°	509.4	3.6
160°-170°	311.2	2.2
170°-180°	105.0	0.7
0°-30°	1983.8	14.1
0°-40°	3241.8	23.1
0°-60°	5644.4	40.2
0°-90°	6965.9	49.6
90°-120°	3344.6	23.8
90°-150°	6152.6	43.8
90°-180°	7078.0	50.4
0°-180°	14044.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2551	2551	2551	2551	2551	
5°	2561	2536	2544	2537	2535	243
15°	2464	2443	2464	2464	2462	695
25°	2275	2259	2292	2284	2284	1047
35°	2001	1996	2032	2018	2018	1251
45°	1668	1663	1680	1658	1654	1284
55°	1276	1260	1259	1240	1240	1137
65°	827	808	810	803	803	818
75°	357	373	394	397	397	385
85°	52	80	94	97	94	71
90°	3	8	17	18	18	8
95°	78	279	841	430	298	82
105°	256	398	1528	2286	2145	269
115°	451	552	1272	2459	2781	444
125°	616	708	1142	1931	2272	550
135°	742	828	1110	1558	1764	572
145°	858	924	1096	1332	1430	538
155°	974	1009	1087	1195	1233	448
165°	1056	1068	1091	1134	1140	298
175°	1098	1096	1092	1108	1105	104
180°	1096	1096	1096	1096	1096	



TEST NUMBER: P563059

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2551.4	2551.4	2551.4	2551.4	2551.4
2.5°	2566.6	2544.4	2551.4	2545.6	2536.3
5°	2560.9	2535.5	2544.3	2537.2	2534.9
7.5°	2542.5	2517.0	2528.8	2524.0	2521.7
10°	2525.4	2500.0	2513.6	2508.9	2506.5
12.5°	2502.8	2479.2	2494.7	2490.0	2489.5
15°	2464.0	2443.2	2464.0	2464.0	2461.7
17.5°	2415.4	2396.4	2418.7	2420.0	2418.7
20°	2381.3	2360.5	2388.4	2386.1	2388.4
22.5°	2339.8	2322.7	2352.5	2346.4	2348.7
25°	2275.0	2258.9	2291.6	2284.5	2284.5
27.5°	2198.5	2186.9	2222.6	2215.0	2215.0
30°	2147.5	2135.9	2173.4	2164.0	2164.0
32.5°	2090.8	2082.9	2118.6	2107.3	2107.3
35°	2001.0	1996.4	2031.7	2017.5	2017.5
37.5°	1908.4	1904.2	1936.3	1919.1	1913.6
40°	1840.3	1838.0	1866.3	1847.4	1847.4
42.5°	1772.3	1770.0	1794.5	1771.8	1771.8
45°	1667.9	1663.3	1679.7	1658.3	1653.7
47.5°	1554.0	1549.4	1559.7	1536.5	1534.2
50°	1476.5	1471.9	1476.5	1455.2	1452.9
52.5°	1397.1	1388.8	1389.6	1368.3	1367.9
55°	1275.7	1259.5	1259.2	1240.3	1240.3
57.5°	1147.2	1125.9	1127.8	1111.7	1109.4
60°	1058.4	1035.3	1037.1	1022.9	1020.6
62.5°	971.4	944.6	950.2	934.1	933.6
65°	826.9	808.4	810.3	803.2	803.2
67.5°	687.9	670.8	683.2	677.5	677.1
70°	585.9	574.3	590.6	590.6	588.2
72.5°	491.4	490.9	511.2	511.3	512.6
75°	356.7	372.9	394.5	396.9	396.9
77.5°	238.1	266.8	290.6	291.5	291.1
80°	170.1	202.4	224.4	229.1	226.8
82.5°	115.3	149.5	167.7	172.4	170.1
85°	52.0	79.7	94.5	96.8	94.5
87.5°	15.7	33.4	41.2	41.3	37.7
90°	2.8	8.3	16.8	18.2	18.2
92.5°	34.1	120.4	238.0	114.6	79.6
95°	78.2	279.0	840.8	430.0	297.5
97.5°	124.9	319.3	1318.8	1101.7	830.8
100°	160.6	335.4	1470.8	1538.8	1276.6
102.5°	195.3	358.1	1521.1	1866.2	1651.0
105°	255.6	397.6	1528.0	2286.1	2145.4
107.5°	312.6	439.3	1463.0	2501.9	2538.2
110°	350.6	470.8	1403.7	2568.8	2701.3

TEST NUMBER: P563059

CATALOG NUMBER: SQ4-PC3-125U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.8	502.3	1346.7	2554.0	2771.7
115°	451.2	552.2	1272.4	2458.6	2780.9
117.5°	506.2	601.0	1214.9	2306.4	2665.3
120°	541.9	633.4	1185.8	2197.1	2565.8
122.5°	573.2	663.6	1164.6	2085.3	2453.0
125°	616.0	707.5	1142.5	1931.1	2272.5
127.5°	657.0	747.2	1128.6	1795.1	2099.9
130°	681.6	771.8	1123.0	1717.1	1984.8
132.5°	706.2	795.2	1117.4	1648.4	1894.3
135°	741.7	827.7	1110.4	1557.9	1764.1
137.5°	775.5	858.0	1106.8	1481.1	1650.4
140°	798.9	878.2	1103.4	1433.8	1586.7
142.5°	823.5	897.3	1101.2	1389.6	1518.5
145°	857.6	924.5	1096.5	1331.9	1430.3
147.5°	894.5	952.7	1091.7	1283.4	1360.7
150°	919.1	969.6	1089.5	1252.9	1317.1
152.5°	941.4	985.4	1088.3	1228.1	1280.3
155°	973.5	1009.0	1086.7	1195.1	1233.3
157.5°	1001.8	1029.3	1087.0	1171.9	1197.6
160°	1019.6	1042.8	1088.1	1158.3	1177.5
162.5°	1035.3	1054.1	1089.2	1147.0	1160.7
165°	1055.9	1068.2	1090.9	1134.3	1139.8
167.5°	1072.7	1079.8	1092.3	1124.4	1126.6
170°	1083.9	1086.6	1092.3	1118.8	1118.8
172.5°	1090.6	1091.1	1093.4	1113.2	1113.2
175°	1097.8	1096.5	1092.3	1107.6	1104.8
177.5°	1100.9	1098.7	1093.1	1102.0	1099.8
180°	1096.5	1096.5	1096.5	1096.5	1096.5

(END OF REPORT)