

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519643

Luminaire Tested: **SQ4-025U-0D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519643
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2735.1 lumens
Efficiency: N/A
Efficacy: 177.6 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519643
CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519643

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20
RC	80								50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	956	12505	4390
100°	1102	10348	8145
105°	1157	7103	10061
110°	1217	4816	9729
115°	1260	3484	7933
120°	1281	2762	6073
125°	1291	2335	4656
130°	1268	2045	3637
135°	1247	1835	2930
140°	1249	1683	2432
145°	1249	1564	2051
150°	1259	1479	1787
155°	1276	1414	1597
160°	1284	1363	1469
165°	1292	1326	1395
170°	1301	1309	1343
175°	1303	1294	1311



TEST NUMBER: P519643

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	205.7	7.5
100°-110°	540.7	19.8
110°-120°	560.7	20.5
120°-130°	449.7	16.4
130°-140°	352.9	12.9
140°-150°	270.8	9.9
150°-160°	195.1	7.1
160°-170°	119.3	4.4
170°-180°	40.3	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1307.0	47.8
90°-150°	2380.4	87.0
90°-180°	2735.0	100.0
0°-180°	2735.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	8	22	11	11	
95°	27	106	354	183	124	32
105°	97	148	598	908	847	103
115°	173	210	479	955	1090	171
125°	241	270	436	736	868	214
135°	287	316	422	594	674	222
145°	333	354	417	507	546	208
155°	376	387	417	458	471	173
165°	406	411	417	433	438	115
175°	422	422	419	425	425	40
180°	422	422	422	422	422	



TEST NUMBER: P519643

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.7	8.0	21.6	10.8	10.8
92.5°	11.4	54.7	121.2	53.7	34.6
95°	27.1	106.4	354.4	182.6	124.4
97.5°	47.1	116.9	530.2	421.6	310.5
100°	62.2	125.7	584.3	592.1	459.9
102.5°	75.2	134.4	599.4	737.5	624.3
105°	97.4	147.6	597.8	907.5	846.7
107.5°	120.1	166.7	563.7	995.8	1010.6
110°	135.3	177.6	535.6	1018.5	1082.0
112.5°	150.4	190.6	509.6	1004.2	1101.5
115°	173.1	210.2	478.8	955.2	1090.1
117.5°	195.3	229.2	457.7	887.4	1037.1
120°	208.3	240.0	449.0	841.9	987.3
122.5°	221.3	253.0	442.5	796.4	939.7
125°	240.8	269.8	435.5	736.1	868.3
127.5°	256.4	286.1	429.6	687.5	799.1
130°	265.1	296.8	427.4	657.0	760.1
132.5°	273.8	305.5	425.2	630.8	723.3
135°	286.7	315.8	422.0	594.2	673.6
137.5°	300.3	328.8	421.4	566.8	631.9
140°	311.1	337.5	419.3	545.1	605.9
142.5°	319.7	344.1	419.3	529.8	582.1
145°	332.7	353.9	416.6	506.7	546.4
147.5°	345.7	366.3	416.6	487.7	520.5
150°	354.4	372.9	416.6	476.7	503.1
152.5°	363.0	377.3	416.6	467.9	488.0
155°	376.0	386.6	416.6	457.5	470.7
157.5°	385.7	395.8	416.6	448.2	457.7
160°	392.2	400.2	416.6	443.8	449.0
162.5°	398.7	404.5	416.6	439.4	444.7
165°	405.8	411.0	416.6	432.9	438.2
167.5°	412.3	414.9	419.3	430.2	432.3
170°	416.6	419.2	419.3	430.1	430.1
172.5°	418.7	419.3	419.3	427.9	425.8
175°	422.0	422.0	419.3	424.7	424.7
177.5°	422.0	422.0	419.8	424.1	422.0
180°	422.0	422.0	422.0	422.0	422.0

(END OF REPORT)