

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518491

Luminaire Tested: **SQ4-BB-075U-050D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P518491
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-12)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12030.0 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 107.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P518491
CATALOG NUMBER: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P518491

CATALOG NUMBER: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	30
1	94	90	87	84	84	81	79	76	64	63	61	49	48	47	35	34	33	27
2	87	80	75	70	78	72	68	64	58	55	52	44	42	41	32	31	30	24
3	80	71	65	60	72	65	59	55	52	48	45	40	38	36	29	28	27	22
4	73	64	57	52	66	58	52	47	47	43	39	36	34	32	27	25	24	20
5	68	57	50	45	61	52	46	41	42	38	35	33	30	28	25	23	22	18
6	63	52	45	39	56	47	41	36	39	34	31	30	27	25	23	21	20	16
7	58	47	40	35	52	43	37	32	35	31	27	28	25	23	21	19	18	15
8	54	43	36	31	49	39	33	29	32	28	25	26	23	21	20	18	16	14
9	51	39	33	28	46	36	30	26	30	25	22	24	21	19	18	16	15	13
10	47	36	30	25	43	33	27	24	28	23	20	22	19	17	17	15	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9150	9150	9150
5°	9003	8981	9048
10°	8424	8536	8775
15°	7658	7901	8341
20°	6798	7151	7778
25°	5920	6389	7146
30°	5071	5628	6548
35°	4205	4777	5826
40°	3231	3820	4964
45°	2335	2892	3994
50°	1591	2155	3168
55°	1034	1559	2462
60°	593	1098	1779
65°	157	670	901
70°	77	207	259
75°	34	17	0
80°	25	0	0
85°	0	0	0



TEST NUMBER: P518491

CATALOG NUMBER: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.5	2.3
10°-20°	694.4	5.8
20°-30°	869.3	7.2
30°-40°	803.0	6.7
40°-50°	539.5	4.5
50°-60°	278.7	2.3
60°-70°	87.3	0.7
70°-80°	5.5	0.0
80°-90°	3.4	0.0
90°-100°	613.7	5.1
100°-110°	1688.6	14.0
110°-120°	1742.9	14.5
120°-130°	1396.4	11.6
130°-140°	1096.8	9.1
140°-150°	840.5	7.0
150°-160°	604.3	5.0
160°-170°	369.5	3.1
170°-180°	124.6	1.0
0°-30°	1835.2	15.3
0°-40°	2638.2	21.9
0°-60°	3456.4	28.7
0°-90°	3552.6	29.5
90°-120°	4045.3	33.6
90°-150°	7379.0	61.3
90°-180°	8477.0	70.5
0°-180°	12030.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2975	2975	2975	2975	2975	
5°	2916	2887	2909	2920	2931	270
15°	2405	2397	2482	2565	2620	670
25°	1745	1759	1883	2012	2106	800
35°	1120	1148	1272	1422	1552	694
45°	537	569	665	794	918	422
55°	193	225	291	373	459	180
65°	22	41	92	111	124	36
75°	3	3	1	0	0	4
85°	0	0	0	0	0	0
90°	3	11	19	25	25	6
95°	91	335	1085	464	296	97
105°	302	464	1861	2834	2644	318
115°	534	651	1492	2972	3372	527
125°	736	839	1354	2290	2683	657
135°	889	986	1315	1852	2096	686
145°	1027	1098	1296	1578	1700	644
155°	1163	1201	1288	1418	1459	534
165°	1257	1273	1293	1346	1354	354
175°	1301	1304	1296	1312	1310	124
180°	1301	1301	1301	1301	1301	



TEST NUMBER: P518491

CATALOG NUMBER: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2975.3	2975.3	2975.3	2975.3	2975.3
2.5°	2982.3	2954.1	2961.5	2961.3	2953.5
5°	2916.3	2886.8	2909.1	2919.5	2930.7
7.5°	2793.1	2770.0	2813.0	2845.2	2868.5
10°	2697.5	2677.8	2733.5	2777.4	2809.8
12.5°	2587.0	2571.8	2639.1	2699.3	2740.7
15°	2405.3	2396.9	2481.6	2564.9	2619.8
17.5°	2210.7	2210.4	2307.2	2410.6	2476.7
20°	2077.1	2081.4	2185.1	2299.1	2376.5
22.5°	1943.5	1953.4	2064.2	2183.1	2271.7
25°	1744.6	1758.7	1882.8	2011.6	2105.9
27.5°	1553.5	1574.0	1704.6	1838.5	1953.3
30°	1427.9	1451.9	1584.8	1725.7	1843.9
32.5°	1304.7	1333.1	1462.8	1611.8	1732.2
35°	1119.9	1148.0	1272.5	1422.2	1551.7
37.5°	929.0	956.6	1078.1	1225.6	1365.5
40°	804.7	835.6	951.5	1094.3	1236.5
42.5°	691.8	722.8	831.7	972.1	1106.4
45°	536.9	569.3	665.0	794.5	918.4
47.5°	408.5	443.7	527.7	644.8	757.7
50°	332.5	367.7	450.5	553.8	662.1
52.5°	271.5	305.5	380.3	477.6	576.9
55°	192.9	225.3	290.8	373.3	459.2
57.5°	133.3	161.2	219.9	288.8	356.1
60°	96.4	123.2	178.5	234.4	289.3
62.5°	64.2	88.7	142.8	185.7	222.5
65°	21.6	41.3	92.1	111.1	123.8
67.5°	10.9	13.2	48.4	51.1	55.3
70°	8.6	8.6	23.0	24.6	28.8
72.5°	6.3	6.3	9.2	11.8	12.7
75°	2.9	2.9	1.4	0.0	0.0
77.5°	1.4	1.4	1.2	0.0	0.0
80°	1.4	1.4	0.0	0.0	0.0
82.5°	0.3	0.3	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.6	2.2	3.9	5.0	5.0
90°	2.8	10.9	19.4	24.9	24.9
92.5°	38.2	163.3	283.0	108.6	89.2
95°	91.4	335.0	1085.3	464.1	296.3
97.5°	149.0	371.5	1656.2	1276.1	900.4
100°	191.0	394.1	1835.7	1852.8	1511.7
102.5°	230.9	421.0	1882.2	2298.7	1985.7
105°	301.8	464.2	1860.6	2833.6	2644.1
107.5°	369.3	517.7	1754.8	3095.6	3151.9
110°	418.1	553.4	1675.1	3160.8	3355.7



TEST NUMBER: P518491

CATALOG NUMBER: SQ4-BB-075U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	462.4	593.4	1595.3	3118.8	3415.5
115°	534.4	650.8	1492.3	2971.6	3372.3
117.5°	603.0	710.2	1427.0	2765.2	3218.4
120°	645.1	748.0	1398.2	2610.5	3078.8
122.5°	682.8	785.6	1378.3	2474.8	2919.3
125°	736.5	839.4	1353.9	2290.3	2682.9
127.5°	787.4	885.4	1337.8	2136.4	2480.8
130°	814.0	914.2	1329.0	2044.9	2358.9
132.5°	845.0	945.2	1322.3	1964.5	2248.2
135°	888.8	986.2	1315.1	1852.3	2095.9
137.5°	929.7	1020.2	1309.0	1761.6	1962.5
140°	960.7	1044.7	1306.8	1701.3	1882.7
142.5°	987.3	1064.7	1302.4	1647.6	1803.0
145°	1027.2	1097.6	1295.8	1578.2	1700.0
147.5°	1069.8	1130.5	1292.4	1516.7	1614.2
150°	1096.4	1150.6	1290.2	1483.0	1558.8
152.5°	1120.8	1170.6	1288.0	1453.9	1516.7
155°	1162.9	1200.8	1287.5	1418.5	1459.1
157.5°	1193.3	1224.2	1287.5	1389.4	1417.6
160°	1215.5	1239.8	1287.5	1373.8	1395.4
162.5°	1233.2	1253.2	1289.7	1360.4	1377.7
165°	1257.0	1273.2	1293.0	1345.8	1353.9
167.5°	1273.6	1286.1	1295.8	1333.5	1335.6
170°	1284.7	1292.8	1295.8	1329.0	1329.0
172.5°	1293.5	1297.3	1295.8	1322.3	1320.1
175°	1301.3	1304.0	1295.8	1312.3	1309.6
177.5°	1303.5	1303.5	1294.7	1307.8	1303.5
180°	1301.3	1301.3	1301.3	1301.3	1301.3

(END OF REPORT)