

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P518731

Luminaire Tested: **SQ4-BB-100U-100D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P518731  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2009-966-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH BLACK BAFFLE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 18293.9 lumens  
Efficiency: N/A  
Efficacy: 100.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 182.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P518731  
CATALOG NUMBER: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P518731

CATALOG NUMBER: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	96	93	89	86	87	84	82	79	69	67	65	55	54	53	42	41	41	35				
2	89	83	77	73	81	75	71	67	62	59	56	50	48	46	38	37	36	31				
3	82	74	67	62	75	68	62	58	56	52	49	45	43	41	35	34	33	28				
4	76	66	59	54	69	61	55	50	51	46	43	41	38	36	33	31	29	25				
5	70	60	53	47	64	55	49	44	46	42	38	38	35	32	30	28	27	23				
6	65	54	47	42	59	50	44	39	42	37	34	35	31	29	28	26	24	21				
7	60	49	42	37	55	46	39	35	39	34	31	32	29	26	26	24	22	19				
8	56	45	38	33	51	42	36	31	36	31	28	30	26	24	24	22	20	18				
9	53	41	35	30	48	38	32	28	33	28	25	28	24	22	23	20	19	16				
10	49	38	32	27	45	36	30	26	30	26	23	26	22	20	21	19	17	15				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17834	17834	17834
5°	17546	17503	17633
10°	16418	16637	17101
15°	14925	15399	16256
20°	13249	13937	15159
25°	11538	12452	13927
30°	9883	10968	12762
35°	8194	9311	11354
40°	6296	7445	9675
45°	4551	5637	7784
50°	3100	4201	6174
55°	2015	3039	4798
60°	1156	2140	3468
65°	306	1306	1756
70°	151	404	504
75°	67	33	0
80°	50	0	0
85°	0	0	0



TEST NUMBER: P518731

CATALOG NUMBER: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	529.2	2.9
10°-20°	1353.3	7.4
20°-30°	1694.2	9.3
30°-40°	1564.9	8.6
40°-50°	1051.5	5.7
50°-60°	543.1	3.0
60°-70°	170.1	0.9
70°-80°	10.7	0.1
80°-90°	3.8	0.0
90°-100°	819.7	4.5
100°-110°	2262.9	12.4
110°-120°	2333.8	12.8
120°-130°	1875.4	10.3
130°-140°	1473.9	8.1
140°-150°	1130.4	6.2
150°-160°	812.4	4.4
160°-170°	496.8	2.7
170°-180°	167.5	0.9
0°-30°	3576.8	19.6
0°-40°	5141.7	28.1
0°-60°	6736.4	36.8
0°-90°	6921.0	37.8
90°-120°	5416.4	29.6
90°-150°	9896.1	54.1
90°-180°	11373.0	62.2
0°-180°	18293.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5799	5799	5799	5799	5799	
5°	5684	5626	5670	5690	5712	527
15°	4688	4671	4836	4999	5106	1306
25°	3400	3428	3670	3920	4104	1559
35°	2183	2238	2480	2772	3024	1352
45°	1046	1110	1296	1548	1790	822
55°	376	439	567	728	895	351
65°	42	80	180	217	241	71
75°	6	6	3	0	0	8
85°	0	0	0	0	0	1
90°	6	11	22	25	28	9
95°	120	444	1487	611	398	129
105°	403	622	2490	3801	3579	429
115°	722	873	2005	3970	4514	710
125°	991	1128	1818	3076	3610	882
135°	1193	1322	1767	2491	2809	923
145°	1384	1479	1745	2121	2282	866
155°	1560	1612	1731	1903	1963	719
165°	1689	1711	1739	1807	1820	476
175°	1750	1753	1742	1767	1762	166
180°	1750	1750	1750	1750	1750	



TEST NUMBER: P518731

CATALOG NUMBER: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5798.8	5798.8	5798.8	5798.8	5798.8
2.5°	5812.2	5757.4	5771.8	5771.5	5756.1
5°	5683.7	5626.1	5669.7	5689.8	5711.8
7.5°	5443.6	5398.6	5482.3	5545.1	5590.6
10°	5257.3	5218.9	5327.4	5413.0	5476.1
12.5°	5041.9	5012.2	5143.4	5260.8	5341.5
15°	4687.8	4671.4	4836.5	4998.8	5105.8
17.5°	4308.5	4308.0	4496.5	4698.0	4827.0
20°	4048.2	4056.4	4258.6	4480.8	4631.7
22.5°	3787.8	3807.0	4022.9	4254.7	4427.5
25°	3400.1	3427.6	3669.5	3920.5	4104.3
27.5°	3027.6	3067.6	3322.1	3583.1	3806.9
30°	2783.0	2829.6	3088.7	3363.3	3593.7
32.5°	2542.8	2598.2	2850.8	3141.2	3376.0
35°	2182.6	2237.5	2480.0	2771.9	3024.2
37.5°	1810.6	1864.4	2101.2	2388.5	2661.2
40°	1568.2	1628.6	1854.4	2132.8	2409.8
42.5°	1348.3	1408.6	1621.0	1894.5	2156.2
45°	1046.4	1109.5	1296.1	1548.5	1789.8
47.5°	796.2	864.7	1028.5	1256.8	1476.8
50°	648.0	716.6	878.1	1079.3	1290.5
52.5°	529.1	595.5	741.2	930.7	1124.4
55°	375.9	439.0	566.7	727.6	894.9
57.5°	259.8	314.1	428.7	562.9	694.1
60°	188.0	240.1	347.9	456.9	563.9
62.5°	125.1	172.8	278.3	361.8	433.7
65°	42.1	80.5	179.5	216.6	241.3
67.5°	21.3	25.7	94.3	99.5	107.7
70°	16.8	16.8	44.9	47.9	56.1
72.5°	12.3	12.3	18.0	23.0	24.7
75°	5.6	5.6	2.8	0.0	0.0
77.5°	2.8	2.8	2.2	0.0	0.0
80°	2.8	2.8	0.0	0.0	0.0
82.5°	0.6	0.6	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	1.1	2.2	4.5	5.1	5.6
90°	5.6	11.1	22.4	25.3	28.0
92.5°	50.4	209.2	374.2	136.5	106.4
95°	120.4	443.5	1487.1	611.3	397.7
97.5°	199.4	496.8	2202.9	1696.0	1228.3
100°	257.7	528.7	2467.3	2484.7	2019.2
102.5°	313.7	565.0	2518.8	3070.0	2628.6
105°	403.3	622.3	2489.7	3800.9	3579.1
107.5°	498.5	693.5	2350.8	4153.4	4234.5
110°	565.7	741.0	2243.3	4229.2	4492.1



TEST NUMBER: P518731

CATALOG NUMBER: SQ4-BB-100U-100D-830-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	626.2	794.9	2142.4	4169.3	4557.1
115°	722.5	873.2	2005.2	3969.6	4514.5
117.5°	806.6	956.6	1915.0	3688.4	4308.4
120°	862.6	1010.4	1879.2	3498.1	4122.4
122.5°	916.3	1057.6	1850.1	3320.4	3911.8
125°	991.4	1128.3	1817.6	3076.0	3609.9
127.5°	1055.3	1192.2	1798.5	2869.3	3329.9
130°	1097.8	1234.7	1789.6	2742.9	3161.8
132.5°	1138.2	1268.5	1780.6	2636.7	3016.2
135°	1193.0	1321.7	1767.2	2491.3	2809.0
137.5°	1254.7	1371.9	1760.4	2369.3	2640.4
140°	1288.3	1403.3	1756.0	2287.9	2526.1
142.5°	1326.4	1432.6	1751.5	2215.5	2425.3
145°	1383.5	1479.3	1744.8	2120.9	2282.5
147.5°	1438.4	1522.2	1738.6	2041.1	2166.5
150°	1478.7	1547.2	1736.4	1993.5	2094.8
152.5°	1510.1	1574.1	1734.1	1952.8	2036.6
155°	1559.9	1611.9	1730.8	1903.0	1963.2
157.5°	1605.8	1645.8	1731.3	1866.7	1907.8
160°	1632.7	1668.3	1733.6	1846.3	1876.4
162.5°	1655.1	1686.4	1735.8	1828.2	1851.7
165°	1688.7	1710.7	1739.2	1806.7	1820.4
167.5°	1714.5	1727.7	1742.0	1793.6	1798.0
170°	1728.0	1738.9	1742.0	1786.8	1786.8
172.5°	1739.2	1745.7	1742.0	1777.8	1775.6
175°	1750.4	1753.1	1742.0	1767.0	1761.6
177.5°	1754.8	1752.6	1741.4	1757.0	1752.6
180°	1750.4	1750.4	1750.4	1750.4	1750.4

(END OF REPORT)