

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563155

Luminaire Tested: **SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563155  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15495.0 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 127.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563155  
CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P563155

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	89	85	88	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	80	74	69	65	62	58	55	51	48	46	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15693	15693	15693
5°	15812	15709	15651
10°	15773	15699	15655
15°	15690	15690	15676
20°	15587	15633	15633
25°	15440	15552	15504
30°	15252	15436	15369
35°	15025	15256	15149
40°	14776	14985	14833
45°	14508	14611	14385
50°	14129	14129	13903
55°	13680	13503	13300
60°	13020	12758	12555
65°	12035	11793	11690
70°	10537	10621	10578
75°	8477	9375	9432
80°	6025	7948	8033
85°	3670	6669	6669



TEST NUMBER: P563155

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	241.5	1.6
10°-20°	692.9	4.5
20°-30°	1049.4	6.8
30°-40°	1258.0	8.1
40°-50°	1282.8	8.3
50°-60°	1119.8	7.2
60°-70°	801.7	5.2
70°-80°	412.9	2.7
80°-90°	107.2	0.7
90°-100°	614.8	4.0
100°-110°	1662.2	10.7
110°-120°	1747.6	11.3
120°-130°	1419.5	9.2
130°-140°	1113.5	7.2
140°-150°	854.6	5.5
150°-160°	614.6	4.0
160°-170°	375.5	2.4
170°-180°	126.6	0.8
0°-30°	1983.8	12.8
0°-40°	3241.8	20.9
0°-60°	5644.4	36.4
0°-90°	6966.1	45.0
90°-120°	4024.6	26.0
90°-150°	7412.3	47.8
90°-180°	8529.0	55.0
0°-180°	15495.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2551	2551	2551	2551	2551	
5°	2561	2536	2544	2537	2535	243
15°	2464	2443	2464	2464	2462	695
25°	2275	2259	2292	2284	2284	1047
35°	2001	1996	2032	2018	2018	1251
45°	1668	1663	1680	1658	1654	1284
55°	1276	1260	1259	1240	1240	1137
65°	827	808	810	803	803	818
75°	357	373	394	397	397	385
85°	52	80	94	97	94	71
90°	3	8	18	20	18	8
95°	95	335	1022	529	315	100
105°	309	478	1844	2720	2609	325
115°	544	665	1529	2960	3342	537
125°	745	853	1378	2326	2733	664
135°	893	999	1341	1878	2126	690
145°	1038	1116	1323	1608	1730	649
155°	1172	1218	1312	1442	1490	541
165°	1276	1288	1317	1369	1376	359
175°	1324	1323	1319	1336	1333	126
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P563155

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2551.4	2551.4	2551.4	2551.4	2551.4
2.5°	2566.6	2544.4	2551.4	2545.6	2536.3
5°	2560.9	2535.5	2544.3	2537.2	2534.9
7.5°	2542.5	2517.0	2528.8	2524.0	2521.7
10°	2525.4	2500.0	2513.6	2508.9	2506.5
12.5°	2502.8	2479.2	2494.7	2490.0	2489.5
15°	2464.0	2443.2	2464.0	2464.0	2461.7
17.5°	2415.4	2396.4	2418.7	2420.0	2418.7
20°	2381.3	2360.5	2388.4	2386.1	2388.4
22.5°	2339.8	2322.7	2352.5	2346.4	2348.7
25°	2275.0	2258.9	2291.6	2284.5	2284.5
27.5°	2198.5	2186.9	2222.6	2215.0	2215.0
30°	2147.5	2135.9	2173.4	2164.0	2164.0
32.5°	2090.8	2082.9	2118.6	2107.3	2107.3
35°	2001.0	1996.4	2031.7	2017.5	2017.5
37.5°	1908.4	1904.2	1936.3	1919.1	1913.6
40°	1840.3	1838.0	1866.3	1847.4	1847.4
42.5°	1772.3	1770.0	1794.5	1771.8	1771.8
45°	1667.9	1663.3	1679.7	1658.3	1653.7
47.5°	1554.0	1549.4	1559.7	1536.5	1534.2
50°	1476.5	1471.9	1476.5	1455.2	1452.9
52.5°	1397.1	1388.8	1389.6	1368.3	1367.9
55°	1275.7	1259.5	1259.2	1240.3	1240.3
57.5°	1147.2	1125.9	1127.8	1111.7	1109.4
60°	1058.4	1035.3	1037.1	1022.9	1020.6
62.5°	971.4	944.6	950.2	934.1	933.6
65°	826.9	808.4	810.3	803.2	803.2
67.5°	687.9	670.8	683.2	677.5	677.1
70°	585.9	574.3	590.6	590.6	588.2
72.5°	491.4	490.9	511.2	511.3	512.6
75°	356.7	372.9	394.5	396.9	396.9
77.5°	238.1	266.8	290.6	291.5	291.1
80°	170.1	202.4	224.4	229.1	226.8
82.5°	115.3	149.5	167.7	172.4	170.1
85°	52.0	79.7	94.5	96.8	94.5
87.5°	15.7	33.4	41.5	41.7	37.7
90°	2.8	8.4	18.5	19.9	18.5
92.5°	40.4	147.4	290.8	126.2	91.4
95°	95.4	334.9	1022.4	529.1	314.7
97.5°	153.2	384.1	1593.7	1318.9	968.6
100°	196.5	404.0	1771.4	1847.4	1493.7
102.5°	236.4	431.6	1834.1	2248.1	1983.6
105°	309.0	477.5	1844.0	2720.1	2608.7
107.5°	376.2	529.9	1763.4	3014.5	3051.5
110°	428.6	567.8	1691.7	3093.6	3250.9

TEST NUMBER: P563155

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	475.3	605.6	1625.6	3077.8	3342.0
115°	544.0	665.1	1529.3	2960.5	3342.0
117.5°	611.2	724.8	1465.8	2781.4	3213.9
120°	652.2	763.6	1428.2	2652.9	3094.3
122.5°	690.9	800.1	1405.4	2515.1	2959.8
125°	744.7	853.3	1378.4	2326.0	2732.6
127.5°	794.3	900.9	1362.4	2171.7	2529.2
130°	821.6	931.6	1355.6	2076.4	2399.4
132.5°	850.1	959.0	1348.8	1990.3	2287.7
135°	892.8	998.6	1341.4	1878.1	2126.0
137.5°	935.8	1035.8	1335.1	1787.1	1989.0
140°	965.4	1058.7	1332.8	1728.5	1908.1
142.5°	993.9	1081.6	1328.3	1675.6	1832.9
145°	1038.1	1116.0	1322.9	1607.6	1730.1
147.5°	1078.2	1147.3	1316.6	1546.0	1640.1
150°	1107.8	1169.1	1314.3	1512.5	1587.7
152.5°	1135.2	1188.6	1313.2	1481.5	1543.3
155°	1171.9	1217.9	1311.5	1442.1	1489.5
157.5°	1210.1	1242.1	1311.7	1414.7	1445.9
160°	1231.7	1258.2	1312.9	1397.4	1419.7
162.5°	1248.8	1270.8	1314.0	1383.6	1400.3
165°	1275.9	1288.4	1317.2	1368.6	1375.5
167.5°	1294.4	1303.0	1317.4	1355.7	1359.0
170°	1305.8	1309.9	1318.6	1349.9	1349.9
172.5°	1314.9	1315.7	1318.6	1343.1	1341.9
175°	1324.3	1322.9	1318.6	1335.6	1332.8
177.5°	1327.4	1324.1	1318.3	1329.6	1326.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)