

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P563179

Luminaire Tested: **SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563179
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4128.6 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563179
CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563179

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57				
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48				
3	85	75	68	62	80	71	65	59	64	58	54	57	53	49	50	47	44	41				
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35				
5	72	60	51	45	67	57	49	44	51	45	40	46	41	37	41	37	33	31				
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27				
7	61	49	40	35	57	46	39	34	42	36	31	38	32	29	34	29	26	24				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19				
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6632	6632	6632
5°	6681	6640	6617
10°	6670	6623	6594
15°	6626	6590	6554
20°	6582	6545	6495
25°	6504	6459	6394
30°	6384	6349	6269
35°	6216	6174	6096
40°	6018	5979	5911
45°	5853	5812	5755
50°	5643	5607	5553
55°	5351	5280	5240
60°	4871	4731	4709
65°	4292	4113	4098
70°	3705	3552	3552
75°	3189	3144	3099
80°	2812	2844	2777
85°	2202	2399	2399



TEST NUMBER: P563179

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	2.5
10°-20°	291.2	7.1
20°-30°	436.1	10.6
30°-40°	511.5	12.4
40°-50°	513.1	12.4
50°-60°	437.7	10.6
60°-70°	285.5	6.9
70°-80°	143.2	3.5
80°-90°	40.8	1.0
90°-100°	102.8	2.5
100°-110°	270.3	6.5
110°-120°	280.3	6.8
120°-130°	224.9	5.4
130°-140°	176.4	4.3
140°-150°	135.4	3.3
150°-160°	97.5	2.4
160°-170°	59.7	1.4
170°-180°	20.2	0.5
0°-30°	829.2	20.1
0°-40°	1340.7	32.5
0°-60°	2291.6	55.5
0°-90°	2761.1	66.9
90°-120°	653.5	15.8
90°-150°	1190.2	28.8
90°-180°	1368.0	33.1
0°-180°	4128.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1078	1078	1078	1078	1078	
5°	1082	1072	1076	1072	1072	103
15°	1040	1030	1035	1031	1029	294
25°	958	947	952	943	942	441
35°	828	820	822	813	812	517
45°	673	668	668	662	662	518
55°	499	497	492	490	489	443
65°	295	289	283	281	282	294
75°	134	134	132	131	130	146
85°	31	34	34	34	34	37
90°	1	4	11	5	5	2
95°	14	53	177	91	62	15
105°	49	74	299	454	423	52
115°	87	105	239	478	545	85
125°	120	135	218	368	434	107
135°	143	158	211	297	337	111
145°	166	177	208	253	273	104
155°	188	193	208	229	235	86
165°	203	206	208	216	219	57
175°	211	211	210	212	212	20
180°	211	211	211	211	211	

TEST NUMBER: P563179

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1078.3	1078.3	1078.3	1078.3	1078.3
2.5°	1085.1	1076.3	1078.3	1076.7	1072.3
5°	1082.1	1072.0	1075.5	1071.7	1071.7
7.5°	1074.7	1063.7	1067.2	1063.4	1063.2
10°	1067.9	1056.9	1060.4	1056.6	1055.7
12.5°	1058.1	1047.0	1051.3	1046.8	1046.6
15°	1040.5	1030.4	1034.9	1031.0	1029.2
17.5°	1020.7	1009.6	1015.0	1009.7	1009.0
20°	1005.6	994.5	999.9	992.3	992.3
22.5°	987.4	976.3	982.5	972.7	972.7
25°	958.3	947.2	951.7	943.2	942.2
27.5°	923.7	912.8	917.5	907.8	907.7
30°	898.8	888.6	894.0	883.6	882.7
32.5°	871.6	862.1	866.1	855.7	854.7
35°	827.9	819.6	822.2	812.8	811.8
37.5°	782.0	773.5	776.5	768.3	768.0
40°	749.5	743.9	744.7	738.1	736.2
42.5°	719.2	712.9	713.7	707.1	706.7
45°	672.9	668.3	668.2	661.6	661.6
47.5°	623.8	620.2	619.2	613.7	613.5
50°	589.7	587.0	586.0	581.2	580.3
52.5°	554.2	552.9	549.7	545.7	545.5
55°	499.0	497.2	492.4	489.5	488.6
57.5°	439.1	435.4	430.0	425.9	426.6
60°	396.0	392.3	384.6	382.8	382.8
62.5°	354.4	350.0	342.3	339.7	341.2
65°	294.9	289.3	282.6	280.7	281.6
67.5°	240.8	235.8	228.5	228.5	227.8
70°	206.0	203.3	197.5	197.5	197.5
72.5°	175.0	173.7	169.5	169.5	168.8
75°	134.2	134.2	132.3	131.3	130.4
77.5°	100.6	100.9	100.0	99.0	97.3
80°	79.4	81.2	80.3	79.4	78.4
82.5°	59.7	61.6	61.4	59.7	59.5
85°	31.2	34.0	34.0	34.0	34.0
87.5°	8.6	12.1	14.3	13.2	13.9
90°	1.4	4.0	10.8	5.4	5.4
92.5°	5.7	27.4	60.6	26.8	17.3
95°	13.5	53.2	177.2	91.3	62.2
97.5°	23.5	58.4	265.1	210.8	155.3
100°	31.1	62.8	292.1	296.1	229.9
102.5°	37.6	67.2	299.7	368.8	312.2
105°	48.7	73.8	298.9	453.8	423.3
107.5°	60.1	83.3	281.9	497.9	505.3
110°	67.6	88.8	267.8	509.3	541.0



TEST NUMBER: P563179

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	75.2	95.3	254.8	502.1	550.8
115°	86.6	105.1	239.4	477.6	545.1
117.5°	97.7	114.6	228.8	443.7	518.6
120°	104.1	120.0	224.5	420.9	493.7
122.5°	110.6	126.5	221.3	398.2	469.9
125°	120.4	134.9	217.8	368.0	434.2
127.5°	128.2	143.0	214.8	343.7	399.5
130°	132.5	148.4	213.7	328.5	380.1
132.5°	136.9	152.7	212.6	315.4	361.7
135°	143.4	157.9	211.0	297.1	336.8
137.5°	150.1	164.4	210.7	283.4	316.0
140°	155.5	168.8	209.6	272.6	303.0
142.5°	159.9	172.0	209.6	264.9	291.1
145°	166.4	176.9	208.3	253.4	273.2
147.5°	172.9	183.2	208.3	243.8	260.2
150°	177.2	186.4	208.3	238.3	251.6
152.5°	181.5	188.7	208.3	233.9	244.0
155°	188.0	193.3	208.3	228.7	235.3
157.5°	192.9	197.9	208.3	224.1	228.8
160°	196.1	200.1	208.3	221.9	224.5
162.5°	199.4	202.3	208.3	219.7	222.4
165°	202.9	205.5	208.3	216.5	219.1
167.5°	206.1	207.4	209.6	215.1	216.1
170°	208.3	209.6	209.6	215.1	215.1
172.5°	209.4	209.6	209.6	213.9	212.9
175°	211.0	211.0	209.6	212.3	212.3
177.5°	211.0	211.0	209.9	212.1	211.0
180°	211.0	211.0	211.0	211.0	211.0

(END OF REPORT)