

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P520219

Luminaire Tested: **SQ4-F-100U-100D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P520219
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G3-1910-536-19)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-F-100U-100D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 22526.0 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 183.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P520219
CATALOG NUMBER: SQ4-F-100U-100D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P520219

CATALOG NUMBER: SQ4-F-100U-100D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	31	27	25	22
6	63	50	42	36	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	45	37	32	53	42	35	30	36	31	26	31	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	34	27	22	43	32	26	21	28	23	19	24	19	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12572	12572	12572
5°	12629	12455	12550
10°	12564	12407	12503
15°	12488	12319	12417
20°	12359	12212	12314
25°	12224	12082	12177
30°	12076	11946	12006
35°	11924	11776	11840
40°	11726	11591	11602
45°	11519	11361	11324
50°	11222	11088	11061
55°	10891	10771	10696
60°	10562	10371	10337
65°	10045	9820	9739
70°	9334	9107	8931
75°	8334	8068	7901
80°	6858	6608	6310
85°	4058	4453	4555



TEST NUMBER: P520219

CATALOG NUMBER: SQ4-F-100U-100D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	385.8	1.7
10°-20°	1098.7	4.9
20°-30°	1650.0	7.3
30°-40°	1969.1	8.7
40°-50°	2018.3	9.0
50°-60°	1797.3	8.0
60°-70°	1339.8	5.9
70°-80°	725.4	3.2
80°-90°	168.7	0.7
90°-100°	819.7	3.6
100°-110°	2262.9	10.0
110°-120°	2333.8	10.4
120°-130°	1875.4	8.3
130°-140°	1473.9	6.5
140°-150°	1130.4	5.0
150°-160°	812.4	3.6
160°-170°	496.8	2.2
170°-180°	167.5	0.7
0°-30°	3134.5	13.9
0°-40°	5103.6	22.7
0°-60°	8919.2	39.6
0°-90°	11153.1	49.5
90°-120°	5416.4	24.0
90°-150°	9896.1	43.9
90°-180°	11373.0	50.5
0°-180°	22526.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4088	4088	4088	4088	4088	
5°	4091	4082	4035	4071	4065	388
15°	3922	3909	3869	3900	3900	1105
25°	3602	3594	3560	3580	3588	1660
35°	3176	3162	3137	3143	3154	1983
45°	2649	2635	2612	2598	2604	2038
55°	2031	2034	2009	1989	1995	1818
65°	1380	1375	1350	1336	1338	1365
75°	701	693	679	665	665	747
85°	115	126	126	129	129	161
90°	6	11	22	25	28	11
95°	120	444	1487	611	398	129
105°	403	622	2490	3801	3579	429
115°	722	873	2005	3970	4514	710
125°	991	1128	1818	3076	3610	882
135°	1193	1322	1767	2491	2809	923
145°	1384	1479	1745	2121	2282	866
155°	1560	1612	1731	1903	1963	719
165°	1689	1711	1739	1807	1820	476
175°	1750	1753	1742	1767	1762	166
180°	1750	1750	1750	1750	1750	

TEST NUMBER: P520219

CATALOG NUMBER: SQ4-F-100U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4087.9	4087.9	4087.9	4087.9	4087.9
2.5°	4103.6	4094.9	4058.7	4087.8	4083.4
5°	4090.7	4082.5	4034.6	4070.9	4065.4
7.5°	4052.6	4044.3	4002.0	4035.6	4030.7
10°	4023.3	4015.1	3972.9	4006.5	4003.7
12.5°	3985.2	3977.0	3934.7	3968.3	3965.6
15°	3922.4	3908.6	3869.1	3899.9	3899.9
17.5°	3839.3	3828.8	3792.2	3818.0	3818.5
20°	3776.4	3768.2	3731.5	3759.7	3762.5
22.5°	3713.6	3705.4	3664.3	3690.1	3695.1
25°	3602.5	3594.3	3560.4	3580.2	3588.5
27.5°	3488.0	3476.0	3442.6	3460.2	3466.2
30°	3400.5	3395.1	3364.0	3372.7	3380.9
32.5°	3308.5	3303.0	3276.5	3280.7	3295.6
35°	3176.1	3162.3	3136.7	3142.6	3153.6
37.5°	3019.5	3012.9	2988.0	2985.0	2995.4
40°	2920.7	2909.7	2887.1	2881.6	2889.8
42.5°	2812.9	2802.0	2774.8	2769.4	2779.9
45°	2648.6	2634.9	2612.1	2598.2	2603.7
47.5°	2464.5	2464.5	2441.0	2424.8	2433.1
50°	2345.6	2345.6	2317.5	2303.7	2311.9
52.5°	2222.1	2224.3	2194.1	2186.6	2184.0
55°	2031.3	2034.1	2008.9	1989.4	1994.8
57.5°	1847.3	1841.2	1811.9	1799.0	1801.8
60°	1717.1	1708.9	1686.2	1666.9	1680.6
62.5°	1584.6	1580.9	1558.3	1536.4	1534.7
65°	1380.4	1374.9	1349.5	1335.5	1338.3
67.5°	1177.3	1170.7	1147.6	1127.5	1134.6
70°	1038.1	1038.1	1012.8	1001.4	993.2
72.5°	910.2	899.2	880.4	864.6	858.5
75°	701.4	693.2	679.0	664.9	664.9
77.5°	510.7	503.5	494.3	484.8	482.0
80°	387.2	384.4	373.1	370.1	356.3
82.5°	272.7	272.2	265.4	258.1	257.5
85°	115.0	126.0	126.2	129.1	129.1
87.5°	21.3	35.6	35.9	32.0	32.5
90°	5.6	11.1	22.4	25.2	28.0
92.5°	50.5	209.2	374.1	136.5	106.4
95°	120.4	443.6	1487.1	611.2	397.7
97.5°	199.4	496.8	2202.9	1696.0	1228.3
100°	257.7	528.7	2467.3	2484.7	2019.2
102.5°	313.7	565.0	2518.8	3070.0	2628.6
105°	403.3	622.3	2489.7	3801.0	3579.1
107.5°	498.5	693.4	2350.8	4153.4	4234.4
110°	565.7	740.9	2243.3	4229.2	4492.1



TEST NUMBER: P520219

CATALOG NUMBER: SQ4-F-100U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	626.2	794.9	2142.4	4169.4	4557.1
115°	722.5	873.2	2005.2	3969.6	4514.5
117.5°	806.6	956.7	1915.0	3688.4	4308.4
120°	862.6	1010.5	1879.2	3498.1	4122.5
122.5°	916.3	1057.7	1850.0	3320.3	3911.9
125°	991.4	1128.3	1817.6	3076.0	3610.0
127.5°	1055.3	1192.2	1798.5	2869.3	3329.9
130°	1097.8	1234.7	1789.6	2742.9	3161.8
132.5°	1138.2	1268.5	1780.6	2636.7	3016.2
135°	1193.0	1321.8	1767.1	2491.3	2809.0
137.5°	1254.6	1371.8	1760.4	2369.3	2640.4
140°	1288.3	1403.3	1756.0	2287.9	2526.1
142.5°	1326.3	1432.6	1751.5	2215.6	2425.3
145°	1383.5	1479.3	1744.8	2120.9	2282.4
147.5°	1438.4	1522.2	1738.6	2041.2	2166.5
150°	1478.7	1547.1	1736.4	1993.5	2094.9
152.5°	1510.0	1574.1	1734.1	1952.8	2036.6
155°	1559.9	1611.9	1730.7	1903.0	1963.2
157.5°	1605.9	1645.9	1731.3	1866.7	1907.7
160°	1632.7	1668.3	1733.5	1846.3	1876.3
162.5°	1655.2	1686.3	1735.8	1828.2	1851.7
165°	1688.8	1710.7	1739.1	1806.7	1820.4
167.5°	1714.5	1727.7	1741.9	1793.6	1798.0
170°	1728.0	1738.9	1741.9	1786.7	1786.7
172.5°	1739.1	1745.8	1741.9	1777.7	1775.5
175°	1750.3	1753.1	1741.9	1767.0	1761.6
177.5°	1754.9	1752.7	1741.4	1757.0	1752.6
180°	1750.3	1750.3	1750.3	1750.3	1750.3

(END OF REPORT)