

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563299

Luminaire Tested: **SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563299
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6889.8 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563299
CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563299

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	69	64	61	59	56	54	51	49	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	54	49	54	48	44	47	43	39	40	37	34	31
5	70	58	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	38	60	49	42	37	44	38	33	38	33	30	33	29	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	26	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9775	9775	9775
5°	9847	9787	9753
10°	9831	9761	9718
15°	9766	9713	9659
20°	9701	9646	9574
25°	9585	9520	9425
30°	9408	9359	9240
35°	9162	9100	8984
40°	8869	8813	8713
45°	8627	8566	8482
50°	8317	8264	8184
55°	7887	7782	7723
60°	7179	6974	6939
65°	6325	6062	6041
70°	5462	5235	5235
75°	4701	4634	4568
80°	4144	4194	4095
85°	3246	3536	3536



TEST NUMBER: P563299

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	2.2
10°-20°	429.1	6.2
20°-30°	642.8	9.3
30°-40°	753.9	10.9
40°-50°	756.3	11.0
50°-60°	645.2	9.4
60°-70°	420.8	6.1
70°-80°	211.1	3.1
80°-90°	60.1	0.9
90°-100°	207.4	3.0
100°-110°	563.3	8.2
110°-120°	579.1	8.4
120°-130°	463.0	6.7
130°-140°	363.8	5.3
140°-150°	279.0	4.0
150°-160°	200.6	2.9
160°-170°	122.7	1.8
170°-180°	41.3	0.6
0°-30°	1222.2	17.7
0°-40°	1976.1	28.7
0°-60°	3377.6	49.0
0°-90°	4069.5	59.1
90°-120°	1349.8	19.6
90°-150°	2455.6	35.6
90°-180°	2820.0	40.9
0°-180°	6889.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1589	1589	1589	1589	1589	
5°	1595	1580	1585	1580	1580	151
15°	1534	1519	1525	1520	1517	433
25°	1412	1396	1403	1390	1389	649
35°	1220	1208	1212	1198	1196	762
45°	992	985	985	975	975	764
55°	736	733	726	722	720	654
65°	435	426	416	414	415	434
75°	198	198	195	194	192	215
85°	46	50	50	50	50	54
90°	1	6	10	12	12	4
95°	31	113	361	157	106	32
105°	100	156	619	943	888	106
115°	178	216	496	986	1124	175
125°	244	278	449	756	892	218
135°	294	327	436	616	694	228
145°	340	365	430	523	562	214
155°	385	398	428	470	483	177
165°	417	422	429	447	449	118
175°	432	433	430	436	435	41
180°	432	432	432	432	432	

TEST NUMBER: P563299

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1589.3	1589.3	1589.3	1589.3	1589.3
2.5°	1599.4	1586.3	1589.3	1587.0	1580.4
5°	1594.9	1579.9	1585.2	1579.6	1579.6
7.5°	1584.1	1567.7	1572.9	1567.3	1567.1
10°	1574.0	1557.7	1562.9	1557.3	1555.9
12.5°	1559.5	1543.2	1549.5	1542.8	1542.5
15°	1533.6	1518.6	1525.3	1519.6	1516.9
17.5°	1504.4	1488.0	1496.0	1488.2	1487.1
20°	1482.1	1465.7	1473.7	1462.6	1462.6
22.5°	1455.3	1439.0	1448.1	1433.6	1433.6
25°	1412.4	1396.1	1402.7	1390.1	1388.8
27.5°	1361.5	1345.4	1352.3	1338.1	1337.8
30°	1324.7	1309.7	1317.7	1302.4	1301.0
32.5°	1284.6	1270.7	1276.5	1261.1	1259.8
35°	1220.2	1208.0	1211.9	1197.9	1196.5
37.5°	1152.5	1140.0	1144.4	1132.5	1131.9
40°	1104.6	1096.4	1097.6	1087.8	1085.1
42.5°	1060.0	1050.8	1052.0	1042.2	1041.6
45°	991.8	985.0	984.8	975.1	975.1
47.5°	919.3	914.2	912.7	904.6	904.3
50°	869.2	865.1	863.6	856.6	855.3
52.5°	816.8	814.9	810.1	804.3	804.0
55°	735.5	732.7	725.7	721.5	720.2
57.5°	647.2	641.7	633.8	627.7	628.8
60°	583.6	578.2	566.9	564.1	564.1
62.5°	522.4	515.8	504.5	500.7	502.9
65°	434.6	426.4	416.5	413.7	415.1
67.5°	354.9	347.6	336.8	336.8	335.7
70°	303.7	299.6	291.1	291.1	291.1
72.5°	258.0	256.1	249.9	249.9	248.8
75°	197.8	197.8	195.0	193.6	192.2
77.5°	148.2	148.8	147.4	145.9	143.5
80°	117.0	119.7	118.4	117.0	115.6
82.5°	88.0	90.8	90.5	88.0	87.8
85°	46.0	50.1	50.1	50.1	50.1
87.5°	12.5	17.7	19.8	20.4	21.4
90°	1.4	5.5	9.7	12.5	12.5
92.5°	12.5	56.8	98.6	42.4	35.8
95°	30.6	113.4	361.1	157.2	105.6
97.5°	50.6	125.2	553.6	430.7	302.5
100°	63.9	133.1	612.5	620.9	501.4
102.5°	77.2	141.0	628.0	767.9	662.5
105°	100.0	155.7	619.4	943.2	887.5
107.5°	123.6	172.8	583.6	1033.7	1049.1
110°	140.3	185.1	556.9	1051.5	1118.0

TEST NUMBER: P563299

CATALOG NUMBER: SQ4-PP3-050U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.7	197.4	530.3	1036.7	1136.9
115°	177.8	215.8	495.8	986.4	1123.6
117.5°	199.4	235.8	473.9	915.2	1069.7
120°	213.9	249.2	463.9	867.4	1020.8
122.5°	226.1	261.4	457.2	819.5	967.5
125°	244.4	278.4	448.6	755.8	891.6
127.5°	260.8	294.5	443.9	707.6	824.2
130°	270.8	303.4	441.7	677.4	781.9
132.5°	280.8	313.4	439.4	651.5	744.2
135°	294.4	327.0	436.1	615.7	694.4
137.5°	309.2	338.8	434.4	584.0	650.3
140°	318.0	346.6	433.3	563.8	623.6
142.5°	326.9	353.3	432.2	548.1	598.0
145°	340.3	364.7	430.5	523.1	562.5
147.5°	355.3	376.2	429.2	503.5	534.4
150°	365.3	382.9	429.2	492.2	516.7
152.5°	373.0	388.5	428.0	482.1	502.2
155°	384.7	398.3	427.8	469.7	483.3
157.5°	396.1	406.7	427.8	461.3	471.7
160°	402.8	412.3	427.8	455.7	463.9
162.5°	409.4	416.8	428.9	451.2	457.2
165°	416.7	422.1	429.2	447.2	448.6
167.5°	424.2	426.9	430.5	442.5	443.6
170°	426.4	429.1	430.5	440.3	440.3
172.5°	428.6	430.2	430.5	438.0	438.0
175°	431.9	433.3	430.5	436.1	434.7
177.5°	433.0	433.0	429.7	434.1	431.9
180°	431.9	431.9	431.9	431.9	431.9

(END OF REPORT)