

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563347

Luminaire Tested: **SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563347
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9719.4 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563347
CATALOG NUMBER: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563347

CATALOG NUMBER: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60
2	94	86	80	75	89	82	76	72	74	69	66	66	63	60	59	57	55	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	43
4	79	68	59	53	74	64	57	51	58	52	48	53	48	44	47	44	40	37
5	72	60	52	46	68	58	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	34	31	29
7	62	49	41	35	58	47	39	34	43	37	32	39	34	30	35	31	28	25
8	57	45	37	31	54	43	35	30	39	33	29	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16576	16576	16576
5°	16697	16595	16537
10°	16669	16551	16477
15°	16559	16469	16379
20°	16449	16357	16233
25°	16253	16141	15981
30°	15953	15869	15668
35°	15536	15429	15234
40°	15039	14944	14773
45°	14628	14525	14381
50°	14103	14013	13877
55°	13373	13195	13095
60°	12174	11826	11768
65°	10725	10278	10243
70°	9260	8877	8877
75°	7971	7859	7745
80°	7028	7113	6943
85°	5498	5999	5999



TEST NUMBER: P563347

CATALOG NUMBER: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.8	2.6
10°-20°	727.6	7.5
20°-30°	1089.9	11.2
30°-40°	1278.4	13.2
40°-50°	1282.4	13.2
50°-60°	1094.0	11.3
60°-70°	713.4	7.3
70°-80°	357.9	3.7
80°-90°	100.7	1.0
90°-100°	207.4	2.1
100°-110°	563.3	5.8
110°-120°	579.1	6.0
120°-130°	463.0	4.8
130°-140°	363.8	3.7
140°-150°	279.0	2.9
150°-160°	200.6	2.1
160°-170°	122.7	1.3
170°-180°	41.3	0.4
0°-30°	2072.3	21.3
0°-40°	3350.7	34.5
0°-60°	5727.0	58.9
0°-90°	6899.1	71.0
90°-120°	1349.8	13.9
90°-150°	2455.6	25.3
90°-180°	2820.0	29.0
0°-180°	9719.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2695	2695	2695	2695	2695	
5°	2704	2679	2688	2678	2678	257
15°	2600	2575	2586	2577	2572	734
25°	2395	2367	2378	2357	2355	1101
35°	2069	2048	2055	2031	2029	1292
45°	1682	1670	1670	1653	1653	1295
55°	1247	1242	1230	1223	1221	1108
65°	737	723	706	702	704	735
75°	335	335	331	328	326	364
85°	78	85	85	85	85	92
90°	1	6	10	12	12	5
95°	31	113	361	157	106	32
105°	100	156	619	943	888	106
115°	178	216	496	986	1124	175
125°	244	278	449	756	892	218
135°	294	327	436	616	694	228
145°	340	365	430	523	562	214
155°	385	398	428	470	483	177
165°	417	422	429	447	449	118
175°	432	433	430	436	435	41
180°	432	432	432	432	432	

TEST NUMBER: P563347

CATALOG NUMBER: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2694.9	2694.9	2694.9	2694.9	2694.9
2.5°	2711.9	2689.7	2694.9	2690.9	2679.8
5°	2704.3	2678.9	2687.8	2678.4	2678.4
7.5°	2685.9	2658.2	2667.0	2657.6	2657.1
10°	2668.9	2641.2	2650.0	2640.5	2638.2
12.5°	2644.4	2616.6	2627.4	2616.0	2615.5
15°	2600.4	2575.0	2586.3	2576.7	2572.1
17.5°	2550.8	2523.1	2536.7	2523.4	2521.5
20°	2513.0	2485.3	2498.9	2480.0	2480.0
22.5°	2467.7	2440.0	2455.4	2430.8	2430.8
25°	2394.9	2367.2	2378.4	2357.1	2354.8
27.5°	2308.5	2281.2	2292.9	2268.8	2268.3
30°	2246.1	2220.7	2234.3	2208.3	2206.0
32.5°	2178.1	2154.6	2164.4	2138.4	2136.1
35°	2069.0	2048.2	2054.8	2031.2	2028.9
37.5°	1954.2	1933.0	1940.5	1920.2	1919.3
40°	1873.0	1859.1	1861.2	1844.5	1839.9
42.5°	1797.4	1781.7	1783.7	1767.1	1766.2
45°	1681.7	1670.1	1669.8	1653.3	1653.3
47.5°	1558.8	1550.1	1547.5	1533.8	1533.3
50°	1473.8	1466.9	1464.4	1452.5	1450.2
52.5°	1385.0	1381.8	1373.7	1363.7	1363.3
55°	1247.1	1242.5	1230.5	1223.4	1221.1
57.5°	1097.3	1088.1	1074.7	1064.3	1066.2
60°	989.6	980.4	961.3	956.6	956.6
62.5°	885.7	874.6	855.5	848.9	852.6
65°	736.9	723.0	706.2	701.5	703.8
67.5°	601.8	589.3	571.1	571.1	569.2
70°	514.9	508.0	493.6	493.6	493.6
72.5°	437.4	434.2	423.7	423.7	421.8
75°	335.4	335.4	330.7	328.2	325.9
77.5°	251.3	252.2	249.9	247.4	243.3
80°	198.4	203.0	200.8	198.3	196.0
82.5°	149.3	153.9	153.5	149.3	148.8
85°	77.9	84.9	85.0	85.0	85.0
87.5°	21.1	29.3	32.2	32.8	34.6
90°	1.4	5.5	9.7	12.5	12.5
92.5°	12.5	56.8	98.6	42.4	35.8
95°	30.6	113.4	361.1	157.2	105.6
97.5°	50.6	125.2	553.6	430.7	302.5
100°	63.9	133.1	612.5	620.9	501.4
102.5°	77.2	141.0	628.0	767.9	662.5
105°	100.0	155.7	619.4	943.2	887.5
107.5°	123.6	172.8	583.6	1033.7	1049.1
110°	140.3	185.1	556.9	1051.5	1118.0



TEST NUMBER: P563347

CATALOG NUMBER: SQ4-PP3-050U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.7	197.4	530.3	1036.7	1136.9
115°	177.8	215.8	495.8	986.4	1123.6
117.5°	199.4	235.8	473.9	915.2	1069.7
120°	213.9	249.2	463.9	867.4	1020.8
122.5°	226.1	261.4	457.2	819.5	967.5
125°	244.4	278.4	448.6	755.8	891.6
127.5°	260.8	294.5	443.9	707.6	824.2
130°	270.8	303.4	441.7	677.4	781.9
132.5°	280.8	313.4	439.4	651.5	744.2
135°	294.4	327.0	436.1	615.7	694.4
137.5°	309.2	338.8	434.4	584.0	650.3
140°	318.0	346.6	433.3	563.8	623.6
142.5°	326.9	353.3	432.2	548.1	598.0
145°	340.3	364.7	430.5	523.1	562.5
147.5°	355.3	376.2	429.2	503.5	534.4
150°	365.3	382.9	429.2	492.2	516.7
152.5°	373.0	388.5	428.0	482.1	502.2
155°	384.7	398.3	427.8	469.7	483.3
157.5°	396.1	406.7	427.8	461.3	471.7
160°	402.8	412.3	427.8	455.7	463.9
162.5°	409.4	416.8	428.9	451.2	457.2
165°	416.7	422.1	429.2	447.2	448.6
167.5°	424.2	426.9	430.5	442.5	443.6
170°	426.4	429.1	430.5	440.3	440.3
172.5°	428.6	430.2	430.5	438.0	438.0
175°	431.9	433.3	430.5	436.1	434.7
177.5°	433.0	433.0	429.7	434.1	431.9
180°	431.9	431.9	431.9	431.9	431.9

(END OF REPORT)