

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937209

Luminaire Tested: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937209
REPORT IS A COMBINATION OF REPORTS P933495 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17708.9 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 153.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937209
CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937209

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	93	89	85	90	86	82	79	73	70	68	61	59	57	50	49	47	42
2	88	80	74	69	81	74	69	64	63	59	55	53	50	47	43	41	39	34
3	80	70	62	56	74	65	58	53	55	50	46	46	42	39	38	35	32	28
4	73	62	53	47	67	57	50	44	49	43	38	41	36	33	33	30	27	24
5	67	55	46	40	61	51	43	37	43	37	33	36	32	28	30	26	23	20
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	27	23	20	17
7	56	44	35	30	52	41	33	28	35	29	24	29	25	21	24	20	18	15
8	52	39	31	26	48	37	29	24	31	26	21	27	22	19	22	18	16	13
9	49	36	28	23	45	33	26	22	29	23	19	24	20	16	20	17	14	12
10	45	33	25	20	42	31	24	19	26	21	17	22	18	15	19	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3645	3645	3645
5°	3562	4214	4900
10°	3232	6144	8122
15°	2748	8029	9808
20°	2238	9307	9996
25°	1868	9741	9793
30°	1576	9805	9774
35°	1394	9645	10027
40°	1215	9436	10288
45°	1101	9284	10329
50°	1011	9148	10157
55°	969	8947	9707
60°	993	8558	8996
65°	1035	7965	8019
70°	1105	6951	6775
75°	1230	5672	5287
80°	1352	3939	3562
85°	1228	2093	1824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10329 cd/sqm



TEST NUMBER: P937209

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.4	0.9
10°-20°	675.6	3.8
20°-30°	1181.7	6.7
30°-40°	1521.2	8.6
40°-50°	1699.2	9.6
50°-60°	1627.4	9.2
60°-70°	1289.7	7.3
70°-80°	758.4	4.3
80°-90°	215.7	1.2
90°-100°	645.7	3.6
100°-110°	1697.7	9.6
110°-120°	1760.3	9.9
120°-130°	1411.9	8.0
130°-140°	1107.9	6.3
140°-150°	850.3	4.8
150°-160°	612.4	3.5
160°-170°	374.7	2.1
170°-180°	126.6	0.7
0°-30°	2009.8	11.3
0°-40°	3531.0	19.9
0°-60°	6857.6	38.7
0°-90°	9121.5	51.5
90°-120°	4103.6	23.2
90°-150°	7473.8	42.2
90°-180°	8587.0	48.5
0°-180°	17708.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1178	1178	1178	1178	1178	
5°	1148	1232	1387	1569	1626	106
15°	860	1588	2675	3244	3346	239
25°	549	1800	3187	3327	3331	253
35°	371	1720	3001	3172	3297	232
45°	254	1372	2652	3039	3175	196
55°	182	872	2251	2615	2687	166
65°	144	462	1671	1879	1906	143
75°	106	284	917	1008	1012	111
85°	38	87	227	250	254	40
90°	9	25	68	34	34	10
95°	85	334	1112	573	390	95
105°	306	463	1877	2850	2658	324
115°	543	660	1503	2999	3423	537
125°	756	847	1367	2311	2726	671
135°	901	991	1325	1865	2115	697
145°	1045	1111	1308	1592	1716	654
155°	1181	1214	1308	1436	1478	542
165°	1274	1291	1308	1359	1376	360
175°	1325	1325	1317	1334	1334	126
180°	1325	1325	1325	1325	1325	



TEST NUMBER: P937209

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5	1178.5
2.5°	1178.5	1178.5	1186.0	1189.8	1197.4	1201.2	1208.8	1216.3	1239.1	1242.9	1250.4
5°	1148.2	1163.3	1212.6	1231.5	1284.6	1356.6	1386.9	1436.1	1538.4	1568.7	1587.6
7.5°	1102.7	1136.8	1258.0	1288.3	1420.9	1610.4	1690.0	1796.0	1959.0	2038.6	2103.0
10°	1030.7	1102.7	1318.6	1390.6	1606.7	1894.6	2042.4	2190.2	2436.5	2546.3	2588.0
12.5°	951.1	1068.5	1383.0	1481.6	1792.3	2212.9	2391.0	2554.0	2834.3	2982.1	3004.8
15°	860.1	1019.3	1443.7	1587.6	1989.3	2478.1	2675.2	2876.0	3137.5	3243.5	3270.1
17.5°	780.6	981.4	1500.5	1652.1	2140.9	2716.9	2917.7	3084.4	3296.6	3368.6	3387.6
20°	682.0	920.8	1538.4	1735.4	2300.0	2891.1	3084.4	3213.2	3357.2	3402.7	3410.2
22.5°	610.0	856.4	1561.1	1765.7	2406.2	2997.3	3160.2	3262.5	3361.0	3376.2	3379.9
25°	549.4	784.4	1557.3	1799.9	2497.1	3061.7	3186.7	3262.5	3319.3	3326.9	3326.9
27.5°	492.6	704.8	1542.2	1807.4	2565.3	3076.8	3175.4	3228.4	3254.9	3270.1	3270.1
30°	443.3	629.0	1504.3	1792.3	2595.6	3061.7	3141.2	3167.8	3194.3	3217.0	3228.4
32.5°	405.4	557.0	1447.5	1762.0	2599.4	3023.8	3080.6	3095.8	3133.7	3186.7	3205.7
35°	371.3	485.0	1383.0	1720.3	2576.6	2963.1	3001.1	3016.2	3092.0	3171.5	3198.1
37.5°	337.3	432.0	1299.7	1648.3	2542.6	2891.1	2917.7	2944.2	3061.7	3156.4	3186.7
40°	303.1	386.5	1201.2	1568.7	2489.5	2804.0	2826.7	2868.4	3023.8	3133.7	3164.0
42.5°	276.6	348.7	1095.1	1485.3	2421.3	2705.5	2739.6	2800.2	2978.3	3095.8	3129.8
45°	253.9	310.7	981.4	1371.7	2334.2	2603.2	2652.4	2735.8	2925.3	3038.9	3069.2
47.5°	231.2	284.2	863.9	1254.3	2239.4	2500.9	2565.3	2660.0	2853.3	2963.1	2989.7
50°	212.2	257.6	746.4	1129.2	2137.1	2391.0	2466.8	2565.3	2762.4	2864.7	2898.8
52.5°	197.0	234.9	636.6	1004.2	2019.6	2277.3	2364.5	2466.8	2652.4	2751.0	2773.7
55°	181.9	216.0	541.9	871.5	1898.4	2156.1	2250.8	2349.3	2531.2	2614.6	2629.7
57.5°	174.3	200.9	462.3	746.4	1769.6	2019.6	2125.8	2216.7	2387.2	2451.6	2466.8
60°	162.9	189.5	401.6	640.3	1629.3	1890.8	1981.8	2072.7	2216.7	2269.7	2281.1
62.5°	151.5	181.9	356.2	538.0	1485.3	1739.3	1830.2	1913.5	2034.8	2072.7	2087.8
65°	144.0	174.3	322.1	462.3	1337.6	1580.1	1671.0	1743.1	1841.5	1879.4	1887.0
67.5°	136.4	166.7	295.6	397.9	1189.8	1420.9	1489.2	1557.3	1633.1	1671.0	1674.8
70°	125.0	159.2	272.8	352.4	1038.2	1239.1	1296.0	1367.9	1428.6	1447.5	1458.9
72.5°	117.5	147.8	257.6	318.3	882.9	1064.8	1117.9	1159.5	1212.6	1231.5	1231.5
75°	106.1	132.6	242.5	284.2	723.7	871.5	917.0	958.7	1000.4	1007.9	996.5
77.5°	94.7	117.5	208.4	238.7	564.6	689.7	727.5	750.3	784.4	792.0	795.8
80°	79.5	102.3	162.9	185.7	409.3	507.7	534.3	553.2	583.5	583.5	591.1
82.5°	60.6	79.5	117.5	132.6	276.6	348.7	371.3	382.7	401.6	401.6	401.6
85°	37.9	49.2	75.8	87.2	166.7	212.2	227.3	231.2	246.3	250.1	250.1
87.5°	18.9	26.5	49.2	53.1	87.2	109.8	109.8	117.5	117.5	113.7	109.8
90°	8.9	16.0	23.0	24.9	39.1	58.1	67.6	60.0	45.0	33.7	33.7
92.5°	35.6	96.0	156.5	171.6	241.2	334.0	380.5	333.5	239.5	168.9	162.2
95°	85.4	196.0	306.7	334.3	593.6	939.4	1112.2	992.5	753.0	573.4	553.0
97.5°	147.6	245.2	342.8	367.2	799.6	1376.1	1664.3	1588.6	1437.3	1323.8	1285.1
100°	195.6	284.1	372.6	394.7	874.5	1514.2	1834.1	1839.6	1850.7	1859.0	1812.9
102.5°	236.5	319.1	401.6	422.3	908.9	1557.7	1882.2	1978.5	2171.4	2316.0	2276.5
105°	305.8	375.8	445.7	463.2	934.4	1562.7	1876.8	2093.0	2525.3	2849.5	2828.2
107.5°	377.0	442.2	507.3	523.7	939.2	1493.2	1770.1	2071.7	2674.6	3126.8	3132.0
110°	424.9	483.8	542.7	557.4	932.0	1431.5	1681.2	2018.3	2692.4	3197.9	3220.0



TEST NUMBER: P937209

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	472.1	528.2	584.3	598.4	932.4	1377.7	1600.3	1945.3	2635.2	3152.6	3186.5
115°	543.2	594.9	646.7	659.6	940.9	1315.9	1503.4	1835.7	2500.3	2998.8	3045.9
117.5°	613.5	660.5	707.4	719.2	958.4	1277.2	1436.7	1736.6	2336.4	2786.3	2838.6
120°	654.4	698.6	742.8	753.9	972.6	1264.2	1410.0	1684.0	2232.1	2643.1	2693.9
122.5°	694.3	739.0	783.6	794.8	993.1	1257.4	1389.5	1636.3	2129.9	2500.0	2550.1
125°	755.7	796.4	837.2	847.3	1020.6	1251.8	1367.4	1577.0	1996.2	2310.7	2356.8
127.5°	805.5	846.6	887.7	898.0	1048.3	1248.5	1348.7	1528.7	1888.7	2158.6	2197.6
130°	832.2	876.5	920.6	931.7	1068.3	1250.4	1341.6	1501.8	1822.2	2062.6	2098.5
132.5°	859.7	904.0	948.2	959.3	1084.6	1251.8	1335.3	1478.7	1765.6	1980.8	2013.0
135°	900.6	940.9	981.2	991.3	1102.5	1250.6	1324.7	1444.8	1685.0	1865.3	1893.0
137.5°	942.4	982.3	1022.3	1032.2	1129.1	1258.3	1322.9	1424.4	1627.6	1779.9	1802.6
140°	977.0	1013.7	1050.5	1059.7	1145.4	1259.6	1316.7	1404.5	1579.9	1711.4	1732.7
142.5°	1003.7	1037.7	1071.7	1080.2	1159.1	1264.1	1316.7	1393.8	1547.9	1663.4	1681.7
145°	1044.6	1074.3	1103.9	1111.4	1176.8	1264.1	1307.8	1370.8	1496.9	1591.5	1605.3
147.5°	1085.5	1114.4	1143.3	1150.5	1202.9	1272.8	1307.8	1357.4	1456.6	1530.9	1542.4
150°	1112.2	1138.3	1164.4	1170.9	1216.5	1277.4	1307.8	1349.7	1433.4	1496.2	1505.5
152.5°	1139.7	1159.5	1179.2	1184.2	1225.4	1280.4	1307.8	1343.6	1415.1	1468.7	1475.7
155°	1180.7	1195.3	1209.9	1213.5	1245.0	1286.9	1307.8	1336.3	1393.2	1435.8	1440.5
157.5°	1210.9	1225.1	1239.4	1242.9	1264.5	1293.4	1307.8	1329.9	1374.2	1407.3	1410.6
160°	1231.3	1242.4	1253.5	1256.3	1273.5	1296.3	1307.8	1326.7	1364.7	1393.2	1395.1
162.5°	1251.8	1260.1	1268.3	1270.4	1282.9	1299.5	1307.8	1323.8	1355.8	1379.8	1381.6
165°	1274.1	1281.5	1289.0	1290.9	1296.5	1304.1	1307.8	1319.3	1342.1	1359.3	1361.2
167.5°	1294.4	1298.0	1301.6	1302.5	1307.2	1313.5	1316.7	1324.2	1339.2	1350.4	1351.2
170°	1307.8	1311.3	1315.0	1315.8	1316.1	1316.5	1316.7	1324.2	1339.2	1350.4	1350.4
172.5°	1314.9	1315.6	1316.5	1316.7	1316.7	1316.7	1316.7	1322.6	1334.5	1343.4	1342.7
175°	1324.7	1324.7	1324.7	1324.7	1322.1	1318.5	1316.7	1320.4	1328.0	1333.6	1333.6
177.5°	1324.7	1324.7	1324.7	1324.7	1322.6	1319.9	1318.5	1321.5	1327.4	1331.8	1331.0
180°	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7	1324.7



TEST NUMBER: P937209

CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1178.5	1178.5
2.5°	1258.0	1250.4
5°	1618.0	1625.6
7.5°	2178.8	2175.0
10°	2709.3	2743.3
12.5°	3095.8	3103.4
15°	3330.7	3345.9
17.5°	3421.6	3425.4
20°	3425.4	3417.9
22.5°	3383.8	3376.2
25°	3334.5	3330.7
27.5°	3289.0	3292.8
30°	3270.1	3281.5
32.5°	3270.1	3289.0
35°	3277.6	3296.6
37.5°	3273.8	3296.6
40°	3258.7	3285.2
42.5°	3217.0	3236.0
45°	3152.6	3175.4
47.5°	3069.2	3084.4
50°	2963.1	2978.3
52.5°	2830.5	2834.3
55°	2671.4	2686.6
57.5°	2500.9	2504.6
60°	2311.4	2322.8
62.5°	2110.6	2110.6
65°	1898.4	1906.0
67.5°	1678.6	1697.6
70°	1455.0	1458.9
72.5°	1235.2	1235.2
75°	1007.9	1011.7
77.5°	792.0	792.0
80°	587.4	591.1
82.5°	405.4	413.0
85°	253.9	253.9
87.5°	117.5	106.1
90°	33.7	33.7
92.5°	135.4	108.5
95°	471.7	390.3
97.5°	1130.2	975.3
100°	1628.4	1443.8
102.5°	2118.4	1960.4
105°	2743.2	2658.3
107.5°	3152.5	3173.1
110°	3308.5	3397.1



TEST NUMBER: P937209
CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3322.5	3458.4
115°	3234.3	3422.9
117.5°	3047.5	3256.6
120°	2897.1	3100.1
122.5°	2750.4	2950.8
125°	2541.3	2725.8
127.5°	2353.3	2508.9
130°	2242.4	2386.3
132.5°	2141.8	2270.7
135°	2004.1	2115.1
137.5°	1893.5	1984.4
140°	1817.6	1902.5
142.5°	1754.8	1827.9
145°	1660.6	1715.8
147.5°	1588.2	1634.1
150°	1542.7	1579.9
152.5°	1503.8	1531.8
155°	1459.0	1477.6
157.5°	1423.7	1436.7
160°	1402.5	1410.0
162.5°	1388.7	1395.9
165°	1368.7	1376.3
167.5°	1354.5	1357.6
170°	1350.4	1350.4
172.5°	1339.9	1337.2
175°	1333.6	1333.6
177.5°	1327.9	1324.7
180°	1324.7	1324.7



TEST NUMBER: P937209
 CATALOG NUMBER: SQ4-FB-075U-100D-830-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.64	6.56	6.58	7.51	8.76	18.83	19.75	19.77	20.71	21.95
	3H	6.35	7.17	7.30	8.14	9.41	20.68	21.50	21.63	22.47	23.74
	4H	6.65	7.43	7.61	8.40	9.68	21.33	22.11	22.29	23.08	24.36
	6H	6.90	7.62	7.88	8.60	9.89	21.77	22.49	22.74	23.47	24.76
	8H	6.97	7.66	7.95	8.65	9.94	21.90	22.58	22.87	23.58	24.86
	12H	6.99	7.65	7.98	8.63	9.95	21.97	22.62	22.95	23.61	24.92
4H	2H	12.87	13.65	13.84	14.62	15.90	19.11	19.89	20.08	20.86	22.14
	3H	14.44	15.10	15.42	16.10	17.39	21.17	21.82	22.15	22.82	24.12
	4H	14.54	15.14	15.53	16.13	17.45	21.94	22.54	22.93	23.53	24.85
	6H	14.55	15.07	15.55	16.09	17.40	22.49	23.00	23.49	24.02	25.34
	8H	14.53	15.01	15.53	16.03	17.35	22.65	23.14	23.66	24.15	25.48
	12H	14.49	14.93	15.51	15.95	17.29	22.75	23.19	23.77	24.22	25.55
8H	4H	15.99	16.48	16.99	17.49	18.82	22.01	22.49	23.01	23.50	24.83
	6H	16.24	16.64	17.26	17.69	19.02	22.64	23.04	23.67	24.10	25.42
	8H	16.26	16.61	17.29	17.65	18.99	22.87	23.22	23.90	24.26	25.60
	12H	16.23	16.54	17.27	17.57	18.96	23.02	23.33	24.05	24.36	25.75
12H	4H	16.14	16.58	17.16	17.60	18.94	21.96	22.40	22.98	23.43	24.76
	6H	16.50	16.85	17.53	17.89	19.24	22.63	22.98	23.66	24.02	25.36
	8H	16.57	16.88	17.61	17.92	19.30	22.86	23.17	23.90	24.21	25.60