

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563803

Luminaire Tested: **SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563803
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13936.7 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 112.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563803
CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P563803

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	34	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	73	62	54	49	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	67	55	47	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18
6	61	50	42	36	56	45	38	33	38	32	28	30	26	24	23	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	27	24	21	21	19	17	14
8	52	40	33	28	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12989	12989	12989
5°	13085	13004	12959
10°	13062	12970	12912
15°	12976	12905	12834
20°	12890	12817	12720
25°	12737	12649	12523
30°	12501	12435	12278
35°	12174	12091	11937
40°	11785	11710	11577
45°	11463	11382	11270
50°	11051	10980	10874
55°	10479	10341	10261
60°	9540	9267	9221
65°	8405	8054	8027
70°	7256	6956	6956
75°	6245	6157	6070
80°	5508	5572	5441
85°	4312	4700	4700



TEST NUMBER: P563803

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.7	1.4
10°-20°	570.2	4.1
20°-30°	854.1	6.1
30°-40°	1001.8	7.2
40°-50°	1004.9	7.2
50°-60°	857.2	6.2
60°-70°	559.1	4.0
70°-80°	280.5	2.0
80°-90°	80.4	0.6
90°-100°	614.8	4.4
100°-110°	1662.2	11.9
110°-120°	1747.6	12.5
120°-130°	1419.5	10.2
130°-140°	1113.5	8.0
140°-150°	854.6	6.1
150°-160°	614.6	4.4
160°-170°	375.5	2.7
170°-180°	126.6	0.9
0°-30°	1623.9	11.7
0°-40°	2625.7	18.8
0°-60°	4487.8	32.2
0°-90°	5407.7	38.8
90°-120°	4024.6	28.9
90°-150°	7412.3	53.2
90°-180°	8529.0	61.2
0°-180°	13936.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2112	2112	2112	2112	2112	
5°	2119	2099	2106	2099	2099	201
15°	2038	2018	2027	2019	2016	575
25°	1877	1855	1864	1847	1845	863
35°	1621	1605	1610	1592	1590	1013
45°	1318	1309	1308	1296	1296	1015
55°	977	974	964	959	957	868
65°	578	567	553	550	552	576
75°	263	263	259	257	255	285
85°	61	66	67	67	67	72
90°	3	8	18	20	18	9
95°	95	335	1022	529	315	100
105°	309	478	1844	2720	2609	325
115°	544	665	1529	2960	3342	537
125°	745	853	1378	2326	2733	664
135°	893	999	1341	1878	2126	690
145°	1038	1116	1323	1608	1730	649
155°	1172	1218	1312	1442	1490	541
165°	1276	1288	1317	1369	1376	359
175°	1324	1323	1319	1336	1333	126
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P563803

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2111.8	2111.8	2111.8	2111.8	2111.8
2.5°	2125.1	2107.7	2111.8	2108.6	2099.9
5°	2119.2	2099.3	2106.2	2098.8	2098.8
7.5°	2104.7	2083.0	2089.9	2082.5	2082.2
10°	2091.4	2069.7	2076.6	2069.2	2067.4
12.5°	2072.2	2050.4	2058.8	2049.9	2049.6
15°	2037.7	2017.8	2026.6	2019.1	2015.5
17.5°	1998.9	1977.2	1987.8	1977.4	1975.9
20°	1969.3	1947.5	1958.2	1943.3	1943.3
22.5°	1933.7	1912.0	1924.1	1904.9	1904.9
25°	1876.7	1855.0	1863.8	1847.1	1845.3
27.5°	1809.0	1787.6	1796.8	1777.9	1777.5
30°	1760.1	1740.2	1750.9	1730.5	1728.7
32.5°	1706.8	1688.4	1696.1	1675.7	1673.9
35°	1621.3	1605.0	1610.2	1591.7	1589.8
37.5°	1531.4	1514.7	1520.6	1504.7	1504.0
40°	1467.7	1456.8	1458.4	1445.4	1441.8
42.5°	1408.5	1396.2	1397.7	1384.8	1384.0
45°	1317.8	1308.7	1308.5	1295.6	1295.6
47.5°	1221.5	1214.7	1212.6	1201.9	1201.5
50°	1154.9	1149.5	1147.5	1138.2	1136.4
52.5°	1085.3	1082.8	1076.4	1068.6	1068.3
55°	977.2	973.6	964.3	958.7	956.9
57.5°	859.9	852.6	842.1	834.0	835.5
60°	775.5	768.2	753.3	749.6	749.6
62.5°	694.1	685.4	670.4	665.2	668.1
65°	577.5	566.6	553.4	549.7	551.5
67.5°	471.6	461.8	447.5	447.5	446.0
70°	403.5	398.0	386.8	386.8	386.8
72.5°	342.8	340.2	332.0	332.0	330.6
75°	262.8	262.8	259.1	257.2	255.4
77.5°	196.9	197.6	195.8	193.9	190.6
80°	155.5	159.1	157.3	155.4	153.6
82.5°	117.0	120.6	120.3	117.0	116.6
85°	61.1	66.5	66.6	66.6	66.6
87.5°	16.9	23.8	27.4	27.7	28.9
90°	2.8	8.4	18.5	19.9	18.5
92.5°	40.4	147.4	290.8	126.2	91.4
95°	95.4	334.9	1022.4	529.1	314.7
97.5°	153.2	384.1	1593.7	1318.9	968.6
100°	196.5	404.0	1771.4	1847.4	1493.7
102.5°	236.4	431.6	1834.1	2248.1	1983.6
105°	309.0	477.5	1844.0	2720.1	2608.7
107.5°	376.2	529.9	1763.4	3014.5	3051.5
110°	428.6	567.8	1691.7	3093.6	3250.9



TEST NUMBER: P563803

CATALOG NUMBER: SQ4-PP3-150U-100D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.3	605.6	1625.6	3077.8	3342.0
115°	544.0	665.1	1529.3	2960.5	3342.0
117.5°	611.2	724.8	1465.8	2781.4	3213.9
120°	652.2	763.6	1428.2	2652.9	3094.3
122.5°	690.9	800.1	1405.4	2515.1	2959.8
125°	744.7	853.3	1378.4	2326.0	2732.6
127.5°	794.3	900.9	1362.4	2171.7	2529.2
130°	821.6	931.6	1355.6	2076.4	2399.4
132.5°	850.1	959.0	1348.8	1990.3	2287.7
135°	892.8	998.6	1341.4	1878.1	2126.0
137.5°	935.8	1035.8	1335.1	1787.1	1989.0
140°	965.4	1058.7	1332.8	1728.5	1908.1
142.5°	993.9	1081.6	1328.3	1675.6	1832.9
145°	1038.1	1116.0	1322.9	1607.6	1730.1
147.5°	1078.2	1147.3	1316.6	1546.0	1640.1
150°	1107.8	1169.1	1314.3	1512.5	1587.7
152.5°	1135.2	1188.6	1313.2	1481.5	1543.3
155°	1171.9	1217.9	1311.5	1442.1	1489.5
157.5°	1210.1	1242.1	1311.7	1414.7	1445.9
160°	1231.7	1258.2	1312.9	1397.4	1419.7
162.5°	1248.8	1270.8	1314.0	1383.6	1400.3
165°	1275.9	1288.4	1317.2	1368.6	1375.5
167.5°	1294.4	1303.0	1317.4	1355.7	1359.0
170°	1305.8	1309.9	1318.6	1349.9	1349.9
172.5°	1314.9	1315.7	1318.6	1343.1	1341.9
175°	1324.3	1322.9	1318.6	1335.6	1332.8
177.5°	1327.4	1324.1	1318.3	1329.6	1326.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)