

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563177

Luminaire Tested: **SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563177
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8257.3 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 68.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563177

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563177

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	102	98	94	90	96	92	89	86	82	79	77	72	71	69	64	62	61	57				
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48				
3	85	75	68	62	80	71	65	59	64	58	54	57	53	49	50	47	44	41				
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35				
5	72	60	51	45	67	57	49	44	51	45	40	46	41	37	41	37	33	31				
6	66	54	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27				
7	61	49	40	35	57	46	39	34	42	36	31	38	32	29	34	29	26	24				
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	24	21				
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19				
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6633	6633	6633
5°	6681	6640	6617
10°	6670	6623	6593
15°	6626	6590	6554
20°	6582	6545	6495
25°	6504	6459	6395
30°	6383	6350	6269
35°	6216	6174	6096
40°	6018	5980	5911
45°	5853	5812	5755
50°	5643	5607	5553
55°	5351	5280	5240
60°	4871	4732	4708
65°	4291	4113	4099
70°	3706	3552	3552
75°	3189	3144	3099
80°	2812	2846	2779
85°	2202	2399	2399



TEST NUMBER: P563177

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.9	2.5
10°-20°	582.3	7.1
20°-30°	872.2	10.6
30°-40°	1023.1	12.4
40°-50°	1026.2	12.4
50°-60°	875.5	10.6
60°-70°	570.9	6.9
70°-80°	286.5	3.5
80°-90°	81.5	1.0
90°-100°	205.7	2.5
100°-110°	540.7	6.5
110°-120°	560.7	6.8
120°-130°	449.7	5.4
130°-140°	352.9	4.3
140°-150°	270.8	3.3
150°-160°	195.1	2.4
160°-170°	119.3	1.4
170°-180°	40.3	0.5
0°-30°	1658.4	20.1
0°-40°	2681.5	32.5
0°-60°	4583.2	55.5
0°-90°	5522.2	66.9
90°-120°	1307.0	15.8
90°-150°	2380.4	28.8
90°-180°	2735.0	33.1
0°-180°	8257.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2157	2157	2157	2157	2157	
5°	2164	2144	2151	2143	2143	206
15°	2081	2061	2070	2062	2058	587
25°	1917	1894	1903	1886	1884	881
35°	1656	1639	1644	1626	1624	1034
45°	1346	1337	1336	1323	1323	1036
55°	998	994	985	979	977	887
65°	590	579	565	561	563	589
75°	268	268	265	263	261	291
85°	62	68	68	68	68	73
90°	3	8	22	11	11	5
95°	27	106	354	183	124	30
105°	97	148	598	908	847	103
115°	173	210	479	955	1090	171
125°	241	270	436	736	868	214
135°	287	316	422	594	674	222
145°	333	354	417	507	546	208
155°	376	387	417	458	471	173
165°	406	411	417	433	438	115
175°	422	422	419	425	425	40
180°	422	422	422	422	422	

TEST NUMBER: P563177

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2156.7	2156.7	2156.7	2156.7	2156.7
2.5°	2170.3	2152.5	2156.7	2153.5	2144.6
5°	2164.2	2143.9	2151.0	2143.4	2143.4
7.5°	2149.5	2127.3	2134.4	2126.8	2126.4
10°	2135.9	2113.7	2120.8	2113.2	2111.3
12.5°	2116.2	2094.1	2102.6	2093.5	2093.2
15°	2081.1	2060.7	2069.7	2062.1	2058.4
17.5°	2041.4	2019.2	2030.0	2019.4	2017.9
20°	2011.1	1989.0	1999.8	1984.7	1984.7
22.5°	1974.8	1952.7	1965.0	1945.4	1945.4
25°	1916.6	1894.5	1903.4	1886.3	1884.5
27.5°	1847.4	1825.6	1835.0	1815.7	1815.3
30°	1797.5	1777.2	1788.1	1767.3	1765.4
32.5°	1743.1	1724.3	1732.1	1711.3	1709.5
35°	1655.8	1639.2	1644.4	1625.5	1623.7
37.5°	1563.9	1546.9	1553.0	1536.7	1535.9
40°	1498.9	1487.8	1489.5	1476.1	1472.4
42.5°	1438.4	1425.8	1427.5	1414.2	1413.5
45°	1345.8	1336.6	1336.3	1323.1	1323.1
47.5°	1247.5	1240.5	1238.4	1227.5	1227.1
50°	1179.5	1173.9	1171.9	1162.4	1160.6
52.5°	1108.4	1105.8	1099.3	1091.4	1091.0
55°	998.0	994.3	984.8	979.1	977.2
57.5°	878.2	870.8	860.0	851.7	853.2
60°	792.0	784.6	769.3	765.5	765.5
62.5°	708.8	699.9	684.6	679.4	682.4
65°	589.7	578.6	565.2	561.4	563.3
67.5°	481.6	471.6	457.0	457.0	455.5
70°	412.1	406.5	395.0	395.0	395.0
72.5°	350.1	347.5	339.1	339.1	337.6
75°	268.4	268.4	264.6	262.7	260.8
77.5°	201.1	201.9	200.0	198.0	194.7
80°	158.8	162.5	160.7	158.7	156.9
82.5°	119.5	123.2	122.9	119.5	119.1
85°	62.4	67.9	68.0	68.0	68.0
87.5°	17.2	24.1	28.5	26.4	27.9
90°	2.7	8.0	21.6	10.8	10.8
92.5°	11.4	54.7	121.2	53.7	34.6
95°	27.1	106.4	354.4	182.6	124.4
97.5°	47.1	116.9	530.2	421.6	310.5
100°	62.2	125.7	584.3	592.1	459.9
102.5°	75.2	134.4	599.4	737.5	624.3
105°	97.4	147.6	597.8	907.5	846.7
107.5°	120.1	166.7	563.7	995.8	1010.6
110°	135.3	177.6	535.6	1018.5	1082.0

TEST NUMBER: P563177

CATALOG NUMBER: SQ4-PP3-025U-050D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	150.4	190.6	509.6	1004.2	1101.5
115°	173.1	210.2	478.8	955.2	1090.1
117.5°	195.3	229.2	457.7	887.4	1037.1
120°	208.3	240.0	449.0	841.9	987.3
122.5°	221.3	253.0	442.5	796.4	939.7
125°	240.8	269.8	435.5	736.1	868.3
127.5°	256.4	286.1	429.6	687.5	799.1
130°	265.1	296.8	427.4	657.0	760.1
132.5°	273.8	305.5	425.2	630.8	723.3
135°	286.7	315.8	422.0	594.2	673.6
137.5°	300.3	328.8	421.4	566.8	631.9
140°	311.1	337.5	419.3	545.1	605.9
142.5°	319.7	344.1	419.3	529.8	582.1
145°	332.7	353.9	416.6	506.7	546.4
147.5°	345.7	366.3	416.6	487.7	520.5
150°	354.4	372.9	416.6	476.7	503.1
152.5°	363.0	377.3	416.6	467.9	488.0
155°	376.0	386.6	416.6	457.5	470.7
157.5°	385.7	395.8	416.6	448.2	457.7
160°	392.2	400.2	416.6	443.8	449.0
162.5°	398.7	404.5	416.6	439.4	444.7
165°	405.8	411.0	416.6	432.9	438.2
167.5°	412.3	414.9	419.3	430.2	432.3
170°	416.6	419.2	419.3	430.1	430.1
172.5°	418.7	419.3	419.3	427.9	425.8
175°	422.0	422.0	419.3	424.7	424.7
177.5°	422.0	422.0	419.8	424.1	422.0
180°	422.0	422.0	422.0	422.0	422.0

(END OF REPORT)