

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564019

Luminaire Tested: **SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564019
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9678.6 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 87.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564019
CATALOG NUMBER: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P564019

CATALOG NUMBER: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	75	75	75	71	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	64	64	64	60	
2	94	87	80	75	89	82	77	72	74	70	66	67	63	60	60	57	55	55	55	55	51	
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	47	47	47	44	
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	33	
6	67	55	47	41	63	52	45	39	48	41	37	43	38	34	39	35	32	32	32	32	29	
7	62	50	42	36	59	48	40	35	43	37	33	40	34	30	36	32	28	28	28	28	26	
8	58	45	37	32	55	43	36	31	40	34	29	36	31	27	33	29	25	25	25	25	23	
9	54	41	34	29	51	40	33	28	37	30	26	33	28	25	31	26	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16870	16870	16870
5°	17023	16891	16803
10°	16968	16850	16762
15°	16894	16789	16698
20°	16809	16700	16577
25°	16690	16578	16386
30°	16510	16393	16158
35°	16267	16125	15894
40°	15896	15725	15440
45°	15248	14981	14673
50°	14107	13767	13496
55°	12312	12034	11780
60°	10375	10288	10085
65°	8974	9009	8939
70°	8242	8285	8285
75°	7916	7916	7973
80°	7449	7531	7449
85°	5999	6669	6669



TEST NUMBER: P564019

CATALOG NUMBER: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.4	2.7
10°-20°	742.1	7.7
20°-30°	1119.3	11.6
30°-40°	1333.6	13.8
40°-50°	1314.9	13.6
50°-60°	1004.9	10.4
60°-70°	621.9	6.4
70°-80°	353.2	3.6
80°-90°	109.1	1.1
90°-100°	207.4	2.1
100°-110°	563.3	5.8
110°-120°	579.1	6.0
120°-130°	463.0	4.8
130°-140°	363.8	3.8
140°-150°	279.0	2.9
150°-160°	200.6	2.1
160°-170°	122.7	1.3
170°-180°	41.3	0.4
0°-30°	2120.8	21.9
0°-40°	3454.4	35.7
0°-60°	5774.2	59.7
0°-90°	6858.3	70.9
90°-120°	1349.8	13.9
90°-150°	2455.6	25.4
90°-180°	2820.0	29.1
0°-180°	9678.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2743	2743	2743	2743	2743	
5°	2757	2727	2736	2726	2722	262
15°	2653	2625	2636	2627	2622	749
25°	2459	2429	2443	2417	2414	1132
35°	2166	2141	2148	2119	2117	1352
45°	1753	1730	1722	1691	1687	1343
55°	1148	1130	1122	1103	1098	1029
65°	617	612	619	614	614	625
75°	333	333	333	336	336	352
85°	85	90	94	94	94	99
90°	1	6	10	12	12	5
95°	31	113	361	157	106	32
105°	100	156	619	943	888	106
115°	178	216	496	986	1124	175
125°	244	278	449	756	892	218
135°	294	327	436	616	694	228
145°	340	365	430	523	562	214
155°	385	398	428	470	483	177
165°	417	422	429	447	449	118
175°	432	433	430	436	435	41
180°	432	432	432	432	432	

TEST NUMBER: P564019

CATALOG NUMBER: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2742.8	2742.8	2742.8	2742.8	2742.8
2.5°	2759.8	2735.8	2742.8	2736.8	2723.9
5°	2757.0	2726.9	2735.7	2726.1	2721.5
7.5°	2735.7	2706.1	2714.9	2705.4	2702.6
10°	2716.8	2689.1	2697.9	2688.3	2683.7
12.5°	2696.0	2666.4	2677.1	2665.7	2661.0
15°	2653.0	2625.3	2636.5	2626.9	2622.3
17.5°	2605.8	2576.2	2587.3	2576.3	2570.3
20°	2568.0	2540.2	2551.4	2534.8	2532.5
22.5°	2526.4	2498.7	2509.8	2487.6	2487.2
25°	2459.3	2429.3	2442.8	2416.7	2414.4
27.5°	2379.4	2351.7	2362.9	2336.4	2333.6
30°	2324.6	2296.9	2308.1	2279.6	2275.0
32.5°	2262.3	2236.4	2245.7	2217.3	2214.5
35°	2166.4	2140.9	2147.5	2119.0	2116.7
37.5°	2057.2	2034.1	2037.8	2006.6	2004.3
40°	1979.7	1956.6	1958.5	1925.3	1923.0
42.5°	1894.7	1871.6	1869.6	1836.5	1834.2
45°	1752.9	1729.8	1722.2	1691.4	1686.8
47.5°	1591.3	1568.2	1554.0	1528.9	1525.7
50°	1474.2	1451.1	1438.7	1417.3	1410.4
52.5°	1347.5	1324.4	1314.0	1294.5	1287.5
55°	1148.1	1129.7	1122.2	1103.2	1098.5
57.5°	958.7	946.2	944.0	925.6	923.7
60°	843.4	836.5	836.3	819.8	819.8
62.5°	745.1	740.0	743.7	732.8	730.9
65°	616.6	612.0	619.0	614.2	614.2
67.5°	515.0	515.0	519.3	517.4	517.4
70°	458.3	458.3	460.7	460.7	460.7
72.5°	407.3	405.4	411.5	411.5	409.6
75°	333.1	333.1	333.1	335.5	335.5
77.5°	259.4	259.9	261.8	261.2	259.4
80°	210.3	212.6	212.6	210.3	210.3
82.5°	161.1	163.4	163.5	163.0	161.1
85°	85.0	89.7	94.5	94.5	94.5
87.5°	24.8	33.1	39.7	40.3	38.4
90°	1.4	5.5	9.7	12.5	12.5
92.5°	12.5	56.8	98.6	42.4	35.8
95°	30.6	113.4	361.1	157.2	105.6
97.5°	50.6	125.2	553.6	430.7	302.5
100°	63.9	133.1	612.5	620.9	501.4
102.5°	77.2	141.0	628.0	767.9	662.5
105°	100.0	155.7	619.4	943.2	887.5
107.5°	123.6	172.8	583.6	1033.7	1049.1
110°	140.3	185.1	556.9	1051.5	1118.0

TEST NUMBER: P564019

CATALOG NUMBER: SQ4-PR1-050U-125D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	154.7	197.4	530.3	1036.7	1136.9
115°	177.8	215.8	495.8	986.4	1123.6
117.5°	199.4	235.8	473.9	915.2	1069.7
120°	213.9	249.2	463.9	867.4	1020.8
122.5°	226.1	261.4	457.2	819.5	967.5
125°	244.4	278.4	448.6	755.8	891.6
127.5°	260.8	294.5	443.9	707.6	824.2
130°	270.8	303.4	441.7	677.4	781.9
132.5°	280.8	313.4	439.4	651.5	744.2
135°	294.4	327.0	436.1	615.7	694.4
137.5°	309.2	338.8	434.4	584.0	650.3
140°	318.0	346.6	433.3	563.8	623.6
142.5°	326.9	353.3	432.2	548.1	598.0
145°	340.3	364.7	430.5	523.1	562.5
147.5°	355.3	376.2	429.2	503.5	534.4
150°	365.3	382.9	429.2	492.2	516.7
152.5°	373.0	388.5	428.0	482.1	502.2
155°	384.7	398.3	427.8	469.7	483.3
157.5°	396.1	406.7	427.8	461.3	471.7
160°	402.8	412.3	427.8	455.7	463.9
162.5°	409.4	416.8	428.9	451.2	457.2
165°	416.7	422.1	429.2	447.2	448.6
167.5°	424.2	426.9	430.5	442.5	443.6
170°	426.4	429.1	430.5	440.3	440.3
172.5°	428.6	430.2	430.5	438.0	438.0
175°	431.9	433.3	430.5	436.1	434.7
177.5°	433.0	433.0	429.7	434.1	431.9
180°	431.9	431.9	431.9	431.9	431.9

(END OF REPORT)