

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563201

Luminaire Tested: **SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563201
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10873.1 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 94.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563201
CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563201

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75																												
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64																												
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54																												
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46																												
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39																												
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34																												
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30																												
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27																												
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24																												
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22																												
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20																												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9776	9776	9776
5°	9847	9787	9753
10°	9831	9761	9718
15°	9766	9712	9659
20°	9701	9646	9574
25°	9586	9520	9425
30°	9408	9359	9240
35°	9162	9099	8985
40°	8869	8813	8713
45°	8627	8566	8482
50°	8317	8264	8184
55°	7887	7782	7723
60°	7180	6974	6940
65°	6325	6062	6041
70°	5461	5236	5236
75°	4701	4634	4569
80°	4144	4194	4095
85°	3243	3539	3539



TEST NUMBER: P563201

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	300.6	2.8
10°-20°	858.2	7.9
20°-30°	1285.5	11.8
30°-40°	1507.9	13.9
40°-50°	1512.6	13.9
50°-60°	1290.3	11.9
60°-70°	841.5	7.7
70°-80°	422.2	3.9
80°-90°	119.1	1.1
90°-100°	205.7	1.9
100°-110°	540.7	5.0
110°-120°	560.7	5.2
120°-130°	449.7	4.1
130°-140°	352.9	3.2
140°-150°	270.8	2.5
150°-160°	195.1	1.8
160°-170°	119.3	1.1
170°-180°	40.3	0.4
0°-30°	2444.4	22.5
0°-40°	3952.2	36.3
0°-60°	6755.1	62.1
0°-90°	8138.0	74.8
90°-120°	1307.0	12.0
90°-150°	2380.4	21.9
90°-180°	2735.0	25.2
0°-180°	10873.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3179	3179	3179	3179	3179	
5°	3190	3160	3170	3159	3159	303
15°	3067	3037	3050	3039	3034	865
25°	2825	2792	2805	2780	2778	1299
35°	2440	2416	2424	2396	2393	1524
45°	1984	1970	1970	1950	1950	1527
55°	1471	1466	1451	1443	1440	1307
65°	869	853	833	828	830	867
75°	396	396	390	387	384	429
85°	92	100	100	100	100	108
90°	3	8	22	11	11	6
95°	27	106	354	183	124	30
105°	97	148	598	908	847	103
115°	173	210	479	955	1090	171
125°	241	270	436	736	868	214
135°	287	316	422	594	674	222
145°	333	354	417	507	546	208
155°	376	387	417	458	471	173
165°	406	411	417	433	438	115
175°	422	422	419	425	425	40
180°	422	422	422	422	422	



TEST NUMBER: P563201

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3178.7	3178.7	3178.7	3178.7	3178.7
2.5°	3198.8	3172.6	3178.7	3173.9	3160.9
5°	3189.8	3159.9	3170.3	3159.2	3159.2
7.5°	3168.1	3135.4	3145.8	3134.7	3134.1
10°	3148.1	3115.4	3125.8	3114.6	3111.8
12.5°	3119.1	3086.4	3099.0	3085.6	3085.1
15°	3067.3	3037.3	3050.5	3039.3	3033.8
17.5°	3008.8	2976.1	2992.0	2976.4	2974.2
20°	2964.2	2931.5	2947.5	2925.2	2925.2
22.5°	2910.7	2878.0	2896.2	2867.2	2867.2
25°	2824.9	2792.2	2805.4	2780.3	2777.5
27.5°	2722.9	2690.8	2704.5	2676.1	2675.6
30°	2649.4	2619.4	2635.4	2604.7	2602.0
32.5°	2569.1	2541.4	2553.0	2522.3	2519.6
35°	2440.4	2415.9	2423.7	2395.8	2393.1
37.5°	2305.0	2280.0	2288.9	2264.9	2263.8
40°	2209.2	2192.9	2195.3	2175.7	2170.2
42.5°	2120.1	2101.5	2103.9	2084.4	2083.3
45°	1983.6	1969.9	1969.6	1950.1	1950.1
47.5°	1838.7	1828.3	1825.3	1809.1	1808.6
50°	1738.4	1730.2	1727.2	1713.3	1710.5
52.5°	1633.6	1629.8	1620.3	1608.6	1608.0
55°	1470.9	1465.5	1451.4	1443.0	1440.3
57.5°	1294.3	1283.4	1267.6	1255.4	1257.5
60°	1167.3	1156.4	1133.9	1128.3	1128.3
62.5°	1044.7	1031.6	1009.0	1001.3	1005.7
65°	869.2	852.9	833.0	827.5	830.2
67.5°	709.8	695.1	673.6	673.6	671.4
70°	607.3	599.2	582.3	582.3	582.3
72.5°	515.9	512.1	499.8	499.7	497.6
75°	395.6	395.6	390.0	387.2	384.5
77.5°	296.4	297.5	294.7	291.8	286.9
80°	234.0	239.5	236.8	234.0	231.2
82.5°	176.1	181.5	181.1	176.1	175.5
85°	91.9	100.1	100.3	100.3	100.3
87.5°	25.1	34.8	40.0	37.9	40.1
90°	2.7	8.0	21.6	10.8	10.8
92.5°	11.4	54.7	121.2	53.7	34.6
95°	27.1	106.4	354.4	182.6	124.4
97.5°	47.1	116.9	530.2	421.6	310.5
100°	62.2	125.7	584.3	592.1	459.9
102.5°	75.2	134.4	599.4	737.5	624.3
105°	97.4	147.6	597.8	907.5	846.7
107.5°	120.1	166.7	563.7	995.8	1010.6
110°	135.3	177.6	535.6	1018.5	1082.0

TEST NUMBER: P563201

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	150.4	190.6	509.6	1004.2	1101.5
115°	173.1	210.2	478.8	955.2	1090.1
117.5°	195.3	229.2	457.7	887.4	1037.1
120°	208.3	240.0	449.0	841.9	987.3
122.5°	221.3	253.0	442.5	796.4	939.7
125°	240.8	269.8	435.5	736.1	868.3
127.5°	256.4	286.1	429.6	687.5	799.1
130°	265.1	296.8	427.4	657.0	760.1
132.5°	273.8	305.5	425.2	630.8	723.3
135°	286.7	315.8	422.0	594.2	673.6
137.5°	300.3	328.8	421.4	566.8	631.9
140°	311.1	337.5	419.3	545.1	605.9
142.5°	319.7	344.1	419.3	529.8	582.1
145°	332.7	353.9	416.6	506.7	546.4
147.5°	345.7	366.3	416.6	487.7	520.5
150°	354.4	372.9	416.6	476.7	503.1
152.5°	363.0	377.3	416.6	467.9	488.0
155°	376.0	386.6	416.6	457.5	470.7
157.5°	385.7	395.8	416.6	448.2	457.7
160°	392.2	400.2	416.6	443.8	449.0
162.5°	398.7	404.5	416.6	439.4	444.7
165°	405.8	411.0	416.6	432.9	438.2
167.5°	412.3	414.9	419.3	430.2	432.3
170°	416.6	419.2	419.3	430.1	430.1
172.5°	418.7	419.3	419.3	427.9	425.8
175°	422.0	422.0	419.3	424.7	424.7
177.5°	422.0	422.0	419.8	424.1	422.0
180°	422.0	422.0	422.0	422.0	422.0

(END OF REPORT)