

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563537

Luminaire Tested: **SQ4-PP3-0U-125D-830-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563537
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13794.9 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Direct

Input Watts (W): 140.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563537
CATALOG NUMBER: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P563537

CATALOG NUMBER: SQ4-PP3-OU-125D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16576	16576	16576
5°	16697	16595	16537
10°	16669	16551	16477
15°	16559	16469	16379
20°	16449	16356	16233
25°	16254	16141	15981
30°	15953	15869	15668
35°	15536	15429	15234
40°	15038	14944	14773
45°	14628	14525	14381
50°	14103	14012	13877
55°	13373	13196	13095
60°	12174	11826	11767
65°	10725	10278	10244
70°	9260	8878	8878
75°	7971	7858	7746
80°	7028	7111	6944
85°	5501	6002	6002



TEST NUMBER: P563537

CATALOG NUMBER: SQ4-PP3-0U-125D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	509.7	3.7
10°-20°	1455.2	10.5
20°-30°	2179.8	15.8
30°-40°	2556.7	18.5
40°-50°	2564.7	18.6
50°-60°	2187.9	15.9
60°-70°	1426.9	10.3
70°-80°	715.9	5.2
80°-90°	198.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4144.7	30.0
0°-40°	6701.4	48.6
0°-60°	11454.0	83.0
0°-90°	13794.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13794.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5390	5390	5390	5390	5390	
5°	5409	5358	5376	5357	5357	514
15°	5201	5150	5172	5153	5144	1467
25°	4790	4734	4757	4714	4710	2203
35°	4138	4096	4110	4062	4058	2585
45°	3363	3340	3340	3307	3307	2590
55°	2494	2485	2461	2447	2442	2217
65°	1474	1446	1412	1403	1408	1471
75°	671	671	661	656	652	728
85°	156	170	170	170	170	189
90°	0	0	0	0	0	



TEST NUMBER: P563537

CATALOG NUMBER: SQ4-PP3-OU-125D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5389.8	5389.8	5389.8	5389.8	5389.8
2.5°	5423.8	5379.5	5389.8	5381.7	5359.6
5°	5408.7	5357.9	5375.6	5356.7	5356.7
7.5°	5371.9	5316.4	5334.1	5315.1	5314.2
10°	5337.8	5282.4	5300.1	5281.1	5276.4
12.5°	5288.7	5233.3	5254.7	5232.0	5231.1
15°	5200.9	5150.0	5172.5	5153.4	5144.2
17.5°	5101.7	5046.2	5073.3	5046.8	5043.1
20°	5026.1	4970.7	4997.7	4959.9	4959.9
22.5°	4935.4	4880.0	4910.8	4861.7	4861.7
25°	4789.9	4734.5	4756.8	4714.2	4709.6
27.5°	4617.0	4562.5	4585.8	4537.6	4536.7
30°	4492.3	4441.5	4468.7	4416.6	4412.0
32.5°	4356.2	4309.1	4328.8	4276.8	4272.2
35°	4138.0	4096.4	4109.7	4062.3	4057.7
37.5°	3908.4	3865.9	3881.0	3840.4	3838.5
40°	3745.9	3718.2	3722.3	3689.0	3679.8
42.5°	3594.8	3563.4	3567.4	3534.3	3532.4
45°	3363.3	3340.2	3339.7	3306.6	3306.6
47.5°	3117.7	3100.1	3095.0	3067.6	3066.7
50°	2947.6	2933.8	2928.7	2905.0	2900.4
52.5°	2770.0	2763.5	2747.3	2727.5	2726.6
55°	2494.1	2484.9	2461.1	2446.8	2442.2
57.5°	2194.7	2176.2	2149.3	2128.6	2132.3
60°	1979.3	1960.8	1922.6	1913.1	1913.1
62.5°	1771.4	1749.2	1710.9	1697.9	1705.3
65°	1473.8	1446.1	1412.4	1403.1	1407.7
67.5°	1203.6	1178.7	1142.2	1142.1	1138.4
70°	1029.8	1015.9	987.3	987.3	987.3
72.5°	874.8	868.4	847.4	847.4	843.7
75°	670.8	670.8	661.3	656.5	651.9
77.5°	502.6	504.5	499.8	494.9	486.5
80°	396.8	406.0	401.5	396.7	392.1
82.5°	298.5	307.8	307.0	298.5	297.6
85°	155.9	169.7	170.1	170.1	170.1
87.5°	41.6	56.3	60.5	60.5	64.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)