

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P564499

Luminaire Tested: **SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564499  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 15388.4 lumens  
Efficiency: N/A  
Efficacy: 121.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 127.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564499  
CATALOG NUMBER: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P564499

CATALOG NUMBER: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	81	75	69	65	62	59	55	51	48	46	40	39	37	32
3	81	72	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	63	56	50	68	58	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18
7	58	46	38	33	53	42	35	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16870	16870	16870
5°	17023	16891	16803
10°	16968	16850	16762
15°	16894	16789	16698
20°	16809	16700	16577
25°	16690	16578	16386
30°	16510	16393	16158
35°	16267	16125	15894
40°	15896	15725	15440
45°	15248	14981	14673
50°	14107	13767	13496
55°	12312	12034	11780
60°	10375	10288	10085
65°	8974	9009	8939
70°	8242	8285	8285
75°	7916	7916	7973
80°	7449	7531	7449
85°	5999	6669	6669



TEST NUMBER: P564499

CATALOG NUMBER: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	259.4	1.7
10°-20°	742.1	4.8
20°-30°	1119.3	7.3
30°-40°	1333.6	8.7
40°-50°	1314.9	8.5
50°-60°	1004.9	6.5
60°-70°	621.9	4.0
70°-80°	353.2	2.3
80°-90°	110.2	0.7
90°-100°	614.8	4.0
100°-110°	1662.2	10.8
110°-120°	1747.6	11.4
120°-130°	1419.5	9.2
130°-140°	1113.5	7.2
140°-150°	854.6	5.6
150°-160°	614.6	4.0
160°-170°	375.5	2.4
170°-180°	126.6	0.8
0°-30°	2120.8	13.8
0°-40°	3454.4	22.4
0°-60°	5774.2	37.5
0°-90°	6859.4	44.6
90°-120°	4024.6	26.2
90°-150°	7412.3	48.2
90°-180°	8529.0	55.4
0°-180°	15388.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2743	2743	2743	2743	2743	
5°	2757	2727	2736	2726	2722	262
15°	2653	2625	2636	2627	2622	749
25°	2459	2429	2443	2417	2414	1132
35°	2166	2141	2148	2119	2117	1352
45°	1753	1730	1722	1691	1687	1343
55°	1148	1130	1122	1103	1098	1029
65°	617	612	619	614	614	625
75°	333	333	333	336	336	352
85°	85	90	94	94	94	99
90°	3	8	18	20	18	10
95°	95	335	1022	529	315	100
105°	309	478	1844	2720	2609	325
115°	544	665	1529	2960	3342	537
125°	745	853	1378	2326	2733	664
135°	893	999	1341	1878	2126	690
145°	1038	1116	1323	1608	1730	649
155°	1172	1218	1312	1442	1490	541
165°	1276	1288	1317	1369	1376	359
175°	1324	1323	1319	1336	1333	126
180°	1323	1323	1323	1323	1323	

TEST NUMBER: P564499

CATALOG NUMBER: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2742.8	2742.8	2742.8	2742.8	2742.8
2.5°	2759.8	2735.8	2742.8	2736.8	2723.9
5°	2757.0	2726.9	2735.7	2726.1	2721.5
7.5°	2735.7	2706.1	2714.9	2705.4	2702.6
10°	2716.8	2689.1	2697.9	2688.3	2683.7
12.5°	2696.0	2666.4	2677.1	2665.7	2661.0
15°	2653.0	2625.3	2636.5	2626.9	2622.3
17.5°	2605.8	2576.2	2587.3	2576.3	2570.3
20°	2568.0	2540.2	2551.4	2534.8	2532.5
22.5°	2526.4	2498.7	2509.8	2487.6	2487.2
25°	2459.3	2429.3	2442.8	2416.7	2414.4
27.5°	2379.4	2351.7	2362.9	2336.4	2333.6
30°	2324.6	2296.9	2308.1	2279.6	2275.0
32.5°	2262.3	2236.4	2245.7	2217.3	2214.5
35°	2166.4	2140.9	2147.5	2119.0	2116.7
37.5°	2057.2	2034.1	2037.8	2006.6	2004.3
40°	1979.7	1956.6	1958.5	1925.3	1923.0
42.5°	1894.7	1871.6	1869.6	1836.5	1834.2
45°	1752.9	1729.8	1722.2	1691.4	1686.8
47.5°	1591.3	1568.2	1554.0	1528.9	1525.7
50°	1474.2	1451.1	1438.7	1417.3	1410.4
52.5°	1347.5	1324.4	1314.0	1294.5	1287.5
55°	1148.1	1129.7	1122.2	1103.2	1098.5
57.5°	958.7	946.2	944.0	925.6	923.7
60°	843.4	836.5	836.3	819.8	819.8
62.5°	745.1	740.0	743.7	732.8	730.9
65°	616.6	612.0	619.0	614.2	614.2
67.5°	515.0	515.0	519.3	517.4	517.4
70°	458.3	458.3	460.7	460.7	460.7
72.5°	407.3	405.4	411.5	411.5	409.6
75°	333.1	333.1	333.1	335.5	335.5
77.5°	259.4	259.9	261.8	261.2	259.4
80°	210.3	212.6	212.6	210.3	210.3
82.5°	161.1	163.4	163.5	163.0	161.1
85°	85.0	89.7	94.5	94.5	94.5
87.5°	25.1	33.6	41.5	41.7	39.6
90°	2.8	8.4	18.5	19.9	18.5
92.5°	40.4	147.4	290.8	126.2	91.4
95°	95.4	334.9	1022.4	529.1	314.7
97.5°	153.2	384.1	1593.7	1318.9	968.6
100°	196.5	404.0	1771.4	1847.4	1493.7
102.5°	236.4	431.6	1834.1	2248.1	1983.6
105°	309.0	477.5	1844.0	2720.1	2608.7
107.5°	376.2	529.9	1763.4	3014.5	3051.5
110°	428.6	567.8	1691.7	3093.6	3250.9



TEST NUMBER: P564499

CATALOG NUMBER: SQ4-PR1-150U-125D-830-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	475.3	605.6	1625.6	3077.8	3342.0
115°	544.0	665.1	1529.3	2960.5	3342.0
117.5°	611.2	724.8	1465.8	2781.4	3213.9
120°	652.2	763.6	1428.2	2652.9	3094.3
122.5°	690.9	800.1	1405.4	2515.1	2959.8
125°	744.7	853.3	1378.4	2326.0	2732.6
127.5°	794.3	900.9	1362.4	2171.7	2529.2
130°	821.6	931.6	1355.6	2076.4	2399.4
132.5°	850.1	959.0	1348.8	1990.3	2287.7
135°	892.8	998.6	1341.4	1878.1	2126.0
137.5°	935.8	1035.8	1335.1	1787.1	1989.0
140°	965.4	1058.7	1332.8	1728.5	1908.1
142.5°	993.9	1081.6	1328.3	1675.6	1832.9
145°	1038.1	1116.0	1322.9	1607.6	1730.1
147.5°	1078.2	1147.3	1316.6	1546.0	1640.1
150°	1107.8	1169.1	1314.3	1512.5	1587.7
152.5°	1135.2	1188.6	1313.2	1481.5	1543.3
155°	1171.9	1217.9	1311.5	1442.1	1489.5
157.5°	1210.1	1242.1	1311.7	1414.7	1445.9
160°	1231.7	1258.2	1312.9	1397.4	1419.7
162.5°	1248.8	1270.8	1314.0	1383.6	1400.3
165°	1275.9	1288.4	1317.2	1368.6	1375.5
167.5°	1294.4	1303.0	1317.4	1355.7	1359.0
170°	1305.8	1309.9	1318.6	1349.9	1349.9
172.5°	1314.9	1315.7	1318.6	1343.1	1341.9
175°	1324.3	1322.9	1318.6	1335.6	1332.8
177.5°	1327.4	1324.1	1318.3	1329.6	1326.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)