

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519189

Luminaire Tested: **SQ4-WB-075U-075D-830-1D-UNV-STD-W-6**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519189
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7770.6 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 68
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519189
CATALOG NUMBER: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P519189

CATALOG NUMBER: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45		
1	98	94	90	87	90	86	83	81	72	70	68	59	58	57	47	47	46	40		
2	90	83	78	73	82	77	72	68	65	61	58	53	51	49	43	42	40	36		
3	83	74	67	62	76	69	63	58	58	54	50	48	45	43	39	37	36	31		
4	76	66	59	54	70	61	55	50	52	48	44	44	40	38	36	34	32	28		
5	70	60	52	47	65	55	49	44	47	42	39	40	36	33	33	30	28	25		
6	65	54	47	41	60	50	44	39	43	38	34	36	33	30	30	28	26	23		
7	61	49	42	37	56	46	39	35	39	34	31	34	30	27	28	25	23	21		
8	56	45	38	33	52	42	36	31	36	31	28	31	27	24	26	23	21	19		
9	53	41	34	29	49	39	32	28	34	29	25	29	25	22	24	21	19	17		
10	49	38	31	27	46	36	30	25	31	26	23	27	23	20	23	20	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14902	14902	14902
5°	14715	14663	14748
10°	13903	14029	14354
15°	12834	13132	13721
20°	11655	12094	12893
25°	10453	11024	12012
30°	9347	9958	11099
35°	8174	8764	10017
40°	6880	7425	8672
45°	5678	6167	7241
50°	4740	5167	6032
55°	4025	4434	4981
60°	3440	3844	3976
65°	2739	3234	2569
70°	2428	2523	1568
75°	2248	2046	960
80°	2072	1884	829
85°	1877	1722	677



TEST NUMBER: P519189

CATALOG NUMBER: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	222.2	2.9
10°-20°	578.0	7.4
20°-30°	748.7	9.6
30°-40°	733.1	9.4
40°-50°	561.2	7.2
50°-60°	373.9	4.8
60°-70°	204.0	2.6
70°-80°	85.0	1.1
80°-90°	25.7	0.3
90°-100°	306.9	3.9
100°-110°	844.3	10.9
110°-120°	871.5	11.2
120°-130°	698.2	9.0
130°-140°	548.4	7.1
140°-150°	420.3	5.4
150°-160°	302.2	3.9
160°-170°	184.8	2.4
170°-180°	62.3	0.8
0°-30°	1548.9	19.9
0°-40°	2282.0	29.4
0°-60°	3217.1	41.4
0°-90°	3531.9	45.5
90°-120°	2022.6	26.0
90°-150°	3689.5	47.5
90°-180°	4239.0	54.6
0°-180°	7770.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2423	2423	2423	2423	2423	
5°	2383	2359	2375	2380	2389	222
15°	2016	2008	2062	2118	2155	563
25°	1540	1544	1624	1695	1770	708
35°	1089	1094	1167	1246	1334	677
45°	653	665	709	763	832	509
55°	375	391	414	429	464	340
65°	188	204	222	194	176	196
75°	95	95	86	59	40	101
85°	27	27	24	16	10	29
90°	1	5	10	12	12	4
95°	46	168	543	232	148	48
105°	151	232	930	1417	1322	159
115°	267	325	746	1486	1686	264
125°	368	420	677	1145	1341	328
135°	444	493	658	926	1048	343
145°	514	549	648	789	850	322
155°	581	600	644	709	730	267
165°	628	637	646	673	677	177
175°	651	652	648	656	655	62
180°	651	651	651	651	651	

TEST NUMBER: P519189

CATALOG NUMBER: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2422.7	2422.7	2422.7	2422.7	2422.7
2.5°	2428.6	2407.0	2412.5	2412.3	2405.7
5°	2383.3	2359.4	2374.8	2380.3	2388.6
7.5°	2294.9	2276.8	2304.9	2325.7	2342.5
10°	2226.0	2210.4	2246.2	2276.5	2298.3
12.5°	2146.1	2133.0	2177.3	2217.9	2246.4
15°	2015.5	2008.2	2062.3	2118.4	2154.8
17.5°	1875.8	1872.3	1934.3	1999.8	2046.3
20°	1780.6	1779.5	1847.6	1915.8	1969.8
22.5°	1684.5	1686.8	1758.3	1829.2	1890.7
25°	1540.3	1544.5	1624.3	1695.1	1770.0
27.5°	1407.0	1408.9	1491.4	1566.2	1646.0
30°	1316.0	1321.2	1402.1	1479.5	1562.7
32.5°	1225.0	1231.1	1310.3	1390.3	1475.1
35°	1088.6	1093.7	1167.2	1245.8	1334.1
37.5°	947.8	954.9	1020.1	1094.4	1181.2
40°	856.8	867.2	924.8	994.8	1080.0
42.5°	769.2	782.1	835.5	901.9	978.8
45°	652.7	665.2	709.0	762.7	832.4
47.5°	552.4	566.7	600.4	646.6	706.1
50°	495.4	508.9	540.0	574.3	630.4
52.5°	445.2	458.7	486.4	512.8	560.6
55°	375.3	390.8	413.5	429.2	464.5
57.5°	317.8	332.8	350.8	357.9	379.3
60°	279.6	296.2	312.5	311.7	323.2
62.5°	244.7	258.8	275.1	263.9	264.5
65°	188.2	203.7	222.2	194.1	176.5
67.5°	152.0	155.3	174.3	135.4	114.4
70°	135.0	135.0	140.3	104.8	87.2
72.5°	118.8	118.8	114.0	85.3	66.8
75°	94.6	94.6	86.1	59.1	40.4
77.5°	72.9	72.1	65.9	44.1	29.3
80°	58.5	58.5	53.2	34.8	23.4
82.5°	45.7	45.7	41.2	27.2	17.4
85°	26.6	26.6	24.4	15.8	9.6
87.5°	9.6	10.4	10.4	7.6	6.7
90°	1.4	5.4	9.7	12.5	12.5
92.5°	19.1	81.6	141.5	54.3	44.6
95°	45.7	167.5	542.7	232.0	148.1
97.5°	74.5	185.7	828.1	638.1	450.2
100°	95.5	197.0	917.8	926.4	755.9
102.5°	115.5	210.5	941.1	1149.3	992.9
105°	150.9	232.1	930.3	1416.8	1322.1
107.5°	184.7	258.9	877.4	1547.8	1576.0
110°	209.0	276.7	837.5	1580.4	1677.8

TEST NUMBER: P519189

CATALOG NUMBER: SQ4-WB-075U-075D-830-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	231.2	296.7	797.7	1559.4	1707.7
115°	267.2	325.4	746.2	1485.8	1686.1
117.5°	301.5	355.1	713.5	1382.6	1609.2
120°	322.6	374.0	699.1	1305.2	1539.4
122.5°	341.4	392.8	689.1	1237.4	1459.7
125°	368.2	419.7	677.0	1145.2	1341.4
127.5°	393.7	442.7	668.9	1068.2	1240.4
130°	407.0	457.1	664.5	1022.5	1179.5
132.5°	422.5	472.6	661.2	982.2	1124.1
135°	444.4	493.1	657.6	926.1	1048.0
137.5°	464.9	510.1	654.5	880.8	981.2
140°	480.4	522.3	653.4	850.7	941.4
142.5°	493.7	532.4	651.2	823.8	901.5
145°	513.6	548.8	647.9	789.1	850.0
147.5°	534.9	565.2	646.2	758.4	807.1
150°	548.2	575.3	645.1	741.5	779.4
152.5°	560.4	585.3	644.0	726.9	758.4
155°	581.4	600.4	643.7	709.3	729.6
157.5°	596.7	612.1	643.7	694.7	708.8
160°	607.7	619.9	643.7	686.9	697.7
162.5°	616.6	626.6	644.8	680.2	688.9
165°	628.5	636.6	646.5	672.9	677.0
167.5°	636.8	643.0	647.9	666.7	667.8
170°	642.3	646.4	647.9	664.5	664.5
172.5°	646.8	648.7	647.9	661.1	660.1
175°	650.6	652.0	647.9	656.2	654.8
177.5°	651.8	651.8	647.3	653.9	651.8
180°	650.6	650.6	650.6	650.6	650.6

(END OF REPORT)