

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519656

Luminaire Tested: **SQ4-025U-0D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519656
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-025U-0D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 768.7 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 5.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519656
CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519656

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	805	10544	3705
100°	930	8724	6865
105°	977	5989	8480
110°	1025	4060	8203
115°	1063	2938	6689
120°	1079	2329	5121
125°	1089	1969	3925
130°	1069	1724	3066
135°	1052	1547	2470
140°	1053	1419	2051
145°	1053	1319	1730
150°	1061	1248	1506
155°	1076	1192	1347
160°	1082	1150	1239
165°	1089	1119	1176
170°	1097	1104	1133
175°	1098	1091	1105



TEST NUMBER: P519656

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	57.8	7.5
100°-110°	151.9	19.8
110°-120°	157.6	20.5
120°-130°	126.4	16.4
130°-140°	99.2	12.9
140°-150°	76.1	9.9
150°-160°	54.8	7.1
160°-170°	33.5	4.4
170°-180°	11.3	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	367.3	47.8
90°-150°	669.0	87.0
90°-180°	769.0	100.0
0°-180°	768.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	2	6	3	3	
95°	8	30	100	51	35	9
105°	27	42	168	255	238	29
115°	49	59	135	268	306	48
125°	68	76	122	207	244	60
135°	81	89	119	167	189	62
145°	94	99	117	142	154	59
155°	106	109	117	129	132	49
165°	114	116	117	122	123	32
175°	119	119	118	119	119	11
180°	119	119	119	119	119	



TEST NUMBER: P519656

CATALOG NUMBER: SQ4-025U-0D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	0.8	2.2	6.1	3.0	3.0
92.5°	3.2	15.4	34.1	15.1	9.7
95°	7.6	29.9	99.6	51.3	35.0
97.5°	13.2	32.8	149.0	118.5	87.3
100°	17.5	35.3	164.2	166.4	129.2
102.5°	21.1	37.8	168.5	207.3	175.4
105°	27.4	41.5	168.0	255.0	237.9
107.5°	33.8	46.8	158.4	279.8	284.0
110°	38.0	49.9	150.5	286.2	304.1
112.5°	42.3	53.6	143.2	282.2	309.5
115°	48.7	59.1	134.6	268.4	306.4
117.5°	54.9	64.4	128.6	249.4	291.5
120°	58.5	67.5	126.2	236.6	277.5
122.5°	62.2	71.1	124.4	223.8	264.1
125°	67.7	75.8	122.4	206.9	244.0
127.5°	72.1	80.4	120.7	193.2	224.6
130°	74.5	83.4	120.1	184.6	213.6
132.5°	76.9	85.8	119.5	177.3	203.3
135°	80.6	88.8	118.6	167.0	189.3
137.5°	84.4	92.4	118.4	159.3	177.6
140°	87.4	94.9	117.8	153.2	170.3
142.5°	89.9	96.7	117.8	148.9	163.6
145°	93.5	99.4	117.1	142.4	153.6
147.5°	97.2	102.9	117.1	137.0	146.3
150°	99.6	104.8	117.1	134.0	141.4
152.5°	102.0	106.0	117.1	131.5	137.1
155°	105.7	108.6	117.1	128.6	132.3
157.5°	108.4	111.2	117.1	125.9	128.6
160°	110.2	112.5	117.1	124.7	126.2
162.5°	112.0	113.7	117.1	123.5	125.0
165°	114.0	115.5	117.1	121.7	123.1
167.5°	115.9	116.6	117.8	120.9	121.5
170°	117.1	117.8	117.8	120.9	120.9
172.5°	117.7	117.8	117.8	120.2	119.7
175°	118.6	118.6	117.8	119.3	119.3
177.5°	118.6	118.6	118.0	119.2	118.6
180°	118.6	118.6	118.6	118.6	118.6

(END OF REPORT)