

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519752

Luminaire Tested: **SQ4-125U-0D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519752
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-125U-0D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3978.2 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519752
CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519752

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20	
RC	80								50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	4658	50029	17700
100°	4798	43919	38122
105°	5123	30614	42984
110°	5314	21284	40954
115°	5536	15614	34122
120°	5621	12299	26610
125°	5569	10330	20544
130°	5499	9060	16011
135°	5440	8143	12937
140°	5408	7470	10741
145°	5429	6940	9054
150°	5503	6523	7887
155°	5570	6218	7057
160°	5627	6004	6498
165°	5669	5856	6119
170°	5707	5751	5891
175°	5714	5686	5751



TEST NUMBER: P519752

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	288.3	7.2
100°-110°	776.6	19.5
110°-120°	815.0	20.5
120°-130°	661.3	16.6
130°-140°	518.7	13.0
140°-150°	398.2	10.0
150°-160°	286.3	7.2
160°-170°	174.9	4.4
170°-180°	59.0	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	1879.8	47.3
90°-150°	3458.0	86.9
90°-180°	3978.0	100.0
0°-180°	3978.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	5	9	10	10	
95°	44	157	473	242	167	49
105°	144	224	859	1285	1206	151
115°	254	310	715	1382	1563	250
125°	346	398	642	1085	1277	309
135°	417	465	624	876	992	322
145°	482	520	616	749	804	302
155°	547	567	611	672	693	252
165°	594	600	613	638	641	167
175°	617	616	614	622	621	59
180°	616	616	616	616	616	



TEST NUMBER: P519752

CATALOG NUMBER: SQ4-125U-0D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.6	4.6	9.4	10.2	10.2
92.5°	19.2	67.7	133.8	64.4	44.7
95°	44.0	156.8	472.6	241.7	167.2
97.5°	70.2	179.5	741.2	619.2	466.9
100°	90.3	188.5	826.6	864.9	717.5
102.5°	109.7	201.2	854.9	1048.9	927.9
105°	143.7	223.5	858.8	1284.9	1205.8
107.5°	175.7	246.9	822.2	1406.1	1426.6
110°	197.0	264.6	789.0	1443.8	1518.2
112.5°	219.7	282.3	756.9	1435.5	1557.8
115°	253.6	310.4	715.2	1381.8	1563.0
117.5°	284.5	337.8	682.8	1296.3	1498.0
120°	304.6	356.0	666.5	1234.8	1442.1
122.5°	322.2	373.0	654.6	1172.0	1378.7
125°	346.2	397.6	642.2	1085.3	1277.2
127.5°	369.3	419.9	634.3	1008.9	1180.2
130°	383.1	433.8	631.2	965.1	1115.5
132.5°	396.9	447.0	628.0	926.5	1064.7
135°	416.9	465.2	624.1	875.6	991.5
137.5°	435.8	482.2	622.1	832.4	927.6
140°	449.0	493.6	620.2	805.8	891.8
142.5°	462.9	504.3	618.9	781.0	853.5
145°	482.0	519.6	616.2	748.6	803.9
147.5°	502.7	535.4	613.6	721.3	764.8
150°	516.5	544.9	612.3	704.2	740.3
152.5°	529.1	553.8	611.7	690.2	719.6
155°	547.2	567.1	610.8	671.7	693.2
157.5°	563.0	578.5	610.9	658.7	673.1
160°	573.1	586.1	611.5	651.0	661.8
162.5°	581.9	592.5	612.2	644.7	652.4
165°	593.5	600.4	613.1	637.5	640.6
167.5°	602.9	606.9	613.9	632.0	633.2
170°	609.2	610.7	613.9	628.8	628.8
172.5°	613.0	613.3	614.5	625.7	625.7
175°	617.0	616.3	613.9	622.5	621.0
177.5°	618.8	617.5	614.4	619.4	618.1
180°	616.2	616.2	616.2	616.2	616.2

(END OF REPORT)