

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P519742

Luminaire Tested: **SQ4-125U-0D-830-1D-UNV-STD-W-8**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519742  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-125U-0D-830-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9437.7 lumens  
Efficiency: N/A  
Efficacy: 153.2 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Indirect

Input Watts (W): 61.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519742  
CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P519742

CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20								20				20				20			
RC	80								50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0		
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0		
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0		
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0		
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0		
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0		
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0		
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0		
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0		
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0		
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	5521	59339	20997
100°	5690	52096	45220
105°	6074	36314	50986
110°	6304	25244	48580
115°	6566	18519	40474
120°	6667	14588	31564
125°	6605	12252	24369
130°	6522	10746	18992
135°	6451	9659	15345
140°	6415	8860	12740
145°	6440	8233	10739
150°	6527	7738	9355
155°	6607	7375	8370
160°	6674	7122	7707
165°	6724	6946	7258
170°	6770	6822	6988
175°	6778	6744	6822



TEST NUMBER: P519742

CATALOG NUMBER: SQ4-125U-0D-830-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	683.9	7.2
100°-110°	1842.3	19.5
110°-120°	1933.4	20.5
120°-130°	1568.9	16.6
130°-140°	1230.4	13.0
140°-150°	944.7	10.0
150°-160°	679.2	7.2
160°-170°	415.0	4.4
170°-180°	139.9	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4459.5	47.3
90°-150°	8203.5	86.9
90°-180°	9438.0	100.0
0°-180°	9437.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	4	11	22	24	24	
95°	104	372	1121	573	397	116
105°	341	530	2037	3048	2861	358
115°	602	736	1697	3278	3708	592
125°	821	943	1523	2575	3030	733
135°	989	1104	1481	2077	2352	763
145°	1144	1233	1462	1776	1907	717
155°	1298	1345	1449	1594	1644	598
165°	1408	1424	1454	1512	1520	397
175°	1464	1462	1456	1477	1473	139
180°	1462	1462	1462	1462	1462	



TEST NUMBER: P519742

CATALOG NUMBER: SQ4-125U-OD-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	3.7	11.0	22.3	24.2	24.2
92.5°	45.4	160.5	317.3	152.8	106.2
95°	104.3	372.0	1121.1	573.3	396.7
97.5°	166.5	425.8	1758.4	1469.0	1107.7
100°	214.2	447.3	1961.0	2051.8	1702.2
102.5°	260.4	477.4	2028.1	2488.3	2201.3
105°	340.8	530.2	2037.4	3048.1	2860.6
107.5°	416.8	585.8	1950.6	3335.8	3384.2
110°	467.4	627.7	1871.6	3425.1	3601.8
112.5°	521.1	669.7	1795.7	3405.4	3695.6
115°	601.5	736.3	1696.6	3278.2	3707.9
117.5°	674.9	801.3	1619.9	3075.2	3553.7
120°	722.6	844.6	1581.1	2929.5	3421.1
122.5°	764.3	884.9	1552.8	2780.4	3270.6
125°	821.3	943.3	1523.4	2574.8	3030.0
127.5°	876.0	996.2	1504.8	2393.4	2799.8
130°	908.8	1029.0	1497.3	2289.5	2646.4
132.5°	941.6	1060.3	1489.9	2197.9	2525.7
135°	988.9	1103.6	1480.6	2077.2	2352.1
137.5°	1034.0	1144.0	1475.7	1974.7	2200.5
140°	1065.3	1170.9	1471.2	1911.7	2115.6
142.5°	1098.0	1196.4	1468.3	1852.8	2024.7
145°	1143.5	1232.7	1461.9	1775.9	1907.0
147.5°	1192.6	1270.2	1455.6	1711.2	1814.3
150°	1225.4	1292.8	1452.6	1670.6	1756.2
152.5°	1255.2	1313.9	1451.1	1637.5	1707.0
155°	1298.0	1345.4	1448.9	1593.5	1644.4
157.5°	1335.7	1372.5	1449.3	1562.5	1596.8
160°	1359.5	1390.5	1450.8	1544.5	1570.0
162.5°	1380.4	1405.5	1452.3	1529.4	1547.6
165°	1407.9	1424.3	1454.5	1512.4	1519.7
167.5°	1430.3	1439.7	1456.3	1499.2	1502.2
170°	1445.2	1448.8	1456.3	1491.7	1491.7
172.5°	1454.1	1454.8	1457.8	1484.3	1484.3
175°	1463.8	1462.0	1456.3	1476.8	1473.1
177.5°	1467.9	1465.0	1457.5	1469.3	1466.4
180°	1461.9	1461.9	1461.9	1461.9	1461.9

(END OF REPORT)