

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519776

Luminaire Tested: **SQ4-150U-0D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519776
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4793.6 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 39.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519776
CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519776

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	5674	60826	18726
100°	5866	52898	44604
105°	6192	36945	52266
110°	6498	25648	49287
115°	6674	18764	41005
120°	6763	14812	32091
125°	6733	12461	24704
130°	6628	10936	19356
135°	6547	9837	15591
140°	6535	9022	12916
145°	6571	8374	10952
150°	6633	7870	9507
155°	6706	7504	8522
160°	6797	7245	7834
165°	6850	7071	7384
170°	6876	6943	7108
175°	6893	6864	6938



TEST NUMBER: P519776

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	345.5	7.2
100°-110°	934.2	19.5
110°-120°	982.2	20.5
120°-130°	797.8	16.6
130°-140°	625.8	13.1
140°-150°	480.3	10.0
150°-160°	345.4	7.2
160°-170°	211.0	4.4
170°-180°	71.1	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2262.0	47.2
90°-150°	4166.0	86.9
90°-180°	4794.0	100.0
0°-180°	4793.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	5	10	11	10	
95°	54	188	575	297	177	59
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	



TEST NUMBER: P519776

CATALOG NUMBER: SQ4-150U-0D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)