

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936250

Luminaire Tested: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936250  
REPORT IS A COMBINATION OF REPORTS P933437 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2073.3 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 22  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936250  
CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P936250

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	68	68	68	63
1	100	95	91	87	93	89	86	82	78	75	73	68	66	64	59	57	56	59	57	56	51
2	90	82	76	70	84	77	71	66	68	63	59	59	55	52	51	48	46	51	48	46	42
3	82	72	64	57	76	67	60	55	59	53	49	51	47	43	44	41	38	44	41	38	34
4	75	63	54	48	69	59	52	46	52	46	41	45	40	37	39	35	32	39	35	32	29
5	68	56	47	41	64	52	45	39	46	40	35	40	35	31	35	31	28	35	31	28	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	24	31	27	24	21
7	58	45	36	30	54	42	34	29	37	31	26	33	27	23	28	24	21	28	24	21	18
8	53	40	32	26	50	38	31	25	34	27	23	30	24	21	26	22	18	26	22	18	16
9	50	37	29	23	46	35	27	22	31	25	20	27	22	18	24	19	16	24	19	16	14
10	46	34	26	21	43	32	25	20	28	22	18	25	20	16	22	18	15	22	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1554	1554	1554
5°	1517	1795	2090
10°	1374	2616	3464
15°	1167	3414	4183
20°	949	3954	4263
25°	790	4135	4176
30°	665	4157	4169
35°	588	4085	4276
40°	511	3992	4387
45°	462	3923	4405
50°	423	3860	4332
55°	405	3769	4140
60°	411	3599	3837
65°	427	3341	3419
70°	449	2908	2889
75°	495	2364	2254
80°	529	1636	1521
85°	447	865	778

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 4405 cd/sqm



TEST NUMBER: P936250

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.7	1.0
10°-20°	96.0	4.6
20°-30°	168.0	8.1
30°-40°	216.3	10.4
40°-50°	241.6	11.7
50°-60°	231.4	11.2
60°-70°	183.4	8.8
70°-80°	107.8	5.2
80°-90°	30.4	1.5
90°-100°	58.4	2.8
100°-110°	153.6	7.4
110°-120°	159.2	7.7
120°-130°	127.7	6.2
130°-140°	100.2	4.8
140°-150°	76.9	3.7
150°-160°	55.4	2.7
160°-170°	33.9	1.6
170°-180°	11.4	0.6
0°-30°	285.7	13.8
0°-40°	502.0	24.2
0°-60°	974.9	47.0
0°-90°	1296.5	62.5
90°-120°	371.2	17.9
90°-150°	676.1	32.6
90°-180°	777.0	37.5
0°-180°	2073.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	168	168	168	168	168	
5°	163	175	197	223	231	15
15°	122	226	380	461	476	34
25°	78	256	453	473	474	36
35°	53	245	427	451	469	33
45°	36	195	377	432	451	28
55°	26	124	320	372	382	24
65°	20	66	238	267	271	20
75°	15	40	130	143	144	16
85°	5	12	32	36	36	6
90°	1	2	6	3	3	1
95°	8	30	101	52	35	9
105°	28	42	170	258	240	29
115°	49	60	136	271	310	49
125°	68	77	124	209	247	61
135°	82	90	120	169	191	63
145°	94	100	118	144	155	59
155°	107	110	118	130	134	49
165°	115	117	118	123	124	33
175°	120	120	119	121	121	11
180°	120	120	120	120	120	



TEST NUMBER: P936250  
 CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	167.5	167.5	167.5	167.5	167.5	167.5	167.5	167.5	167.5	167.5	167.5
2.5°	167.5	167.5	168.6	169.1	170.2	170.8	171.8	172.9	176.2	176.7	177.8
5°	163.2	165.4	172.4	175.1	182.6	192.9	197.1	204.2	218.7	223.0	225.7
7.5°	156.7	161.6	178.8	183.2	202.0	228.9	240.3	255.4	278.5	289.8	299.0
10°	146.5	156.7	187.5	197.7	228.4	269.3	290.4	311.4	346.4	362.0	367.9
12.5°	135.2	151.9	196.7	210.6	254.8	314.6	339.9	363.1	402.9	424.0	427.2
15°	122.3	144.9	205.2	225.7	282.8	352.3	380.3	408.9	446.1	461.1	464.9
17.5°	111.0	139.6	213.4	234.9	304.3	386.2	414.8	438.5	468.6	478.9	481.6
20°	97.0	130.9	218.7	246.8	327.0	411.1	438.5	456.8	477.3	483.7	484.9
22.5°	86.7	121.7	221.9	251.0	342.1	426.1	449.3	463.8	477.8	480.0	480.5
25°	78.1	111.5	221.4	255.9	355.0	435.2	453.1	463.8	471.9	473.0	473.0
27.5°	70.0	100.2	219.2	257.0	364.7	437.4	451.4	459.0	462.8	464.9	464.9
30°	63.0	89.5	213.8	254.8	369.0	435.2	446.5	450.3	454.1	457.4	459.0
32.5°	57.7	79.2	205.8	250.5	369.5	429.8	438.0	440.1	445.5	453.1	455.7
35°	52.8	69.0	196.7	244.6	366.3	421.3	426.6	428.8	439.6	450.9	454.7
37.5°	47.9	61.4	184.8	234.3	361.4	411.1	414.8	418.6	435.2	448.7	453.1
40°	43.1	54.9	170.8	223.0	354.0	398.6	401.9	407.8	429.8	445.5	449.8
42.5°	39.3	49.5	155.7	211.2	344.2	384.6	389.5	398.1	423.4	440.1	444.9
45°	36.1	44.2	139.6	195.0	331.8	370.1	377.1	389.0	415.9	432.0	436.4
47.5°	32.8	40.4	122.9	178.3	318.4	355.6	364.7	378.1	405.7	421.3	425.0
50°	30.2	36.6	106.2	160.5	303.9	339.9	350.7	364.7	392.7	407.3	412.1
52.5°	28.0	33.4	90.5	142.8	287.2	323.8	336.1	350.7	377.1	391.1	394.4
55°	25.9	30.7	77.0	123.9	269.9	306.5	320.0	334.0	359.8	371.7	373.9
57.5°	24.8	28.6	65.7	106.2	251.6	287.2	302.2	315.1	339.3	348.5	350.7
60°	23.1	26.9	57.1	91.1	231.7	268.8	281.8	294.7	315.1	322.6	324.3
62.5°	21.5	25.9	50.7	76.5	211.2	247.2	260.2	272.1	289.2	294.7	296.8
65°	20.5	24.8	45.8	65.7	190.2	224.6	237.5	247.8	261.8	267.2	268.3
67.5°	19.4	23.7	42.0	56.5	169.1	202.0	211.7	221.4	232.1	237.5	238.1
70°	17.7	22.6	38.8	50.1	147.6	176.2	184.2	194.5	203.1	205.8	207.4
72.5°	16.7	21.0	36.6	45.3	125.5	151.4	158.9	164.9	172.4	175.1	175.1
75°	15.1	18.9	34.4	40.4	102.9	123.9	130.3	136.3	142.2	143.3	141.6
77.5°	13.5	16.7	29.6	34.0	80.3	98.0	103.4	106.6	111.5	112.6	113.1
80°	11.3	14.5	23.1	26.4	58.2	72.2	76.0	78.6	82.9	82.9	84.1
82.5°	8.6	11.3	16.7	18.9	39.3	49.5	52.8	54.4	57.1	57.1	57.1
85°	5.4	7.0	10.8	12.4	23.7	30.2	32.4	32.8	35.0	35.6	35.6
87.5°	2.7	3.8	7.0	7.5	12.4	15.7	15.7	16.7	16.7	16.1	15.7
90°	0.8	1.4	2.1	2.2	3.5	5.2	6.1	5.5	4.1	3.1	3.1
92.5°	3.2	8.7	14.1	15.5	21.8	30.3	34.4	30.2	21.7	15.3	14.6
95°	7.7	17.7	27.8	30.3	53.7	85.0	100.6	89.8	68.1	51.9	50.0
97.5°	13.3	22.2	31.0	33.2	72.4	124.5	150.6	143.7	130.0	119.7	116.2
100°	17.7	25.7	33.7	35.7	79.1	137.0	165.9	166.4	167.4	168.1	164.0
102.5°	21.4	28.8	36.4	38.2	82.2	140.9	170.2	179.0	196.4	209.5	205.9
105°	27.7	34.0	40.3	41.9	84.6	141.3	169.8	189.3	228.5	257.8	255.8
107.5°	34.1	40.0	45.9	47.4	85.0	135.1	160.1	187.4	241.9	282.9	283.4
110°	38.5	43.8	49.1	50.4	84.3	129.5	152.1	182.6	243.5	289.3	291.3



TEST NUMBER: P936250

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	42.7	47.8	52.8	54.1	84.3	124.6	144.8	176.0	238.4	285.2	288.3
115°	49.1	53.8	58.5	59.7	85.1	119.1	136.0	166.1	226.2	271.3	275.5
117.5°	55.5	59.7	64.0	65.0	86.7	115.6	130.0	157.1	211.3	252.1	256.8
120°	59.2	63.2	67.2	68.2	87.9	114.3	127.5	152.3	202.0	239.1	243.7
122.5°	62.8	66.8	70.8	71.9	89.8	113.7	125.7	148.0	192.6	226.1	230.6
125°	68.3	72.0	75.7	76.7	92.3	113.2	123.7	142.6	180.6	209.0	213.2
127.5°	72.8	76.6	80.3	81.3	94.8	112.9	122.0	138.3	170.9	195.3	198.8
130°	75.2	79.3	83.3	84.3	96.7	113.1	121.3	135.9	164.9	186.6	189.8
132.5°	77.8	81.8	85.8	86.8	98.1	113.2	120.8	133.8	159.7	179.2	182.1
135°	81.5	85.1	88.8	89.7	99.7	113.1	119.8	130.6	152.4	168.7	171.2
137.5°	85.3	88.9	92.5	93.4	102.1	113.8	119.6	128.8	147.2	161.0	163.1
140°	88.4	91.7	95.1	95.9	103.6	113.9	119.1	127.0	142.9	154.8	156.7
142.5°	90.8	93.9	96.9	97.7	104.9	114.3	119.1	126.1	140.0	150.5	152.2
145°	94.5	97.2	99.9	100.5	106.5	114.3	118.3	124.0	135.4	144.0	145.3
147.5°	98.2	100.8	103.4	104.1	108.8	115.2	118.3	122.8	131.8	138.5	139.6
150°	100.6	102.9	105.4	105.9	110.0	115.6	118.3	122.1	129.7	135.4	136.2
152.5°	103.1	104.9	106.6	107.1	110.8	115.8	118.3	121.5	128.0	132.9	133.5
155°	106.8	108.1	109.4	109.8	112.6	116.4	118.3	120.9	126.1	129.9	130.3
157.5°	109.5	110.8	112.1	112.4	114.3	117.0	118.3	120.3	124.3	127.3	127.6
160°	111.4	112.3	113.4	113.6	115.2	117.2	118.3	120.0	123.4	126.0	126.2
162.5°	113.2	113.9	114.7	114.9	116.0	117.6	118.3	119.7	122.6	124.8	124.9
165°	115.2	115.9	116.6	116.8	117.2	118.0	118.3	119.3	121.4	122.9	123.1
167.5°	117.1	117.4	117.7	117.8	118.2	118.8	119.1	119.7	121.1	122.1	122.2
170°	118.3	118.6	118.9	119.0	119.0	119.1	119.1	119.7	121.1	122.1	122.1
172.5°	118.9	119.0	119.1	119.1	119.1	119.1	119.1	119.6	120.7	121.5	121.4
175°	119.8	119.8	119.8	119.8	119.6	119.2	119.1	119.4	120.1	120.6	120.6
177.5°	119.8	119.8	119.8	119.8	119.6	119.4	119.2	119.5	120.0	120.4	120.4
180°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8



TEST NUMBER: P936250

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	167.5	167.5
2.5°	178.8	177.8
5°	230.1	231.1
7.5°	309.7	309.2
10°	385.2	390.0
12.5°	440.1	441.2
15°	473.5	475.7
17.5°	486.5	487.0
20°	487.0	485.9
22.5°	481.1	480.0
25°	474.1	473.5
27.5°	467.6	468.1
30°	464.9	466.5
32.5°	464.9	467.6
35°	466.0	468.6
37.5°	465.4	468.6
40°	463.3	467.0
42.5°	457.4	460.0
45°	448.2	451.4
47.5°	436.4	438.5
50°	421.3	423.4
52.5°	402.4	402.9
55°	379.8	381.9
57.5°	355.6	356.1
60°	328.6	330.2
62.5°	300.1	300.1
65°	269.9	270.9
67.5°	238.7	241.3
70°	206.9	207.4
72.5°	175.6	175.6
75°	143.3	143.8
77.5°	112.6	112.6
80°	83.5	84.1
82.5°	57.7	58.7
85°	36.1	36.1
87.5°	16.7	15.1
90°	3.1	3.1
92.5°	12.2	9.8
95°	42.7	35.3
97.5°	102.2	88.2
100°	147.4	130.6
102.5°	191.6	177.3
105°	248.2	240.5
107.5°	285.2	287.1
110°	299.3	307.3





TEST NUMBER: P936250

CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	300.6	312.8
115°	292.6	309.6
117.5°	275.7	294.6
120°	262.1	280.4
122.5°	248.8	266.9
125°	229.9	246.6
127.5°	212.9	226.9
130°	202.8	215.8
132.5°	193.8	205.4
135°	181.3	191.4
137.5°	171.3	179.6
140°	164.4	172.1
142.5°	158.8	165.3
145°	150.2	155.2
147.5°	143.7	147.8
150°	139.6	142.9
152.5°	136.0	138.6
155°	132.0	133.7
157.5°	128.8	130.0
160°	126.9	127.5
162.5°	125.6	126.2
165°	123.8	124.5
167.5°	122.5	122.8
170°	122.1	122.1
172.5°	121.2	120.9
175°	120.6	120.6
177.5°	120.1	119.8
180°	119.8	119.8



TEST NUMBER: P936250  
 CATALOG NUMBER: SQ4-FB-025U-050D-930-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.59	4.63	4.42	5.49	6.57	16.73	17.77	17.56	18.63	19.70
	3H	4.31	5.24	5.15	6.11	7.22	18.57	19.50	19.41	20.37	21.48
	4H	4.62	5.50	5.48	6.38	7.49	19.21	20.09	20.07	20.97	22.09
	6H	4.88	5.69	5.75	6.58	7.71	19.64	20.45	20.51	21.34	22.47
	8H	4.95	5.73	5.83	6.63	7.76	19.76	20.54	20.64	21.44	22.57
	12H	4.97	5.72	5.86	6.61	7.77	19.82	20.57	20.71	21.46	22.62
4H	2H	10.80	11.68	11.67	12.56	13.68	17.03	17.91	17.89	18.79	19.90
	3H	12.39	13.13	13.26	14.04	15.17	19.07	19.81	19.95	20.72	21.85
	4H	12.49	13.17	13.38	14.07	15.23	19.84	20.51	20.73	21.42	22.58
	6H	12.51	13.10	13.42	14.03	15.19	20.37	20.96	21.28	21.89	23.05
	8H	12.49	13.04	13.40	13.97	15.14	20.53	21.08	21.44	22.01	23.18
	12H	12.46	12.95	13.39	13.90	15.07	20.63	21.13	21.56	22.07	23.25
8H	4H	13.94	14.49	14.85	15.41	16.58	19.91	20.46	20.82	21.39	22.56
	6H	14.19	14.65	15.13	15.61	16.78	20.54	20.99	21.47	21.96	23.13
	8H	14.21	14.62	15.16	15.57	16.76	20.75	21.16	21.70	22.11	23.30
	12H	14.19	14.54	15.14	15.49	16.73	20.90	21.25	21.85	22.20	23.44
12H	4H	14.09	14.58	15.02	15.53	16.70	19.88	20.37	20.80	21.31	22.49
	6H	14.45	14.85	15.39	15.81	17.00	20.52	20.93	21.47	21.89	23.07
	8H	14.53	14.88	15.48	15.83	17.07	20.76	21.11	21.71	22.06	23.30