

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936450

Luminaire Tested: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936450
REPORT IS A COMBINATION OF REPORTS P933439 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3330.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 38.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936450
CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P936450

CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77				77
1	103	98	94	90	98	94	90	86	85	82	79	77	75	73	70	68	66	63				63
2	93	85	78	72	88	81	75	69	73	68	64	67	63	59	61	57	55	51				51
3	84	74	65	59	80	70	63	57	64	58	53	58	53	49	53	49	45	42				42
4	77	65	56	49	73	62	54	47	56	50	44	51	46	41	47	42	38	35				35
5	70	57	48	42	66	55	46	40	50	43	38	46	40	35	41	37	33	30				30
6	64	51	42	36	61	49	41	35	45	38	32	41	35	30	37	32	28	26				26
7	59	46	37	31	56	44	36	30	40	33	28	37	31	27	34	29	25	22				22
8	55	42	33	27	52	40	32	26	37	30	25	34	28	23	31	26	22	20				20
9	51	38	30	24	49	36	29	23	33	27	22	31	25	21	28	23	20	17				17
10	48	35	27	21	45	33	26	21	31	24	20	28	23	19	26	21	17	16				16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3062	3062	3062
5°	2988	3536	4116
10°	2707	5151	6823
15°	2298	6725	8239
20°	1869	7788	8396
25°	1558	8143	8227
30°	1311	8188	8211
35°	1158	8046	8423
40°	1007	7862	8642
45°	910	7726	8677
50°	833	7602	8533
55°	795	7424	8155
60°	811	7089	7557
65°	840	6582	6737
70°	889	5729	5691
75°	974	4659	4441
80°	1039	3219	2992
85°	878	1700	1532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 8677 cd/sqm



TEST NUMBER: P936450

CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.3
10°-20°	189.2	5.7
20°-30°	330.9	9.9
30°-40°	426.0	12.8
40°-50°	475.8	14.3
50°-60°	455.7	13.7
60°-70°	361.2	10.8
70°-80°	212.4	6.4
80°-90°	59.5	1.8
90°-100°	58.4	1.8
100°-110°	153.6	4.6
110°-120°	159.2	4.8
120°-130°	127.7	3.8
130°-140°	100.2	3.0
140°-150°	76.9	2.3
150°-160°	55.4	1.7
160°-170°	33.9	1.0
170°-180°	11.4	0.3
0°-30°	562.8	16.9
0°-40°	988.7	29.7
0°-60°	1920.2	57.7
0°-90°	2553.2	76.7
90°-120°	371.2	11.1
90°-150°	676.1	20.3
90°-180°	777.0	23.3
0°-180°	3330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	330	330	330	330	330	
5°	322	345	388	439	455	30
15°	241	444	749	908	937	67
25°	154	504	892	932	933	71
35°	104	482	840	888	923	65
45°	71	384	743	851	889	55
55°	51	244	630	732	752	46
65°	40	129	468	526	534	40
75°	30	80	257	282	283	31
85°	11	24	64	70	71	11
90°	1	2	6	3	3	1
95°	8	30	101	52	35	9
105°	28	42	170	258	240	29
115°	49	60	136	271	310	49
125°	68	77	124	209	247	61
135°	82	90	120	169	191	63
145°	94	100	118	144	155	59
155°	107	110	118	130	134	49
165°	115	117	118	123	124	33
175°	120	120	119	121	121	11
180°	120	120	120	120	120	



TEST NUMBER: P936450
 CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	330.0	330.0	330.0	330.0	330.0	330.0	330.0	330.0	330.0	330.0	330.0
2.5°	330.0	330.0	332.1	333.2	335.3	336.4	338.5	340.6	347.0	348.0	350.1
5°	321.5	325.8	339.5	344.8	359.7	379.8	388.3	402.1	430.8	439.2	444.5
7.5°	308.8	318.3	352.3	360.8	397.9	451.0	473.2	502.9	548.5	570.9	588.8
10°	288.6	308.8	369.2	389.4	449.8	530.5	571.9	613.3	682.2	713.0	724.7
12.5°	266.4	299.2	387.3	414.8	501.9	619.7	669.5	715.2	793.7	835.0	841.4
15°	240.8	285.4	404.2	444.5	557.0	694.0	749.1	805.3	878.6	908.3	915.7
17.5°	218.6	274.8	420.1	462.6	599.5	760.8	817.0	863.7	923.1	943.3	948.6
20°	191.0	257.8	430.8	486.0	644.1	809.6	863.7	899.8	940.1	952.8	954.9
22.5°	170.8	239.8	437.2	494.4	673.7	839.3	884.9	913.6	941.1	945.4	946.4
25°	153.9	219.6	436.1	504.0	699.3	857.3	892.3	913.6	929.5	931.6	931.6
27.5°	138.0	197.4	431.9	506.1	718.3	861.5	889.2	904.0	911.4	915.7	915.7
30°	124.1	176.1	421.3	501.9	726.8	857.3	879.6	887.0	894.5	900.8	904.0
32.5°	113.5	155.9	405.4	493.4	727.8	846.7	862.6	866.8	877.4	892.3	897.7
35°	104.0	135.8	387.3	481.7	721.5	829.7	840.3	844.6	865.8	888.1	895.5
37.5°	94.4	120.9	363.9	461.6	711.9	809.6	817.0	824.4	857.3	883.9	892.3
40°	84.9	108.2	336.4	439.2	697.1	785.2	791.5	803.2	846.7	877.4	885.9
42.5°	77.5	97.6	306.7	416.0	678.0	757.6	767.1	784.1	834.0	866.8	876.4
45°	71.1	87.0	274.8	384.1	653.6	729.0	742.7	766.1	819.1	850.9	859.5
47.5°	64.7	79.6	241.9	351.2	627.1	700.3	718.3	744.9	799.0	829.7	837.1
50°	59.4	72.2	209.0	316.2	598.4	669.5	690.7	718.3	773.5	802.1	811.7
52.5°	55.2	65.8	178.3	281.2	565.6	637.7	662.1	690.7	742.7	770.3	776.7
55°	50.9	60.5	151.8	244.0	531.6	603.7	630.3	657.8	708.8	732.1	736.4
57.5°	48.8	56.2	129.4	209.0	495.5	565.6	595.3	620.7	668.4	686.5	690.7
60°	45.6	53.1	112.5	179.3	456.3	529.4	555.0	580.4	620.7	635.6	638.7
62.5°	42.5	50.9	99.7	150.6	416.0	487.0	512.5	535.8	569.8	580.4	584.7
65°	40.3	48.8	90.2	129.4	374.5	442.5	467.9	488.1	515.7	526.3	528.4
67.5°	38.2	46.7	82.8	111.4	333.2	397.9	417.0	436.1	457.3	467.9	469.0
70°	35.0	44.6	76.4	98.7	290.7	347.0	362.9	383.0	400.0	405.4	408.5
72.5°	32.9	41.4	72.2	89.1	247.2	298.2	313.0	324.7	339.5	344.8	344.8
75°	29.7	37.1	67.9	79.6	202.7	244.0	256.8	268.4	280.1	282.3	279.0
77.5°	26.5	32.9	58.4	66.8	158.1	193.1	203.7	210.1	219.6	221.8	222.8
80°	22.2	28.7	45.6	52.0	114.6	142.2	149.6	154.9	163.4	163.4	165.5
82.5°	16.9	22.2	32.9	37.1	77.5	97.6	104.0	107.2	112.5	112.5	112.5
85°	10.6	13.8	21.2	24.4	46.7	59.4	63.7	64.7	69.0	70.0	70.0
87.5°	5.3	7.4	13.8	14.9	24.4	30.8	30.8	32.9	32.9	31.8	30.8
90°	0.8	1.4	2.1	2.2	3.5	5.2	6.1	5.5	4.1	3.1	3.1
92.5°	3.2	8.7	14.1	15.5	21.8	30.3	34.4	30.2	21.7	15.3	14.6
95°	7.7	17.7	27.8	30.3	53.7	85.0	100.6	89.8	68.1	51.9	50.0
97.5°	13.3	22.2	31.0	33.2	72.4	124.5	150.6	143.7	130.0	119.7	116.2
100°	17.7	25.7	33.7	35.7	79.1	137.0	165.9	166.4	167.4	168.1	164.0
102.5°	21.4	28.8	36.4	38.2	82.2	140.9	170.2	179.0	196.4	209.5	205.9
105°	27.7	34.0	40.3	41.9	84.6	141.3	169.8	189.3	228.5	257.8	255.8
107.5°	34.1	40.0	45.9	47.4	85.0	135.1	160.1	187.4	241.9	282.9	283.4
110°	38.5	43.8	49.1	50.4	84.3	129.5	152.1	182.6	243.5	289.3	291.3



TEST NUMBER: P936450

CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	42.7	47.8	52.8	54.1	84.3	124.6	144.8	176.0	238.4	285.2	288.3
115°	49.1	53.8	58.5	59.7	85.1	119.1	136.0	166.1	226.2	271.3	275.5
117.5°	55.5	59.7	64.0	65.0	86.7	115.6	130.0	157.1	211.3	252.1	256.8
120°	59.2	63.2	67.2	68.2	87.9	114.3	127.5	152.3	202.0	239.1	243.7
122.5°	62.8	66.8	70.8	71.9	89.8	113.7	125.7	148.0	192.6	226.1	230.6
125°	68.3	72.0	75.7	76.7	92.3	113.2	123.7	142.6	180.6	209.0	213.2
127.5°	72.8	76.6	80.3	81.3	94.8	112.9	122.0	138.3	170.9	195.3	198.8
130°	75.2	79.3	83.3	84.3	96.7	113.1	121.3	135.9	164.9	186.6	189.8
132.5°	77.8	81.8	85.8	86.8	98.1	113.2	120.8	133.8	159.7	179.2	182.1
135°	81.5	85.1	88.8	89.7	99.7	113.1	119.8	130.6	152.4	168.7	171.2
137.5°	85.3	88.9	92.5	93.4	102.1	113.8	119.6	128.8	147.2	161.0	163.1
140°	88.4	91.7	95.1	95.9	103.6	113.9	119.1	127.0	142.9	154.8	156.7
142.5°	90.8	93.9	96.9	97.7	104.9	114.3	119.1	126.1	140.0	150.5	152.2
145°	94.5	97.2	99.9	100.5	106.5	114.3	118.3	124.0	135.4	144.0	145.3
147.5°	98.2	100.8	103.4	104.1	108.8	115.2	118.3	122.8	131.8	138.5	139.6
150°	100.6	102.9	105.4	105.9	110.0	115.6	118.3	122.1	129.7	135.4	136.2
152.5°	103.1	104.9	106.6	107.1	110.8	115.8	118.3	121.5	128.0	132.9	133.5
155°	106.8	108.1	109.4	109.8	112.6	116.4	118.3	120.9	126.1	129.9	130.3
157.5°	109.5	110.8	112.1	112.4	114.3	117.0	118.3	120.3	124.3	127.3	127.6
160°	111.4	112.3	113.4	113.6	115.2	117.2	118.3	120.0	123.4	126.0	126.2
162.5°	113.2	113.9	114.7	114.9	116.0	117.6	118.3	119.7	122.6	124.8	124.9
165°	115.2	115.9	116.6	116.8	117.2	118.0	118.3	119.3	121.4	122.9	123.1
167.5°	117.1	117.4	117.7	117.8	118.2	118.8	119.1	119.7	121.1	122.1	122.2
170°	118.3	118.6	118.9	119.0	119.0	119.1	119.1	119.7	121.1	122.1	122.1
172.5°	118.9	119.0	119.1	119.1	119.1	119.1	119.1	119.6	120.7	121.5	121.4
175°	119.8	119.8	119.8	119.8	119.6	119.2	119.1	119.4	120.1	120.6	120.6
177.5°	119.8	119.8	119.8	119.8	119.6	119.4	119.2	119.5	120.0	120.4	120.4
180°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8



TEST NUMBER: P936450

CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	330.0	330.0
2.5°	352.3	350.1
5°	453.1	455.2
7.5°	610.1	609.0
10°	758.7	768.1
12.5°	866.8	869.0
15°	932.7	936.9
17.5°	958.1	959.2
20°	959.2	957.0
22.5°	947.5	945.4
25°	933.7	932.7
27.5°	921.0	922.0
30°	915.7	918.9
32.5°	915.7	921.0
35°	917.8	923.1
37.5°	916.7	923.1
40°	912.5	919.9
42.5°	900.8	906.1
45°	882.8	889.2
47.5°	859.5	863.7
50°	829.7	834.0
52.5°	792.6	793.7
55°	748.0	752.3
57.5°	700.3	701.3
60°	647.2	650.4
62.5°	591.0	591.0
65°	531.6	533.7
67.5°	470.1	475.4
70°	407.4	408.5
72.5°	345.9	345.9
75°	282.3	283.3
77.5°	221.8	221.8
80°	164.5	165.5
82.5°	113.5	115.6
85°	71.1	71.1
87.5°	32.9	29.7
90°	3.1	3.1
92.5°	12.2	9.8
95°	42.7	35.3
97.5°	102.2	88.2
100°	147.4	130.6
102.5°	191.6	177.3
105°	248.2	240.5
107.5°	285.2	287.1
110°	299.3	307.3



TEST NUMBER: P936450

CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	300.6	312.8
115°	292.6	309.6
117.5°	275.7	294.6
120°	262.1	280.4
122.5°	248.8	266.9
125°	229.9	246.6
127.5°	212.9	226.9
130°	202.8	215.8
132.5°	193.8	205.4
135°	181.3	191.4
137.5°	171.3	179.6
140°	164.4	172.1
142.5°	158.8	165.3
145°	150.2	155.2
147.5°	143.7	147.8
150°	139.6	142.9
152.5°	136.0	138.6
155°	132.0	133.7
157.5°	128.8	130.0
160°	126.9	127.5
162.5°	125.6	126.2
165°	123.8	124.5
167.5°	122.5	122.8
170°	122.1	122.1
172.5°	121.2	120.9
175°	120.6	120.6
177.5°	120.1	119.8
180°	119.8	119.8



TEST NUMBER: P936450
 CATALOG NUMBER: SQ4-FB-025U-100D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.01	8.24	7.69	8.95	9.78	20.15	21.38	20.83	22.09	22.92
	3H	7.74	8.86	8.44	9.57	10.43	22.00	23.11	22.69	23.83	24.69
	4H	8.06	9.11	8.77	9.84	10.71	22.65	23.70	23.36	24.43	25.30
	6H	8.33	9.30	9.05	10.04	10.93	23.09	24.06	23.82	24.80	25.69
	8H	8.40	9.34	9.14	10.09	10.98	23.21	24.15	23.95	24.90	25.79
	12H	8.44	9.33	9.18	10.07	10.99	23.29	24.18	24.03	24.93	25.85
4H	2H	14.24	15.30	14.96	16.02	16.90	20.47	21.52	21.18	22.25	23.12
	3H	15.85	16.73	16.58	17.49	18.39	22.53	23.42	23.26	24.18	25.07
	4H	15.96	16.76	16.70	17.53	18.45	23.30	24.11	24.05	24.87	25.79
	6H	15.99	16.69	16.75	17.48	18.41	23.85	24.56	24.62	25.34	26.27
	8H	15.98	16.64	16.75	17.42	18.36	24.02	24.68	24.79	25.46	26.40
	12H	15.95	16.55	16.74	17.35	18.30	24.12	24.72	24.91	25.52	26.47
8H	4H	17.42	18.08	18.19	18.87	19.81	23.40	24.05	24.17	24.84	25.78
	6H	17.68	18.23	18.48	19.06	20.00	24.03	24.58	24.83	25.40	26.35
	8H	17.71	18.20	18.52	19.02	19.98	24.25	24.74	25.06	25.56	26.52
	12H	17.69	18.12	18.51	18.94	19.96	24.40	24.83	25.22	25.65	26.66
12H	4H	17.58	18.18	18.37	18.98	19.93	23.37	23.96	24.16	24.77	25.72
	6H	17.94	18.43	18.75	19.26	20.21	24.02	24.51	24.83	25.33	26.29
	8H	18.03	18.46	18.85	19.28	20.29	24.26	24.69	25.07	25.51	26.52