

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936512

Luminaire Tested: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936512
REPORT IS A COMBINATION OF REPORTS P933456 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9635.6 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936512
CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P936512

CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4669	4669	4669
5°	4561	5396	6276
10°	4137	7866	10404
15°	3516	10277	12563
20°	2863	11909	12803
25°	2388	12463	12543
30°	2014	12541	12519
35°	1780	12333	12843
40°	1552	12062	13178
45°	1405	11864	13229
50°	1289	11686	13010
55°	1235	11424	12434
60°	1263	10922	11523
65°	1314	10160	10272
70°	1401	8860	8678
75°	1552	7225	6772
80°	1697	5010	4563
85°	1504	2659	2336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13229 cd/sqm



TEST NUMBER: P936512

CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.4
10°-20°	576.9	6.0
20°-30°	1009.1	10.5
30°-40°	1299.0	13.5
40°-50°	1451.0	15.1
50°-60°	1389.7	14.4
60°-70°	1101.3	11.4
70°-80°	647.6	6.7
80°-90°	181.0	1.9
90°-100°	139.1	1.4
100°-110°	365.7	3.8
110°-120°	379.2	3.9
120°-130°	304.1	3.2
130°-140°	238.6	2.5
140°-150°	183.2	1.9
150°-160°	131.9	1.4
160°-170°	80.7	0.8
170°-180°	27.3	0.3
0°-30°	1716.2	17.8
0°-40°	3015.2	31.3
0°-60°	5855.9	60.8
0°-90°	7785.8	80.8
90°-120°	883.9	9.2
90°-150°	1609.9	16.7
90°-180°	1850.0	19.2
0°-180°	9635.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	980	1052	1184	1340	1388	90
15°	734	1356	2284	2770	2857	204
25°	469	1537	2721	2841	2844	216
35°	317	1469	2563	2708	2815	198
45°	217	1171	2265	2595	2712	168
55°	155	744	1922	2233	2294	142
65°	123	395	1427	1605	1628	122
75°	91	243	783	861	864	95
85°	32	74	194	214	217	34
90°	2	5	14	7	7	4
95°	18	72	240	124	84	20
105°	66	100	404	614	572	70
115°	117	142	324	646	737	116
125°	163	182	294	498	587	144
135°	194	214	285	402	456	150
145°	225	239	282	343	370	141
155°	254	261	282	309	318	117
165°	274	278	282	293	296	77
175°	285	285	284	287	287	27
180°	285	285	285	285	285	



TEST NUMBER: P936512
 CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3	1006.3
2.5°	1006.3	1006.3	1012.8	1016.0	1022.4	1025.7	1032.2	1038.7	1058.1	1061.4	1067.8
5°	980.4	993.4	1035.4	1051.6	1096.9	1158.4	1184.3	1226.4	1313.6	1339.5	1355.7
7.5°	941.6	970.7	1074.3	1100.2	1213.4	1375.2	1443.1	1533.7	1672.8	1740.8	1795.8
10°	880.1	941.6	1126.0	1187.4	1372.0	1617.8	1744.0	1870.2	2080.5	2174.4	2210.0
12.5°	812.1	912.5	1181.0	1265.2	1530.5	1889.6	2041.7	2180.8	2420.3	2546.5	2565.9
15°	734.5	870.4	1232.8	1355.7	1698.7	2116.1	2284.4	2455.9	2679.2	2769.7	2792.4
17.5°	666.5	838.0	1281.3	1410.8	1828.2	2320.0	2491.4	2633.9	2815.0	2876.5	2892.7
20°	582.4	786.3	1313.6	1481.9	1964.1	2468.9	2633.9	2743.8	2866.9	2905.7	2912.1
22.5°	520.9	731.2	1333.1	1507.8	2054.6	2559.4	2698.6	2785.9	2870.0	2883.0	2886.3
25°	469.2	669.8	1329.9	1537.0	2132.4	2614.5	2721.3	2785.9	2834.4	2840.9	2840.9
27.5°	420.6	601.8	1316.9	1543.5	2190.6	2627.4	2711.5	2756.8	2779.5	2792.4	2792.4
30°	378.6	537.1	1284.6	1530.5	2216.5	2614.5	2682.3	2705.0	2727.7	2747.1	2756.8
32.5°	346.3	475.6	1236.0	1504.6	2219.6	2582.1	2630.6	2643.5	2675.9	2721.3	2737.4
35°	317.1	414.1	1181.0	1469.0	2200.2	2530.3	2562.7	2575.6	2640.3	2708.3	2730.9
37.5°	287.9	368.8	1109.8	1407.5	2171.2	2468.9	2491.4	2514.1	2614.5	2695.3	2721.3
40°	258.9	330.0	1025.7	1339.5	2125.9	2394.4	2413.8	2449.4	2582.1	2675.9	2701.8
42.5°	236.2	297.7	935.2	1268.4	2067.6	2310.3	2339.4	2391.1	2543.2	2643.5	2672.7
45°	216.8	265.3	838.0	1171.3	1993.2	2222.9	2265.0	2336.2	2497.9	2595.1	2620.9
47.5°	197.4	242.6	737.7	1071.0	1912.3	2135.5	2190.6	2271.5	2436.5	2530.3	2553.0
50°	181.2	220.1	637.5	964.2	1824.9	2041.7	2106.5	2190.6	2358.8	2446.2	2475.3
52.5°	168.3	200.6	543.6	857.4	1724.6	1944.6	2019.1	2106.5	2265.0	2349.1	2368.5
55°	155.4	184.4	462.7	744.2	1621.1	1841.1	1922.0	2006.2	2161.4	2232.6	2245.5
57.5°	148.8	171.5	394.7	637.5	1511.1	1724.6	1815.3	1892.9	2038.5	2093.4	2106.5
60°	139.1	161.8	343.0	546.8	1391.4	1614.6	1692.2	1769.9	1892.9	1938.2	1947.8
62.5°	129.4	155.4	304.2	459.5	1268.4	1485.1	1562.9	1634.0	1737.5	1769.9	1782.8
65°	122.9	148.8	275.0	394.7	1142.2	1349.3	1426.9	1488.4	1572.5	1604.9	1611.3
67.5°	116.4	142.3	252.4	339.8	1016.0	1213.4	1271.6	1329.9	1394.6	1426.9	1430.2
70°	106.8	135.9	233.0	300.9	886.6	1058.1	1106.6	1168.0	1219.9	1236.0	1245.8
72.5°	100.3	126.2	220.1	271.8	753.9	909.3	954.6	990.1	1035.4	1051.6	1051.6
75°	90.6	113.3	207.1	242.6	618.1	744.2	783.1	818.6	854.2	860.7	851.0
77.5°	80.9	100.3	178.0	203.8	482.1	588.9	621.2	640.7	669.8	676.3	679.5
80°	68.0	87.4	139.1	158.5	349.4	433.5	456.2	472.5	498.3	498.3	504.8
82.5°	51.8	68.0	100.3	113.3	236.2	297.7	317.1	326.8	343.0	343.0	343.0
85°	32.3	42.1	64.7	74.4	142.3	181.2	194.2	197.4	210.3	213.6	213.6
87.5°	16.2	22.7	42.1	45.3	74.4	93.9	93.9	100.3	100.3	97.0	93.9
90°	1.9	3.4	5.0	5.4	8.4	12.5	14.5	12.9	9.7	7.3	7.3
92.5°	7.6	20.6	33.7	37.0	52.0	72.0	81.9	71.8	51.6	36.4	35.0
95°	18.4	42.2	66.1	72.0	127.8	202.3	239.6	213.8	162.2	123.5	119.1
97.5°	31.8	52.9	73.8	79.1	172.2	296.4	358.5	342.2	309.6	285.2	276.9
100°	42.2	61.2	80.2	85.0	188.3	326.1	395.0	396.3	398.7	400.5	390.5
102.5°	51.0	68.7	86.5	90.9	195.8	335.6	405.4	426.2	467.7	498.8	490.3
105°	65.9	81.0	96.1	99.8	201.3	336.6	404.3	450.8	544.0	613.8	609.2
107.5°	81.2	95.2	109.3	112.8	202.3	321.6	381.3	446.2	576.1	673.5	674.6
110°	91.6	104.2	116.9	120.1	200.8	308.3	362.1	434.7	579.9	688.8	693.6



TEST NUMBER: P936512

CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	101.7	113.8	125.8	128.9	200.9	296.7	344.7	419.0	567.6	679.0	686.4
115°	117.0	128.1	139.3	142.1	202.7	283.5	323.8	395.4	538.6	646.0	656.1
117.5°	132.1	142.3	152.4	155.0	206.5	275.1	309.5	374.1	503.2	600.2	611.5
120°	140.9	150.5	160.0	162.4	209.6	272.4	303.7	362.7	480.8	569.3	580.2
122.5°	149.5	159.2	168.8	171.2	214.0	270.8	299.3	352.5	458.8	538.5	549.3
125°	162.8	171.6	180.3	182.5	219.9	269.7	294.5	339.7	430.0	497.7	507.6
127.5°	173.5	182.3	191.2	193.4	225.8	268.9	290.5	329.3	406.9	465.0	473.4
130°	179.2	188.8	198.3	200.7	230.1	269.4	289.0	323.5	392.5	444.3	452.0
132.5°	185.2	194.7	204.2	206.6	233.6	269.7	287.7	318.5	380.3	426.7	433.6
135°	194.0	202.7	211.4	213.6	237.5	269.4	285.4	311.3	363.0	401.8	407.7
137.5°	203.0	211.6	220.2	222.4	243.2	271.0	285.0	306.9	350.6	383.4	388.2
140°	210.4	218.4	226.3	228.3	246.7	271.3	283.6	302.6	340.3	368.6	373.2
142.5°	216.2	223.5	230.9	232.7	249.7	272.4	283.6	300.3	333.5	358.3	362.2
145°	225.0	231.4	237.8	239.4	253.5	272.4	281.7	295.3	322.5	342.8	345.8
147.5°	233.8	240.1	246.3	247.8	259.1	274.2	281.7	292.4	313.8	329.7	332.2
150°	239.6	245.2	250.8	252.2	262.0	275.1	281.7	290.7	308.8	322.3	324.3
152.5°	245.5	249.7	254.0	255.1	264.0	275.8	281.7	289.4	304.8	316.3	317.9
155°	254.3	257.5	260.6	261.4	268.2	277.2	281.7	287.9	300.1	309.3	310.2
157.5°	260.8	263.9	266.9	267.7	272.4	278.6	281.7	286.5	296.0	303.1	303.8
160°	265.2	267.6	270.0	270.5	274.3	279.2	281.7	285.8	294.0	300.1	300.5
162.5°	269.6	271.4	273.1	273.6	276.3	279.9	281.7	285.2	292.1	297.2	297.6
165°	274.5	276.1	277.7	278.1	279.3	281.0	281.7	284.2	289.1	292.8	293.2
167.5°	278.9	279.6	280.4	280.6	281.6	283.0	283.6	285.3	288.5	290.9	291.1
170°	281.7	282.5	283.3	283.5	283.5	283.6	283.6	285.3	288.5	290.9	290.9
172.5°	283.3	283.5	283.6	283.6	283.6	283.6	283.6	284.9	287.5	289.4	289.2
175°	285.4	285.4	285.4	285.4	284.8	284.0	283.6	284.4	286.0	287.3	287.3
177.5°	285.4	285.4	285.4	285.4	284.9	284.3	284.0	284.7	285.9	286.9	286.7
180°	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4	285.4



TEST NUMBER: P936512

CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1006.3	1006.3
2.5°	1074.3	1067.8
5°	1381.6	1388.1
7.5°	1860.5	1857.3
10°	2313.5	2342.7
12.5°	2643.5	2650.0
15°	2844.2	2857.1
17.5°	2921.8	2925.1
20°	2925.1	2918.6
22.5°	2889.5	2883.0
25°	2847.4	2844.2
27.5°	2808.5	2811.8
30°	2792.4	2802.1
32.5°	2792.4	2808.5
35°	2798.9	2815.0
37.5°	2795.6	2815.0
40°	2782.7	2805.4
42.5°	2747.1	2763.3
45°	2692.1	2711.5
47.5°	2620.9	2633.9
50°	2530.3	2543.2
52.5°	2417.1	2420.3
55°	2281.1	2294.1
57.5°	2135.5	2138.8
60°	1973.8	1983.5
62.5°	1802.3	1802.3
65°	1621.1	1627.6
67.5°	1433.4	1449.6
70°	1242.5	1245.8
72.5°	1054.9	1054.9
75°	860.7	863.9
77.5°	676.3	676.3
80°	501.5	504.8
82.5°	346.3	352.7
85°	216.8	216.8
87.5°	100.3	90.6
90°	7.3	7.3
92.5°	29.2	23.3
95°	101.6	84.0
97.5°	243.4	210.0
100°	350.8	311.0
102.5°	456.3	422.3
105°	590.9	572.5
107.5°	679.0	683.4
110°	712.6	731.7



TEST NUMBER: P936512

CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	715.7	744.9
115°	696.7	737.3
117.5°	656.5	701.5
120°	624.0	667.8
122.5°	592.4	635.5
125°	547.4	587.2
127.5°	506.9	540.4
130°	483.0	513.9
132.5°	461.4	489.1
135°	431.6	455.5
137.5°	407.8	427.4
140°	391.5	409.8
142.5°	378.0	393.7
145°	357.7	369.6
147.5°	342.1	352.0
150°	332.3	340.3
152.5°	323.9	329.9
155°	314.2	318.3
157.5°	306.7	309.5
160°	302.1	303.7
162.5°	299.1	300.7
165°	294.8	296.5
167.5°	291.8	292.4
170°	290.9	290.9
172.5°	288.6	288.0
175°	287.3	287.3
177.5°	286.0	285.4
180°	285.4	285.4



TEST NUMBER: P936512
 CATALOG NUMBER: SQ4-FB-025U-125D-830-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.78	10.08	9.41	10.74	11.48	21.96	23.26	22.59	23.92	24.66
	3H	9.52	10.70	10.16	11.36	12.14	23.83	25.01	24.48	25.67	26.45
	4H	9.84	10.95	10.50	11.62	12.42	24.50	25.61	25.16	26.28	27.08
	6H	10.11	11.14	10.79	11.82	12.63	24.95	25.98	25.63	26.66	27.47
	8H	10.19	11.18	10.88	11.88	12.69	25.08	26.07	25.77	26.77	27.59
	12H	10.22	11.17	10.92	11.86	12.71	25.17	26.11	25.86	26.81	27.65
4H	2H	16.05	17.16	16.72	17.83	18.63	22.29	23.40	22.95	24.07	24.87
	3H	17.66	18.59	18.34	19.30	20.12	24.37	25.31	25.05	26.02	26.83
	4H	17.77	18.62	18.47	19.33	20.18	25.16	26.01	25.86	26.72	27.57
	6H	17.81	18.55	18.52	19.29	20.14	25.72	26.47	26.44	27.20	28.06
	8H	17.80	18.49	18.52	19.23	20.09	25.90	26.59	26.62	27.33	28.19
	12H	17.77	18.40	18.52	19.16	20.03	26.01	26.64	26.76	27.40	28.27
8H	4H	19.25	19.95	19.97	20.68	21.55	25.26	25.95	25.98	26.69	27.55
	6H	19.51	20.09	20.27	20.87	21.74	25.91	26.48	26.66	27.26	28.13
	8H	19.54	20.06	20.30	20.83	21.72	26.13	26.65	26.90	27.43	28.31
	12H	19.53	19.99	20.30	20.75	21.70	26.30	26.75	27.07	27.52	28.47
12H	4H	19.42	20.04	20.16	20.80	21.68	25.23	25.86	25.97	26.62	27.49
	6H	19.78	20.30	20.54	21.08	21.96	25.89	26.41	26.66	27.19	28.07
	8H	19.87	20.33	20.64	21.10	22.04	26.15	26.60	26.91	27.37	28.32