

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936550

Luminaire Tested: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936550
REPORT IS A COMBINATION OF REPORTS P933440 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4046.3 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936550
CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P936550

CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3920	3920	3920
5°	3826	4529	5271
10°	3466	6596	8738
15°	2943	8612	10551
20°	2394	9973	10753
25°	1995	10428	10535
30°	1679	10486	10515
35°	1482	10303	10786
40°	1290	10069	11067
45°	1166	9895	11111
50°	1067	9736	10927
55°	1018	9507	10443
60°	1041	9078	9679
65°	1075	8429	8626
70°	1137	7336	7289
75°	1249	5966	5688
80°	1334	4123	3833
85°	1126	2175	1963

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 11111 cd/sqm



TEST NUMBER: P936550

CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	1.4
10°-20°	242.3	6.0
20°-30°	423.8	10.5
30°-40°	545.5	13.5
40°-50°	609.3	15.1
50°-60°	583.6	14.4
60°-70°	462.5	11.4
70°-80°	271.9	6.7
80°-90°	76.0	1.9
90°-100°	58.4	1.4
100°-110°	153.6	3.8
110°-120°	159.2	3.9
120°-130°	127.7	3.2
130°-140°	100.2	2.5
140°-150°	76.9	1.9
150°-160°	55.4	1.4
160°-170°	33.9	0.8
170°-180°	11.4	0.3
0°-30°	720.7	17.8
0°-40°	1266.2	31.3
0°-60°	2459.1	60.8
0°-90°	3269.5	80.8
90°-120°	371.2	9.2
90°-150°	676.1	16.7
90°-180°	777.0	19.2
0°-180°	4046.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	422	422	422	422	422	
5°	412	442	497	562	583	38
15°	308	569	959	1163	1200	86
25°	197	645	1143	1193	1194	91
35°	133	617	1076	1137	1182	83
45°	91	492	951	1090	1139	70
55°	65	312	807	938	963	59
65°	52	166	599	674	683	51
75°	38	102	329	361	363	40
85°	14	31	82	90	91	14
90°	1	2	6	3	3	2
95°	8	30	101	52	35	9
105°	28	42	170	258	240	29
115°	49	60	136	271	310	49
125°	68	77	124	209	247	61
135°	82	90	120	169	191	63
145°	94	100	118	144	155	59
155°	107	110	118	130	134	49
165°	115	117	118	123	124	33
175°	120	120	119	121	121	11
180°	120	120	120	120	120	



TEST NUMBER: P936550
 CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	422.5	422.5	422.5	422.5	422.5	422.5	422.5	422.5	422.5	422.5	422.5
2.5°	422.5	422.5	425.3	426.6	429.4	430.7	433.5	436.2	444.3	445.7	448.4
5°	411.7	417.2	434.8	441.6	460.6	486.5	497.3	515.0	551.7	562.5	569.3
7.5°	395.4	407.6	451.1	462.0	509.5	577.4	606.0	644.1	702.5	731.0	754.1
10°	369.5	395.4	472.8	498.7	576.1	679.3	732.3	785.3	873.7	913.1	928.0
12.5°	341.0	383.2	495.9	531.3	642.7	793.5	857.4	915.8	1016.4	1069.4	1077.5
15°	308.4	365.5	517.7	569.3	713.3	888.6	959.3	1031.3	1125.1	1163.1	1172.6
17.5°	279.9	352.0	538.1	592.5	767.7	974.2	1046.2	1106.1	1182.1	1208.0	1214.7
20°	244.6	330.2	551.7	622.3	824.8	1036.8	1106.1	1152.2	1203.9	1220.2	1222.9
22.5°	218.7	307.1	559.8	633.2	862.8	1074.7	1133.2	1169.9	1205.2	1210.7	1212.0
25°	197.1	281.3	558.5	645.4	895.4	1097.9	1142.7	1169.9	1190.3	1193.0	1193.0
27.5°	176.7	252.7	553.0	648.1	919.8	1103.3	1138.7	1157.7	1167.2	1172.6	1172.6
30°	159.0	225.6	539.5	642.7	930.8	1097.9	1126.4	1135.9	1145.4	1153.6	1157.7
32.5°	145.4	199.7	519.1	631.8	932.1	1084.3	1104.7	1110.1	1123.7	1142.7	1149.5
35°	133.1	173.9	495.9	616.9	923.9	1062.5	1076.1	1081.6	1108.7	1137.3	1146.8
37.5°	120.9	154.9	466.1	591.1	911.7	1036.8	1046.2	1055.8	1097.9	1131.8	1142.7
40°	108.7	138.6	430.7	562.5	892.7	1005.4	1013.6	1028.6	1084.3	1123.7	1134.6
42.5°	99.2	125.0	392.7	532.6	868.2	970.2	982.4	1004.2	1068.0	1110.1	1122.4
45°	91.1	111.5	352.0	491.8	837.0	933.5	951.2	981.0	1049.0	1089.8	1100.6
47.5°	82.9	101.9	309.8	449.8	803.0	896.8	919.8	953.9	1023.1	1062.5	1072.1
50°	76.1	92.4	267.6	404.9	766.3	857.4	884.6	919.8	990.5	1027.2	1039.5
52.5°	70.7	84.2	228.3	360.1	724.2	816.6	847.9	884.6	951.2	986.5	994.6
55°	65.2	77.4	194.3	312.5	680.7	773.1	807.1	842.4	907.6	937.5	943.0
57.5°	62.5	72.0	165.7	267.6	634.5	724.2	762.3	794.9	856.0	879.1	884.6
60°	58.5	67.9	144.1	229.7	584.3	678.1	710.7	743.3	794.9	813.9	817.9
62.5°	54.4	65.2	127.8	193.0	532.6	623.7	656.3	686.2	729.7	743.3	748.6
65°	51.6	62.5	115.5	165.7	479.6	566.6	599.2	625.1	660.4	674.0	676.7
67.5°	48.9	59.8	106.0	142.7	426.6	509.5	534.0	558.5	585.6	599.2	600.6
70°	44.8	57.1	97.8	126.4	372.3	444.3	464.7	490.5	512.2	519.1	523.2
72.5°	42.2	53.0	92.4	114.1	316.6	381.8	400.9	415.8	434.8	441.6	441.6
75°	38.1	47.5	87.0	101.9	259.5	312.5	328.8	343.8	358.7	361.4	357.3
77.5°	34.0	42.2	74.8	85.6	202.4	247.3	260.9	269.0	281.3	283.9	285.3
80°	28.5	36.7	58.5	66.6	146.7	182.0	191.6	198.3	209.3	209.3	212.0
82.5°	21.8	28.5	42.2	47.5	99.2	125.0	133.1	137.2	144.1	144.1	144.1
85°	13.6	17.7	27.1	31.2	59.8	76.1	81.5	82.9	88.3	89.7	89.7
87.5°	6.8	9.5	17.7	19.0	31.2	39.4	39.4	42.2	42.2	40.8	39.4
90°	0.8	1.4	2.1	2.2	3.5	5.2	6.1	5.5	4.1	3.1	3.1
92.5°	3.2	8.7	14.1	15.5	21.8	30.3	34.4	30.2	21.7	15.3	14.6
95°	7.7	17.7	27.8	30.3	53.7	85.0	100.6	89.8	68.1	51.9	50.0
97.5°	13.3	22.2	31.0	33.2	72.4	124.5	150.6	143.7	130.0	119.7	116.2
100°	17.7	25.7	33.7	35.7	79.1	137.0	165.9	166.4	167.4	168.1	164.0
102.5°	21.4	28.8	36.4	38.2	82.2	140.9	170.2	179.0	196.4	209.5	205.9
105°	27.7	34.0	40.3	41.9	84.6	141.3	169.8	189.3	228.5	257.8	255.8
107.5°	34.1	40.0	45.9	47.4	85.0	135.1	160.1	187.4	241.9	282.9	283.4
110°	38.5	43.8	49.1	50.4	84.3	129.5	152.1	182.6	243.5	289.3	291.3



TEST NUMBER: P936550

CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	42.7	47.8	52.8	54.1	84.3	124.6	144.8	176.0	238.4	285.2	288.3
115°	49.1	53.8	58.5	59.7	85.1	119.1	136.0	166.1	226.2	271.3	275.5
117.5°	55.5	59.7	64.0	65.0	86.7	115.6	130.0	157.1	211.3	252.1	256.8
120°	59.2	63.2	67.2	68.2	87.9	114.3	127.5	152.3	202.0	239.1	243.7
122.5°	62.8	66.8	70.8	71.9	89.8	113.7	125.7	148.0	192.6	226.1	230.6
125°	68.3	72.0	75.7	76.7	92.3	113.2	123.7	142.6	180.6	209.0	213.2
127.5°	72.8	76.6	80.3	81.3	94.8	112.9	122.0	138.3	170.9	195.3	198.8
130°	75.2	79.3	83.3	84.3	96.7	113.1	121.3	135.9	164.9	186.6	189.8
132.5°	77.8	81.8	85.8	86.8	98.1	113.2	120.8	133.8	159.7	179.2	182.1
135°	81.5	85.1	88.8	89.7	99.7	113.1	119.8	130.6	152.4	168.7	171.2
137.5°	85.3	88.9	92.5	93.4	102.1	113.8	119.6	128.8	147.2	161.0	163.1
140°	88.4	91.7	95.1	95.9	103.6	113.9	119.1	127.0	142.9	154.8	156.7
142.5°	90.8	93.9	96.9	97.7	104.9	114.3	119.1	126.1	140.0	150.5	152.2
145°	94.5	97.2	99.9	100.5	106.5	114.3	118.3	124.0	135.4	144.0	145.3
147.5°	98.2	100.8	103.4	104.1	108.8	115.2	118.3	122.8	131.8	138.5	139.6
150°	100.6	102.9	105.4	105.9	110.0	115.6	118.3	122.1	129.7	135.4	136.2
152.5°	103.1	104.9	106.6	107.1	110.8	115.8	118.3	121.5	128.0	132.9	133.5
155°	106.8	108.1	109.4	109.8	112.6	116.4	118.3	120.9	126.1	129.9	130.3
157.5°	109.5	110.8	112.1	112.4	114.3	117.0	118.3	120.3	124.3	127.3	127.6
160°	111.4	112.3	113.4	113.6	115.2	117.2	118.3	120.0	123.4	126.0	126.2
162.5°	113.2	113.9	114.7	114.9	116.0	117.6	118.3	119.7	122.6	124.8	124.9
165°	115.2	115.9	116.6	116.8	117.2	118.0	118.3	119.3	121.4	122.9	123.1
167.5°	117.1	117.4	117.7	117.8	118.2	118.8	119.1	119.7	121.1	122.1	122.2
170°	118.3	118.6	118.9	119.0	119.0	119.1	119.1	119.7	121.1	122.1	122.1
172.5°	118.9	119.0	119.1	119.1	119.1	119.1	119.1	119.6	120.7	121.5	121.4
175°	119.8	119.8	119.8	119.8	119.6	119.2	119.1	119.4	120.1	120.6	120.6
177.5°	119.8	119.8	119.8	119.8	119.6	119.4	119.2	119.5	120.0	120.4	120.4
180°	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8	119.8



TEST NUMBER: P936550

CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	422.5	422.5
2.5°	451.1	448.4
5°	580.2	582.9
7.5°	781.3	780.0
10°	971.5	983.8
12.5°	1110.1	1112.8
15°	1194.4	1199.8
17.5°	1227.0	1228.3
20°	1228.3	1225.6
22.5°	1213.3	1210.7
25°	1195.7	1194.4
27.5°	1179.4	1180.7
30°	1172.6	1176.7
32.5°	1172.6	1179.4
35°	1175.4	1182.1
37.5°	1174.0	1182.1
40°	1168.5	1178.0
42.5°	1153.6	1160.3
45°	1130.5	1138.7
47.5°	1100.6	1106.1
50°	1062.5	1068.0
52.5°	1015.0	1016.4
55°	957.9	963.4
57.5°	896.8	898.2
60°	828.9	833.0
62.5°	756.8	756.8
65°	680.7	683.4
67.5°	601.9	608.8
70°	521.8	523.2
72.5°	442.9	442.9
75°	361.4	362.8
77.5°	283.9	283.9
80°	210.6	212.0
82.5°	145.4	148.1
85°	91.1	91.1
87.5°	42.2	38.1
90°	3.1	3.1
92.5°	12.2	9.8
95°	42.7	35.3
97.5°	102.2	88.2
100°	147.4	130.6
102.5°	191.6	177.3
105°	248.2	240.5
107.5°	285.2	287.1
110°	299.3	307.3



TEST NUMBER: P936550
CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	300.6	312.8
115°	292.6	309.6
117.5°	275.7	294.6
120°	262.1	280.4
122.5°	248.8	266.9
125°	229.9	246.6
127.5°	212.9	226.9
130°	202.8	215.8
132.5°	193.8	205.4
135°	181.3	191.4
137.5°	171.3	179.6
140°	164.4	172.1
142.5°	158.8	165.3
145°	150.2	155.2
147.5°	143.7	147.8
150°	139.6	142.9
152.5°	136.0	138.6
155°	132.0	133.7
157.5°	128.8	130.0
160°	126.9	127.5
162.5°	125.6	126.2
165°	123.8	124.5
167.5°	122.5	122.8
170°	122.1	122.1
172.5°	121.2	120.9
175°	120.6	120.6
177.5°	120.1	119.8
180°	119.8	119.8



TEST NUMBER: P936550
 CATALOG NUMBER: SQ4-FB-025U-125D-930-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.16	9.46	8.79	10.11	10.86	21.30	22.60	21.93	23.25	24.00
	3H	8.90	10.08	9.54	10.74	11.52	23.16	24.33	23.80	24.99	25.78
	4H	9.22	10.33	9.88	11.00	11.80	23.81	24.92	24.47	25.60	26.39
	6H	9.49	10.52	10.17	11.20	12.01	24.25	25.28	24.93	25.97	26.78
	8H	9.57	10.56	10.26	11.26	12.07	24.38	25.36	25.07	26.07	26.88
	12H	9.61	10.55	10.30	11.24	12.09	24.46	25.40	25.15	26.09	26.94
4H	2H	15.40	16.52	16.07	17.19	17.98	21.63	22.74	22.29	23.41	24.21
	3H	17.01	17.95	17.69	18.66	19.47	23.70	24.63	24.38	25.34	26.16
	4H	17.13	17.98	17.82	18.69	19.54	24.47	25.32	25.17	26.04	26.88
	6H	17.16	17.91	17.88	18.65	19.50	25.03	25.77	25.74	26.51	27.36
	8H	17.15	17.85	17.87	18.58	19.45	25.19	25.89	25.91	26.62	27.49
	12H	17.13	17.76	17.88	18.52	19.39	25.30	25.93	26.04	26.69	27.56
8H	4H	18.60	19.29	19.32	20.03	20.90	24.57	25.27	25.29	26.00	26.87
	6H	18.86	19.44	19.61	20.22	21.09	25.21	25.79	25.96	26.57	27.43
	8H	18.89	19.40	19.65	20.18	21.07	25.43	25.94	26.19	26.72	27.61
	12H	18.88	19.33	19.64	20.10	21.05	25.59	26.04	26.35	26.81	27.75
12H	4H	18.76	19.39	19.50	20.15	21.02	24.55	25.17	25.29	25.93	26.81
	6H	19.12	19.64	19.89	20.42	21.30	25.20	25.72	25.96	26.49	27.38
	8H	19.21	19.67	19.98	20.44	21.38	25.44	25.90	26.21	26.67	27.61