

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562710

Luminaire Tested: **SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562710  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3949.3 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562710  
CATALOG NUMBER: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562710

CATALOG NUMBER: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	36	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	21	19	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5294	5294	5294
5°	5334	5299	5280
10°	5321	5296	5281
15°	5293	5293	5288
20°	5258	5273	5273
25°	5208	5247	5230
30°	5146	5207	5185
35°	5068	5146	5110
40°	4985	5055	5004
45°	4894	4929	4852
50°	4767	4767	4689
55°	4615	4555	4486
60°	4392	4303	4235
65°	4061	3978	3943
70°	3555	3582	3569
75°	2859	3162	3183
80°	2035	2683	2710
85°	1239	2255	2255



TEST NUMBER: P562710

CATALOG NUMBER: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.3	1.4
10°-20°	155.8	3.9
20°-30°	236.0	6.0
30°-40°	282.9	7.2
40°-50°	288.5	7.3
50°-60°	251.8	6.4
60°-70°	180.3	4.6
70°-80°	92.9	2.4
80°-90°	24.4	0.6
90°-100°	172.5	4.4
100°-110°	474.5	12.0
110°-120°	489.8	12.4
120°-130°	392.4	9.9
130°-140°	308.2	7.8
140°-150°	236.2	6.0
150°-160°	169.8	4.3
160°-170°	103.8	2.6
170°-180°	35.0	0.9
0°-30°	446.1	11.3
0°-40°	729.1	18.5
0°-60°	1269.4	32.1
0°-90°	1567.0	39.7
90°-120°	1136.8	28.8
90°-150°	2073.6	52.5
90°-180°	2382.0	60.3
0°-180°	3949.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	576	570	572	571	570	55
15°	554	550	554	554	554	156
25°	512	508	515	514	514	235
35°	450	449	457	454	454	281
45°	375	374	378	373	372	289
55°	287	283	283	279	279	256
65°	186	182	182	181	181	184
75°	80	84	89	89	89	87
85°	12	18	21	22	21	16
90°	1	3	5	7	7	2
95°	26	94	305	130	83	27
105°	85	130	523	796	743	89
115°	150	183	419	835	948	148
125°	207	236	380	644	754	185
135°	250	277	370	520	589	193
145°	289	308	364	444	478	181
155°	327	337	362	399	410	150
165°	353	358	363	378	380	100
175°	366	366	364	369	368	35
180°	366	366	366	366	366	

TEST NUMBER: P562710

CATALOG NUMBER: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	573.8	573.8	573.8	573.8	573.8
2.5°	577.2	572.2	573.8	572.5	570.4
5°	575.9	570.2	572.2	570.6	570.1
7.5°	571.8	566.1	568.7	567.6	567.1
10°	568.0	562.2	565.3	564.2	563.7
12.5°	562.9	557.6	561.1	560.0	559.9
15°	554.1	549.5	554.1	554.1	553.6
17.5°	543.2	538.9	543.9	544.3	543.9
20°	535.5	530.9	537.1	536.6	537.1
22.5°	526.2	522.4	529.1	527.7	528.2
25°	511.6	508.0	515.4	513.8	513.8
27.5°	494.4	491.8	499.8	498.1	498.1
30°	483.0	480.4	488.8	486.7	486.7
32.5°	470.2	468.4	476.5	473.9	473.9
35°	450.0	449.0	456.9	453.7	453.7
37.5°	429.2	428.2	435.5	431.6	430.4
40°	413.9	413.4	419.7	415.5	415.5
42.5°	398.6	398.1	403.6	398.5	398.5
45°	375.1	374.1	377.8	372.9	371.9
47.5°	349.5	348.4	350.8	345.5	345.0
50°	332.1	331.0	332.1	327.3	326.7
52.5°	314.2	312.3	312.5	307.7	307.6
55°	286.9	283.3	283.2	278.9	278.9
57.5°	258.0	253.2	253.6	250.0	249.5
60°	238.0	232.8	233.2	230.0	229.5
62.5°	218.5	212.4	213.7	210.1	210.0
65°	186.0	181.8	182.2	180.6	180.6
67.5°	154.7	150.9	153.7	152.4	152.3
70°	131.8	129.2	132.8	132.8	132.3
72.5°	110.5	110.4	115.0	115.0	115.3
75°	80.2	83.9	88.7	89.3	89.3
77.5°	53.6	60.0	65.3	65.6	65.5
80°	38.3	45.5	50.5	51.5	51.0
82.5°	25.9	33.6	37.7	38.8	38.3
85°	11.7	17.9	21.3	21.8	21.3
87.5°	3.6	7.8	9.6	9.9	9.1
90°	0.8	3.1	5.4	7.0	7.0
92.5°	10.7	45.9	79.5	30.5	25.1
95°	25.7	94.1	305.0	130.4	83.3
97.5°	41.9	104.4	465.4	358.6	253.0
100°	53.7	110.7	515.9	520.7	424.8
102.5°	64.9	118.3	528.9	646.0	558.0
105°	84.8	130.5	522.9	796.3	743.0
107.5°	103.8	145.5	493.1	869.9	885.7
110°	117.5	155.5	470.7	888.2	943.0



TEST NUMBER: P562710

CATALOG NUMBER: SQ4-PC3-075U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	129.9	166.8	448.3	876.4	959.8
115°	150.2	182.9	419.4	835.1	947.7
117.5°	169.5	199.6	401.0	777.1	904.4
120°	181.3	210.2	392.9	733.6	865.2
122.5°	191.9	220.8	387.3	695.5	820.4
125°	207.0	235.9	380.5	643.6	753.9
127.5°	221.3	248.8	376.0	600.4	697.1
130°	228.8	256.9	373.5	574.7	662.9
132.5°	237.5	265.6	371.6	552.1	631.8
135°	249.8	277.1	369.6	520.5	589.0
137.5°	261.3	286.7	367.9	495.0	551.5
140°	270.0	293.6	367.2	478.1	529.1
142.5°	277.5	299.2	366.0	463.0	506.7
145°	288.7	308.4	364.1	443.5	477.7
147.5°	300.6	317.7	363.2	426.2	453.6
150°	308.1	323.3	362.6	416.7	438.0
152.5°	315.0	329.0	362.0	408.6	426.2
155°	326.8	337.4	361.8	398.6	410.0
157.5°	335.3	344.0	361.8	390.5	398.4
160°	341.6	348.4	361.8	386.1	392.1
162.5°	346.5	352.2	362.4	382.3	387.2
165°	353.2	357.8	363.4	378.2	380.5
167.5°	357.9	361.4	364.1	374.7	375.3
170°	361.0	363.3	364.1	373.5	373.5
172.5°	363.5	364.6	364.1	371.6	371.0
175°	365.7	366.4	364.1	368.8	368.0
177.5°	366.3	366.3	363.8	367.5	366.3
180°	365.7	365.7	365.7	365.7	365.7

(END OF REPORT)