

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562604

Luminaire Tested: **SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562604
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7477.6 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 58.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562604
CATALOG NUMBER: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562604

CATALOG NUMBER: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	49	48	47	42
2	89	82	76	70	82	75	70	66	64	60	57	53	51	48	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	34	32	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6279	6279	6279
5°	6327	6286	6263
10°	6312	6282	6264
15°	6278	6278	6272
20°	6237	6256	6256
25°	6178	6223	6204
30°	6103	6177	6150
35°	6012	6105	6062
40°	5913	5996	5935
45°	5805	5847	5756
50°	5654	5654	5563
55°	5474	5403	5322
60°	5210	5105	5024
65°	4815	4719	4677
70°	4216	4250	4232
75°	3392	3752	3773
80°	2410	3180	3214
85°	1466	2668	2668



TEST NUMBER: P562604

CATALOG NUMBER: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	1.7
10°-20°	369.7	4.9
20°-30°	559.9	7.5
30°-40°	671.2	9.0
40°-50°	684.4	9.2
50°-60°	597.4	8.0
60°-70°	427.7	5.7
70°-80°	220.3	2.9
80°-90°	57.9	0.8
90°-100°	276.5	3.7
100°-110°	751.0	10.0
110°-120°	772.2	10.3
120°-130°	617.4	8.3
130°-140°	485.1	6.5
140°-150°	372.0	5.0
150°-160°	267.5	3.6
160°-170°	163.6	2.2
170°-180°	55.1	0.7
0°-30°	1058.4	14.2
0°-40°	1729.6	23.1
0°-60°	3011.4	40.3
0°-90°	3717.3	49.7
90°-120°	1799.7	24.1
90°-150°	3274.1	43.8
90°-180°	3760.0	50.3
0°-180°	7477.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1361	1361	1361	1361	1361	
5°	1366	1353	1358	1354	1352	130
15°	1315	1304	1315	1315	1313	371
25°	1214	1205	1223	1219	1219	559
35°	1068	1065	1084	1076	1076	668
45°	890	887	896	885	882	685
55°	681	672	672	662	662	607
65°	441	431	432	428	428	436
75°	190	199	210	212	212	206
85°	28	42	50	52	50	38
90°	2	7	13	17	17	4
95°	41	151	482	210	141	43
105°	133	208	826	1258	1183	142
115°	237	288	661	1315	1498	234
125°	326	371	598	1008	1189	291
135°	393	436	582	821	926	304
145°	454	486	574	698	750	285
155°	513	531	570	626	644	237
165°	556	563	572	596	598	157
175°	576	578	574	581	580	55
180°	576	576	576	576	576	

TEST NUMBER: P562604

CATALOG NUMBER: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.2	1361.2	1361.2	1361.2	1361.2
2.5°	1369.3	1357.5	1361.2	1358.1	1353.2
5°	1366.3	1352.7	1357.5	1353.7	1352.4
7.5°	1356.5	1342.9	1349.1	1346.6	1345.4
10°	1347.4	1333.8	1341.1	1338.5	1337.3
12.5°	1335.3	1322.7	1331.0	1328.5	1328.2
15°	1314.6	1303.5	1314.6	1314.6	1313.3
17.5°	1288.6	1278.5	1290.4	1291.1	1290.4
20°	1270.5	1259.4	1274.3	1273.0	1274.3
22.5°	1248.3	1239.2	1255.1	1251.9	1253.1
25°	1213.8	1205.1	1222.6	1218.8	1218.8
27.5°	1172.9	1166.8	1185.8	1181.8	1181.8
30°	1145.7	1139.6	1159.6	1154.5	1154.5
32.5°	1115.5	1111.3	1130.3	1124.3	1124.3
35°	1067.6	1065.1	1084.0	1076.4	1076.4
37.5°	1018.2	1015.9	1033.0	1023.9	1020.9
40°	981.9	980.6	995.7	985.6	985.6
42.5°	945.6	944.3	957.4	945.3	945.3
45°	889.8	887.4	896.2	884.8	882.3
47.5°	829.1	826.6	832.1	819.7	818.5
50°	787.8	785.3	787.8	776.4	775.2
52.5°	745.4	741.0	741.4	730.0	729.8
55°	680.6	672.0	671.8	661.7	661.7
57.5°	612.1	600.7	601.7	593.1	591.9
60°	564.7	552.3	553.3	545.7	544.5
62.5°	518.3	504.0	506.9	498.4	498.1
65°	441.1	431.3	432.3	428.5	428.5
67.5°	367.0	357.9	364.5	361.5	361.2
70°	312.6	306.4	315.1	315.1	313.8
72.5°	262.2	261.9	272.8	272.8	273.5
75°	190.3	198.9	210.5	211.7	211.7
77.5°	127.0	142.3	155.0	155.5	155.3
80°	90.7	108.0	119.7	122.2	121.0
82.5°	61.5	79.7	89.5	92.0	90.7
85°	27.7	42.5	50.4	51.6	50.4
87.5°	8.4	18.4	22.8	23.5	21.5
90°	1.9	7.3	13.0	16.7	16.7
92.5°	16.7	75.7	131.5	56.5	47.8
95°	40.7	151.2	481.5	209.5	140.7
97.5°	67.4	167.0	738.1	574.3	403.3
100°	85.2	177.5	816.7	827.8	668.5
102.5°	103.0	188.1	837.4	1023.8	883.3
105°	133.3	207.6	825.9	1257.5	1183.3
107.5°	164.8	230.4	778.1	1378.2	1398.9
110°	187.0	246.8	742.6	1402.0	1490.7



TEST NUMBER: P562604

CATALOG NUMBER: SQ4-PC3-050U-050D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.3	263.1	707.0	1382.3	1515.9
115°	237.0	287.7	661.1	1315.2	1498.1
117.5°	265.9	314.4	631.8	1220.2	1426.3
120°	285.2	332.3	618.5	1156.5	1361.1
122.5°	301.5	348.6	609.6	1092.6	1290.0
125°	325.9	371.2	598.1	1007.8	1188.9
127.5°	347.8	392.7	591.8	943.5	1098.9
130°	361.1	404.6	588.9	903.2	1042.6
132.5°	374.4	417.9	585.9	868.7	992.2
135°	392.6	436.0	581.5	820.9	925.9
137.5°	412.2	451.7	579.2	778.7	867.0
140°	424.1	462.1	577.8	751.8	831.5
142.5°	435.9	471.0	576.3	730.8	797.4
145°	453.7	486.3	574.1	697.5	750.0
147.5°	473.7	501.6	572.2	671.3	712.6
150°	487.0	510.6	572.2	656.3	688.9
152.5°	497.4	518.0	570.7	642.8	669.6
155°	513.0	531.1	570.4	626.3	644.4
157.5°	528.1	542.3	570.4	615.1	628.9
160°	537.0	549.7	570.4	607.6	618.5
162.5°	545.9	555.7	571.8	601.7	609.6
165°	555.5	562.8	572.2	596.3	598.1
167.5°	565.5	569.2	574.1	590.0	591.5
170°	568.5	572.1	574.1	587.0	587.0
172.5°	571.5	573.6	574.1	584.1	584.1
175°	575.9	577.7	574.1	581.4	579.6
177.5°	577.4	577.4	573.0	578.8	575.9
180°	575.9	575.9	575.9	575.9	575.9

(END OF REPORT)