

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P562854

Luminaire Tested: **SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562854  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3066.8 lumens  
Efficiency: N/A  
Efficacy: 93.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562854  
CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P562854

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10367	10367	10367
5°	10446	10378	10339
10°	10421	10372	10342
15°	10365	10365	10356
20°	10297	10328	10328
25°	10200	10275	10242
30°	10076	10198	10154
35°	9926	10078	10008
40°	9762	9900	9799
45°	9585	9653	9503
50°	9334	9334	9185
55°	9038	8921	8786
60°	8601	8429	8294
65°	7951	7792	7724
70°	6960	7016	6989
75°	5600	6196	6231
80°	3980	5249	5308
85°	2424	4404	4404



TEST NUMBER: P562854

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.3	3.5
10°-20°	305.2	10.0
20°-30°	462.2	15.1
30°-40°	554.1	18.1
40°-50°	565.0	18.4
50°-60°	493.2	16.1
60°-70°	353.1	11.5
70°-80°	181.9	5.9
80°-90°	46.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.7	28.5
0°-40°	1427.8	46.6
0°-60°	2485.9	81.1
0°-90°	3066.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3066.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1124	1124	1124	1124	1124	
5°	1128	1117	1121	1117	1116	107
15°	1085	1076	1085	1085	1084	306
25°	1002	995	1009	1006	1006	461
35°	881	879	895	889	889	551
45°	735	732	740	730	728	565
55°	562	555	555	546	546	501
65°	364	356	357	354	354	360
75°	157	164	174	175	175	170
85°	23	35	42	43	42	32
90°	0	0	0	0	0	



TEST NUMBER: P562854

CATALOG NUMBER: SQ4-PC3-0U-100D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1123.7	1123.7	1123.7	1123.7	1123.7
2.5°	1130.4	1120.6	1123.7	1121.1	1117.0
5°	1127.9	1116.7	1120.6	1117.4	1116.4
7.5°	1119.8	1108.6	1113.7	1111.6	1110.6
10°	1112.3	1101.1	1107.1	1105.0	1103.9
12.5°	1102.3	1091.9	1098.7	1096.7	1096.4
15°	1085.2	1076.1	1085.2	1085.2	1084.2
17.5°	1063.8	1055.4	1065.2	1065.8	1065.2
20°	1048.8	1039.6	1051.9	1050.9	1051.9
22.5°	1030.5	1023.0	1036.1	1033.4	1034.4
25°	1002.0	994.9	1009.3	1006.1	1006.1
27.5°	968.3	963.2	978.9	975.5	975.5
30°	945.8	940.7	957.2	953.1	953.1
32.5°	920.8	917.4	933.1	928.1	928.1
35°	881.3	879.2	894.8	888.6	888.6
37.5°	840.5	838.7	852.8	845.2	842.8
40°	810.5	809.5	822.0	813.6	813.6
42.5°	780.6	779.5	790.3	780.4	780.4
45°	734.6	732.5	739.8	730.4	728.3
47.5°	684.4	682.4	686.9	676.7	675.7
50°	650.3	648.3	650.3	640.9	639.9
52.5°	615.3	611.7	612.0	602.6	602.4
55°	561.9	554.7	554.6	546.2	546.2
57.5°	505.3	495.9	496.7	489.6	488.6
60°	466.1	456.0	456.8	450.5	449.5
62.5°	427.8	416.0	418.5	411.4	411.2
65°	364.2	356.0	356.9	353.8	353.8
67.5°	303.0	295.5	300.9	298.4	298.2
70°	258.0	252.9	260.1	260.1	259.1
72.5°	216.4	216.2	225.2	225.2	225.8
75°	157.1	164.2	173.8	174.8	174.8
77.5°	104.9	117.5	128.0	128.4	128.2
80°	74.9	89.2	98.8	100.9	99.9
82.5°	50.8	65.8	73.9	75.9	74.9
85°	22.9	35.1	41.6	42.6	41.6
87.5°	6.7	14.0	16.6	16.6	15.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)