

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562926

Luminaire Tested: **SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562926
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.2 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 49.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562926
CATALOG NUMBER: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P562926

CATALOG NUMBER: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	87	84	81	78	69	67	65	56	54	53	43	42	41	35
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	31	30	25
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25	22
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22	19
6	61	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7803	7803	7803
5°	7862	7811	7781
10°	7842	7806	7783
15°	7801	7801	7794
20°	7750	7773	7773
25°	7677	7733	7708
30°	7583	7675	7642
35°	7471	7585	7532
40°	7347	7450	7376
45°	7213	7265	7153
50°	7025	7025	6913
55°	6803	6714	6613
60°	6473	6344	6242
65°	5984	5864	5811
70°	5239	5282	5260
75°	4214	4663	4691
80°	2997	3953	3995
85°	1821	3313	3313



TEST NUMBER: P562926

CATALOG NUMBER: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	1.5
10°-20°	229.7	4.2
20°-30°	347.8	6.3
30°-40°	417.0	7.6
40°-50°	425.2	7.7
50°-60°	371.2	6.7
60°-70°	265.7	4.8
70°-80°	136.9	2.5
80°-90°	35.6	0.6
90°-100°	230.4	4.2
100°-110°	635.9	11.6
110°-120°	655.9	11.9
120°-130°	527.0	9.6
130°-140°	414.2	7.5
140°-150°	317.7	5.8
150°-160°	228.3	4.1
160°-170°	139.6	2.5
170°-180°	47.1	0.9
0°-30°	657.6	11.9
0°-40°	1074.5	19.5
0°-60°	1870.9	34.0
0°-90°	2309.1	41.9
90°-120°	1522.1	27.6
90°-150°	2781.0	50.5
90°-180°	3196.0	58.1
0°-180°	5505.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	846	846	846	846	846	
5°	849	840	843	841	840	81
15°	817	810	817	817	816	230
25°	754	749	760	757	757	347
35°	663	662	673	669	669	415
45°	553	551	557	550	548	426
55°	423	418	417	411	411	377
65°	274	268	269	266	266	271
75°	118	124	131	132	132	128
85°	17	26	31	32	31	23
90°	2	3	6	7	8	3
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	



TEST NUMBER: P562926

CATALOG NUMBER: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	845.7	845.7	845.7	845.7	845.7
2.5°	850.7	843.4	845.7	843.8	840.7
5°	848.9	840.4	843.4	841.0	840.2
7.5°	842.7	834.3	838.2	836.6	835.9
10°	837.1	828.7	833.2	831.6	830.8
12.5°	829.6	821.8	826.9	825.4	825.2
15°	816.7	809.9	816.7	816.7	816.0
17.5°	800.6	794.3	801.7	802.2	801.7
20°	789.3	782.4	791.7	790.9	791.7
22.5°	775.6	769.9	779.8	777.8	778.5
25°	754.1	748.7	759.6	757.2	757.2
27.5°	728.7	724.9	736.7	734.2	734.2
30°	711.8	708.0	720.4	717.3	717.3
32.5°	693.0	690.4	702.3	698.5	698.5
35°	663.3	661.7	673.4	668.7	668.7
37.5°	632.6	631.2	641.8	636.1	634.3
40°	610.0	609.2	618.6	612.4	612.4
42.5°	587.5	586.7	594.8	587.3	587.3
45°	552.8	551.3	556.8	549.7	548.2
47.5°	515.1	513.6	517.0	509.3	508.5
50°	489.4	487.9	489.4	482.4	481.6
52.5°	463.1	460.4	460.6	453.6	453.4
55°	422.9	417.5	417.4	411.1	411.1
57.5°	380.3	373.2	373.8	368.5	367.7
60°	350.8	343.2	343.8	339.1	338.3
62.5°	322.0	313.1	315.0	309.6	309.5
65°	274.1	267.9	268.6	266.2	266.2
67.5°	228.0	222.4	226.5	224.6	224.4
70°	194.2	190.4	195.8	195.8	195.0
72.5°	162.9	162.7	169.5	169.5	169.9
75°	118.2	123.6	130.8	131.6	131.6
77.5°	78.9	88.4	96.3	96.6	96.5
80°	56.4	67.1	74.4	75.9	75.2
82.5°	38.2	49.5	55.6	57.1	56.4
85°	17.2	26.4	31.3	32.1	31.3
87.5°	5.3	11.1	13.8	13.9	12.9
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4



TEST NUMBER: P562926

CATALOG NUMBER: SQ4-PC3-100U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)