

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562724

Luminaire Tested: **SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562724
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11129.4 lumens
Efficiency: N/A
Efficacy: 122.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 91
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562724

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562724

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40	35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34	29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22
6	63	51	42	37	58	47	40	34	40	34	30	34	29	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9255	9255	9255
5°	9325	9265	9230
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9104	9065
35°	8861	8997	8934
40°	8714	8838	8748
45°	8556	8617	8484
50°	8333	8333	8199
55°	8068	7964	7844
60°	7678	7524	7404
65°	7097	6955	6894
70°	6214	6264	6239
75°	5000	5529	5563
80°	3555	4689	4737
85°	2165	3933	3933



TEST NUMBER: P562724

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	1.7
10°-20°	544.9	4.9
20°-30°	825.2	7.4
30°-40°	989.3	8.9
40°-50°	1008.7	9.1
50°-60°	880.5	7.9
60°-70°	630.4	5.7
70°-80°	324.7	2.9
80°-90°	84.3	0.8
90°-100°	409.2	3.7
100°-110°	1125.7	10.1
110°-120°	1161.9	10.4
120°-130°	931.0	8.4
130°-140°	731.2	6.6
140°-150°	560.3	5.0
150°-160°	402.9	3.6
160°-170°	246.4	2.2
170°-180°	83.0	0.7
0°-30°	1559.9	14.0
0°-40°	2549.2	22.9
0°-60°	4438.4	39.9
0°-90°	5477.8	49.2
90°-120°	2696.8	24.2
90°-150°	4919.3	44.2
90°-180°	5652.0	50.8
0°-180°	11129.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2014	1994	2001	1995	1993	191
15°	1938	1921	1938	1938	1936	546
25°	1789	1776	1802	1796	1796	823
35°	1574	1570	1598	1586	1586	984
45°	1312	1308	1321	1304	1300	1010
55°	1003	990	990	975	975	894
65°	650	636	637	632	632	643
75°	280	293	310	312	312	303
85°	41	63	74	76	74	56
90°	2	7	13	17	17	6
95°	61	223	724	309	198	64
105°	201	310	1240	1889	1763	212
115°	356	434	995	1981	2248	352
125°	491	560	903	1527	1789	438
135°	592	658	877	1235	1397	457
145°	685	732	864	1052	1133	429
155°	775	800	858	946	973	356
165°	838	849	862	897	903	236
175°	868	869	864	875	873	82
180°	868	868	868	868	868	

TEST NUMBER: P562724

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2006.3	2006.3	2006.3	2006.3	2006.3
2.5°	2018.2	2000.8	2006.3	2001.7	1994.4
5°	2013.7	1993.8	2000.7	1995.1	1993.3
7.5°	1999.3	1979.3	1988.5	1984.7	1982.9
10°	1985.9	1965.9	1976.6	1972.8	1971.0
12.5°	1968.0	1949.5	1961.7	1958.0	1957.6
15°	1937.6	1921.2	1937.6	1937.5	1935.7
17.5°	1899.3	1884.4	1901.9	1903.0	1901.9
20°	1872.6	1856.2	1878.1	1876.3	1878.1
22.5°	1839.9	1826.4	1849.9	1845.1	1846.9
25°	1789.0	1776.2	1802.0	1796.4	1796.4
27.5°	1728.8	1719.7	1747.7	1741.8	1741.8
30°	1688.6	1679.6	1709.1	1701.7	1701.7
32.5°	1644.1	1637.9	1666.0	1657.1	1657.1
35°	1573.5	1569.8	1597.6	1586.5	1586.5
37.5°	1500.6	1497.4	1522.6	1509.1	1504.7
40°	1447.1	1445.3	1467.6	1452.7	1452.7
42.5°	1393.6	1391.8	1411.1	1393.3	1393.3
45°	1311.5	1307.9	1320.8	1304.0	1300.4
47.5°	1222.0	1218.4	1226.5	1208.2	1206.4
50°	1161.1	1157.4	1161.1	1144.3	1142.5
52.5°	1098.6	1092.1	1092.7	1076.0	1075.6
55°	1003.2	990.4	990.2	975.3	975.3
57.5°	902.1	885.4	886.9	874.2	872.4
60°	832.2	814.1	815.5	804.3	802.5
62.5°	763.9	742.8	747.2	734.5	734.2
65°	650.2	635.7	637.2	631.6	631.6
67.5°	541.0	527.5	537.2	532.8	532.4
70°	460.7	451.6	464.4	464.4	462.6
72.5°	386.4	386.0	402.0	402.0	403.1
75°	280.5	293.2	310.2	312.1	312.1
77.5°	187.3	209.8	228.5	229.2	228.9
80°	133.8	159.2	176.5	180.2	178.3
82.5°	90.7	117.5	131.9	135.6	133.8
85°	40.9	62.7	74.3	76.1	74.3
87.5°	12.3	26.4	32.3	33.0	30.1
90°	1.8	7.3	12.9	16.6	16.6
92.5°	25.5	108.9	188.6	72.4	59.4
95°	60.9	223.3	723.6	309.4	197.5
97.5°	99.3	247.7	1104.2	850.8	600.3
100°	127.4	262.7	1223.8	1235.2	1007.8
102.5°	153.9	280.6	1254.8	1532.4	1323.8
105°	201.2	309.5	1240.4	1889.1	1762.7
107.5°	246.2	345.1	1169.9	2063.7	2101.3
110°	278.7	369.0	1116.7	2107.2	2237.1



TEST NUMBER: P562724

CATALOG NUMBER: SQ4-PC3-075U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	308.3	395.6	1063.6	2079.2	2277.0
115°	356.2	433.8	994.9	1981.1	2248.2
117.5°	402.0	473.5	951.3	1843.4	2145.6
120°	430.1	498.7	932.1	1740.3	2052.5
122.5°	455.2	523.8	918.8	1649.9	1946.2
125°	491.0	559.6	902.6	1526.9	1788.6
127.5°	524.9	590.3	891.9	1424.3	1653.8
130°	542.7	609.4	886.0	1363.3	1572.6
132.5°	563.3	630.1	881.6	1309.7	1498.8
135°	592.5	657.5	876.8	1234.8	1397.3
137.5°	619.8	680.1	872.7	1174.4	1308.3
140°	640.5	696.4	871.2	1134.2	1255.2
142.5°	658.2	709.8	868.3	1098.4	1202.0
145°	684.8	731.7	863.8	1052.1	1133.3
147.5°	713.2	753.6	861.6	1011.1	1076.1
150°	730.9	767.0	860.1	988.7	1039.2
152.5°	747.2	780.4	858.7	969.3	1011.1
155°	775.2	800.5	858.3	945.7	972.7
157.5°	795.5	816.1	858.3	926.3	945.1
160°	810.3	826.6	858.3	915.9	930.3
162.5°	822.1	835.5	859.8	906.9	918.5
165°	838.0	848.8	862.0	897.2	902.6
167.5°	849.1	857.4	863.8	889.0	890.4
170°	856.5	861.9	863.8	886.0	886.0
172.5°	862.4	864.9	863.8	881.5	880.1
175°	867.5	869.3	863.8	874.9	873.1
177.5°	869.0	869.0	863.1	871.9	869.0
180°	867.5	867.5	867.5	867.5	867.5

(END OF REPORT)