

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562844

Luminaire Tested: **SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P562844
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7275.4 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Direct

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P562844
CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P562844

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85				
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71				
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60				
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51				
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44				
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39				
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34				
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31				
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28				
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12298	12298	12298
5°	12390	12310	12264
10°	12360	12302	12268
15°	12295	12295	12283
20°	12214	12251	12251
25°	12099	12187	12149
30°	11952	12097	12044
35°	11774	11955	11871
40°	11579	11743	11624
45°	11369	11449	11272
50°	11072	11072	10894
55°	10720	10581	10423
60°	10202	9998	9838
65°	9430	9241	9160
70°	8256	8323	8290
75°	6643	7347	7391
80°	4721	6230	6296
85°	2874	5224	5224



TEST NUMBER: P562844

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.3	3.5
10°-20°	724.0	10.0
20°-30°	1096.4	15.1
30°-40°	1314.4	18.1
40°-50°	1340.3	18.4
50°-60°	1170.0	16.1
60°-70°	837.6	11.5
70°-80°	431.4	5.9
80°-90°	109.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2072.7	28.5
0°-40°	3387.1	46.6
0°-60°	5897.3	81.1
0°-90°	7275.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7275.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2666	2666	2666	2666	2666	
5°	2676	2649	2658	2651	2648	254
15°	2574	2553	2574	2574	2572	726
25°	2377	2360	2394	2387	2387	1094
35°	2091	2086	2123	2108	2108	1308
45°	1743	1738	1755	1733	1728	1341
55°	1333	1316	1316	1296	1296	1188
65°	864	845	847	839	839	854
75°	373	390	412	415	415	403
85°	54	83	99	101	99	76
90°	0	0	0	0	0	



TEST NUMBER: P562844

CATALOG NUMBER: SQ4-PC3-0U-100D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2665.8	2665.8	2665.8	2665.8	2665.8
2.5°	2681.6	2658.4	2665.8	2659.7	2650.0
5°	2675.7	2649.1	2658.4	2650.9	2648.5
7.5°	2656.4	2629.9	2642.1	2637.1	2634.7
10°	2638.6	2612.1	2626.3	2621.3	2618.9
12.5°	2614.9	2590.3	2606.6	2601.6	2601.1
15°	2574.5	2552.7	2574.5	2574.4	2572.0
17.5°	2523.6	2503.8	2527.1	2528.5	2527.1
20°	2488.1	2466.4	2495.5	2493.1	2495.5
22.5°	2444.6	2426.8	2458.0	2451.6	2454.0
25°	2377.0	2360.1	2394.3	2386.9	2386.9
27.5°	2297.0	2285.0	2322.2	2314.3	2314.3
30°	2243.7	2231.6	2270.9	2261.0	2261.0
32.5°	2184.5	2176.3	2213.6	2201.7	2201.7
35°	2090.7	2085.8	2122.8	2108.0	2108.0
37.5°	1993.9	1989.6	2023.0	2005.1	1999.3
40°	1922.8	1920.4	1950.0	1930.2	1930.2
42.5°	1851.7	1849.3	1874.9	1851.2	1851.2
45°	1742.6	1737.8	1755.0	1732.7	1727.8
47.5°	1623.7	1618.8	1629.6	1605.3	1602.9
50°	1542.7	1537.9	1542.7	1520.4	1518.0
52.5°	1459.8	1451.1	1451.9	1429.6	1429.2
55°	1332.9	1316.0	1315.6	1295.9	1295.9
57.5°	1198.6	1176.4	1178.4	1161.5	1159.1
60°	1105.8	1081.7	1083.6	1068.7	1066.3
62.5°	1015.0	987.0	992.8	976.0	975.5
65°	863.9	844.6	846.6	839.2	839.2
67.5°	718.8	700.9	713.8	707.9	707.4
70°	612.1	600.1	617.1	617.0	614.6
72.5°	513.4	512.9	534.1	534.2	535.6
75°	372.7	389.6	412.2	414.7	414.7
77.5°	248.8	278.7	303.6	304.6	304.1
80°	177.7	211.5	234.5	239.4	237.0
82.5°	120.5	156.2	175.3	180.1	177.7
85°	54.3	83.3	98.7	101.1	98.7
87.5°	15.8	33.2	39.5	39.4	35.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)