

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563012

Luminaire Tested: **SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563012
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14916.7 lumens
Efficiency: N/A
Efficacy: 128.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 116
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563012
CATALOG NUMBER: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563012

CATALOG NUMBER: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14
7	56	44	36	31	51	40	33	28	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	36	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9255	9255	9255
5°	9325	9265	9230
10°	9302	9259	9233
15°	9254	9254	9245
20°	9193	9220	9220
25°	9106	9172	9144
30°	8995	9104	9065
35°	8861	8997	8934
40°	8714	8838	8748
45°	8556	8617	8484
50°	8333	8333	8199
55°	8068	7964	7844
60°	7678	7524	7404
65°	7097	6955	6894
70°	6214	6264	6239
75°	5000	5529	5563
80°	3555	4689	4737
85°	2165	3933	3933



TEST NUMBER: P563012

CATALOG NUMBER: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.9	1.3
10°-20°	544.9	3.7
20°-30°	825.2	5.5
30°-40°	989.3	6.6
40°-50°	1008.7	6.8
50°-60°	880.5	5.9
60°-70°	630.4	4.2
70°-80°	324.7	2.2
80°-90°	85.5	0.6
90°-100°	683.9	4.6
100°-110°	1842.3	12.4
110°-120°	1933.4	13.0
120°-130°	1568.9	10.5
130°-140°	1230.4	8.2
140°-150°	944.7	6.3
150°-160°	679.2	4.6
160°-170°	415.0	2.8
170°-180°	139.9	0.9
0°-30°	1559.9	10.5
0°-40°	2549.2	17.1
0°-60°	4438.4	29.8
0°-90°	5479.0	36.7
90°-120°	4459.5	29.9
90°-150°	8203.5	55.0
90°-180°	9438.0	63.3
0°-180°	14916.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2014	1994	2001	1995	1993	191
15°	1938	1921	1938	1938	1936	546
25°	1789	1776	1802	1796	1796	823
35°	1574	1570	1598	1586	1586	984
45°	1312	1308	1321	1304	1300	1010
55°	1003	990	990	975	975	894
65°	650	636	637	632	632	643
75°	280	293	310	312	312	303
85°	41	63	74	76	74	56
90°	4	11	22	24	24	9
95°	104	372	1121	573	397	109
105°	341	530	2037	3048	2861	358
115°	602	736	1697	3278	3708	592
125°	821	943	1523	2575	3030	733
135°	989	1104	1481	2077	2352	763
145°	1144	1233	1462	1776	1907	717
155°	1298	1345	1449	1594	1644	598
165°	1408	1424	1454	1512	1520	397
175°	1464	1462	1456	1477	1473	139
180°	1462	1462	1462	1462	1462	



TEST NUMBER: P563012

CATALOG NUMBER: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2006.3	2006.3	2006.3	2006.3	2006.3
2.5°	2018.2	2000.8	2006.3	2001.7	1994.4
5°	2013.7	1993.8	2000.7	1995.1	1993.3
7.5°	1999.3	1979.3	1988.5	1984.7	1982.9
10°	1985.9	1965.9	1976.6	1972.8	1971.0
12.5°	1968.0	1949.5	1961.7	1958.0	1957.6
15°	1937.6	1921.2	1937.6	1937.5	1935.7
17.5°	1899.3	1884.4	1901.9	1903.0	1901.9
20°	1872.6	1856.2	1878.1	1876.3	1878.1
22.5°	1839.9	1826.4	1849.9	1845.1	1846.9
25°	1789.0	1776.2	1802.0	1796.4	1796.4
27.5°	1728.8	1719.7	1747.7	1741.8	1741.8
30°	1688.6	1679.6	1709.1	1701.7	1701.7
32.5°	1644.1	1637.9	1666.0	1657.1	1657.1
35°	1573.5	1569.8	1597.6	1586.5	1586.5
37.5°	1500.6	1497.4	1522.6	1509.1	1504.7
40°	1447.1	1445.3	1467.6	1452.7	1452.7
42.5°	1393.6	1391.8	1411.1	1393.3	1393.3
45°	1311.5	1307.9	1320.8	1304.0	1300.4
47.5°	1222.0	1218.4	1226.5	1208.2	1206.4
50°	1161.1	1157.4	1161.1	1144.3	1142.5
52.5°	1098.6	1092.1	1092.7	1076.0	1075.6
55°	1003.2	990.4	990.2	975.3	975.3
57.5°	902.1	885.4	886.9	874.2	872.4
60°	832.2	814.1	815.5	804.3	802.5
62.5°	763.9	742.8	747.2	734.5	734.2
65°	650.2	635.7	637.2	631.6	631.6
67.5°	541.0	527.5	537.2	532.8	532.4
70°	460.7	451.6	464.4	464.4	462.6
72.5°	386.4	386.0	402.0	402.0	403.1
75°	280.5	293.2	310.2	312.1	312.1
77.5°	187.3	209.8	228.5	229.2	228.9
80°	133.8	159.2	176.5	180.2	178.3
82.5°	90.7	117.5	131.9	135.6	133.8
85°	40.9	62.7	74.3	76.1	74.3
87.5°	12.6	27.2	34.2	34.5	31.6
90°	3.7	11.0	22.3	24.2	24.2
92.5°	45.4	160.5	317.3	152.8	106.2
95°	104.3	372.0	1121.1	573.3	396.7
97.5°	166.5	425.8	1758.4	1469.0	1107.7
100°	214.2	447.3	1961.0	2051.8	1702.2
102.5°	260.4	477.4	2028.1	2488.3	2201.3
105°	340.8	530.2	2037.4	3048.1	2860.6
107.5°	416.8	585.8	1950.6	3335.8	3384.2
110°	467.4	627.7	1871.6	3425.1	3601.8



TEST NUMBER: P563012

CATALOG NUMBER: SQ4-PC3-125U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	521.1	669.7	1795.7	3405.4	3695.6
115°	601.5	736.3	1696.6	3278.2	3707.9
117.5°	674.9	801.3	1619.9	3075.2	3553.7
120°	722.6	844.6	1581.1	2929.5	3421.1
122.5°	764.3	884.9	1552.8	2780.4	3270.6
125°	821.3	943.3	1523.4	2574.8	3030.0
127.5°	876.0	996.2	1504.8	2393.4	2799.8
130°	908.8	1029.0	1497.3	2289.5	2646.4
132.5°	941.6	1060.3	1489.9	2197.9	2525.7
135°	988.9	1103.6	1480.6	2077.2	2352.1
137.5°	1034.0	1144.0	1475.7	1974.7	2200.5
140°	1065.3	1170.9	1471.2	1911.7	2115.6
142.5°	1098.0	1196.4	1468.3	1852.8	2024.7
145°	1143.5	1232.7	1461.9	1775.9	1907.0
147.5°	1192.6	1270.2	1455.6	1711.2	1814.3
150°	1225.4	1292.8	1452.6	1670.6	1756.2
152.5°	1255.2	1313.9	1451.1	1637.5	1707.0
155°	1298.0	1345.4	1448.9	1593.5	1644.4
157.5°	1335.7	1372.5	1449.3	1562.5	1596.8
160°	1359.5	1390.5	1450.8	1544.5	1570.0
162.5°	1380.4	1405.5	1452.3	1529.4	1547.6
165°	1407.9	1424.3	1454.5	1512.4	1519.7
167.5°	1430.3	1439.7	1456.3	1499.2	1502.2
170°	1445.2	1448.8	1456.3	1491.7	1491.7
172.5°	1454.1	1454.8	1457.8	1484.3	1484.3
175°	1463.8	1462.0	1456.3	1476.8	1473.1
177.5°	1467.9	1465.0	1457.5	1469.3	1466.4
180°	1461.9	1461.9	1461.9	1461.9	1461.9

(END OF REPORT)