

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563204

Luminaire Tested: **SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563204
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7248.8 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563204
CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563204

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75				
1	104	99	95	92	98	95	91	88	86	83	81	78	76	74	70	69	67	64				
2	95	87	81	76	90	83	77	73	76	71	67	69	65	62	62	60	57	54				
3	87	77	69	63	82	73	67	61	67	61	57	61	57	53	55	52	49	46				
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	50	46	42	39				
5	73	61	53	46	69	58	51	45	54	47	42	49	44	40	45	40	37	34				
6	67	55	46	40	64	53	45	39	48	42	37	44	39	35	41	36	33	30				
7	62	50	41	36	59	48	40	35	44	37	33	40	35	31	37	33	29	27				
8	58	45	37	32	55	44	36	31	40	34	29	37	32	28	34	29	26	24				
9	54	41	34	28	51	40	33	28	37	31	26	34	29	25	32	27	24	22				
10	51	38	31	26	48	37	30	25	34	28	24	32	26	23	29	25	21	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9776	9776	9776
5°	9848	9787	9753
10°	9831	9761	9718
15°	9766	9713	9660
20°	9701	9646	9573
25°	9586	9520	9425
30°	9409	9359	9240
35°	9163	9099	8985
40°	8869	8813	8713
45°	8627	8567	8482
50°	8317	8264	8184
55°	7887	7782	7723
60°	7180	6974	6940
65°	6326	6061	6042
70°	5461	5236	5236
75°	4700	4634	4568
80°	4144	4195	4096
85°	3245	3541	3541



TEST NUMBER: P563204

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.4	2.8
10°-20°	572.2	7.9
20°-30°	857.0	11.8
30°-40°	1005.2	13.9
40°-50°	1008.4	13.9
50°-60°	860.2	11.9
60°-70°	561.0	7.7
70°-80°	281.5	3.9
80°-90°	79.4	1.1
90°-100°	137.1	1.9
100°-110°	360.4	5.0
110°-120°	373.8	5.2
120°-130°	299.8	4.1
130°-140°	235.2	3.2
140°-150°	180.5	2.5
150°-160°	130.0	1.8
160°-170°	79.6	1.1
170°-180°	26.9	0.4
0°-30°	1629.6	22.5
0°-40°	2634.8	36.3
0°-60°	4503.4	62.1
0°-90°	5425.3	74.8
90°-120°	871.3	12.0
90°-150°	1586.9	21.9
90°-180°	1823.0	25.1
0°-180°	7248.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2119	2119	2119	2119	2119	
5°	2127	2107	2114	2106	2106	202
15°	2045	2025	2034	2026	2023	577
25°	1883	1862	1870	1854	1852	866
35°	1627	1611	1616	1597	1595	1016
45°	1322	1313	1313	1300	1300	1018
55°	981	977	968	962	960	871
65°	580	569	555	552	554	578
75°	264	264	260	258	256	286
85°	61	67	67	67	67	72
90°	2	5	14	7	7	4
95°	18	71	236	122	83	20
105°	65	98	398	605	564	69
115°	115	140	319	637	727	114
125°	160	180	290	491	579	142
135°	191	211	281	396	449	148
145°	222	236	278	338	364	139
155°	251	258	278	305	314	115
165°	270	274	278	289	292	76
175°	281	281	280	283	283	27
180°	281	281	281	281	281	

TEST NUMBER: P563204

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2119.1	2119.1	2119.1	2119.1	2119.1
2.5°	2132.5	2115.1	2119.1	2116.0	2107.2
5°	2126.6	2106.6	2113.6	2106.1	2106.1
7.5°	2112.1	2090.3	2097.2	2089.8	2089.4
10°	2098.7	2076.9	2083.8	2076.4	2074.6
12.5°	2079.4	2057.6	2066.0	2057.1	2056.7
15°	2044.8	2024.9	2033.7	2026.2	2022.6
17.5°	2005.8	1984.0	1994.7	1984.3	1982.8
20°	1976.1	1954.3	1965.0	1950.1	1950.1
22.5°	1940.5	1918.7	1930.8	1911.5	1911.5
25°	1883.3	1861.5	1870.3	1853.5	1851.7
27.5°	1815.3	1793.9	1803.0	1784.1	1783.7
30°	1766.3	1746.3	1757.0	1736.5	1734.7
32.5°	1712.8	1694.2	1702.0	1681.5	1679.7
35°	1627.0	1610.6	1615.8	1597.2	1595.4
37.5°	1536.7	1520.0	1525.9	1509.9	1509.2
40°	1472.8	1461.9	1463.5	1450.4	1446.8
42.5°	1413.4	1401.0	1402.6	1389.6	1388.9
45°	1322.4	1313.3	1313.1	1300.1	1300.1
47.5°	1225.8	1218.9	1216.9	1206.1	1205.7
50°	1158.9	1153.5	1151.5	1142.2	1140.4
52.5°	1089.1	1086.6	1080.2	1072.4	1072.0
55°	980.6	977.0	967.6	962.0	960.2
57.5°	862.9	855.6	845.1	836.9	838.4
60°	778.2	770.9	755.9	752.2	752.2
62.5°	696.5	687.8	672.7	667.6	670.5
65°	579.5	568.6	555.3	551.6	553.5
67.5°	473.2	463.4	449.1	449.1	447.6
70°	404.9	399.4	388.2	388.2	388.2
72.5°	344.0	341.4	333.2	333.2	331.7
75°	263.7	263.7	260.0	258.1	256.3
77.5°	197.6	198.3	196.5	194.6	191.3
80°	156.0	159.6	157.9	156.0	154.2
82.5°	117.4	121.0	120.7	117.4	117.0
85°	61.3	66.7	66.9	66.9	66.9
87.5°	16.7	23.2	26.7	25.2	26.7
90°	1.8	5.3	14.4	7.2	7.2
92.5°	7.6	36.5	80.8	35.8	23.1
95°	18.0	70.9	236.2	121.7	83.0
97.5°	31.4	77.9	353.5	281.1	207.0
100°	41.5	83.8	389.5	394.7	306.6
102.5°	50.1	89.6	399.6	491.7	416.2
105°	64.9	98.4	398.5	605.0	564.5
107.5°	80.1	111.1	375.8	663.9	673.7
110°	90.2	118.4	357.1	679.0	721.4



TEST NUMBER: P563204

CATALOG NUMBER: SQ4-PP3-025U-075D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	100.3	127.1	339.8	669.4	734.3
115°	115.4	140.1	319.2	636.8	726.8
117.5°	130.2	152.8	305.1	591.6	691.4
120°	138.9	160.0	299.4	561.3	658.2
122.5°	147.5	168.7	295.0	530.9	626.5
125°	160.5	179.9	290.3	490.7	578.9
127.5°	171.0	190.7	286.4	458.3	532.7
130°	176.7	197.9	284.9	438.0	506.7
132.5°	182.5	203.7	283.5	420.5	482.2
135°	191.2	210.6	281.3	396.1	449.0
137.5°	200.2	219.2	281.0	377.9	421.3
140°	207.4	225.0	279.5	363.4	404.0
142.5°	213.2	229.4	279.5	353.2	388.1
145°	221.8	235.9	277.7	337.8	364.3
147.5°	230.5	244.2	277.7	325.1	347.0
150°	236.2	248.6	277.7	317.8	335.4
152.5°	242.0	251.5	277.7	311.9	325.3
155°	250.7	257.7	277.7	305.0	313.8
157.5°	257.2	263.9	277.7	298.8	305.1
160°	261.5	266.8	277.7	295.8	299.4
162.5°	265.8	269.7	277.7	292.9	296.5
165°	270.5	274.0	277.7	288.6	292.1
167.5°	274.8	276.6	279.5	286.8	288.2
170°	277.7	279.5	279.5	286.7	286.7
172.5°	279.2	279.5	279.5	285.3	283.9
175°	281.3	281.3	279.5	283.1	283.1
177.5°	281.3	281.3	279.9	282.7	281.3
180°	281.3	281.3	281.3	281.3	281.3

(END OF REPORT)