

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563598

Luminaire Tested: **SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563598  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5483.3 lumens  
Efficiency: N/A  
Efficacy: 111.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 49.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563598  
CATALOG NUMBER: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563598

CATALOG NUMBER: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	45	43	40	38	34	32	30	26
4	73	63	55	49	67	57	51	46	48	43	39	39	35	32	30	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	32	52	42	35	30	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8242	8242	8242
5°	8302	8251	8222
10°	8288	8229	8193
15°	8234	8189	8144
20°	8179	8133	8071
25°	8081	8026	7945
30°	7932	7890	7790
35°	7724	7671	7574
40°	7477	7430	7346
45°	7273	7222	7150
50°	7012	6967	6900
55°	6650	6561	6511
60°	6052	5879	5851
65°	5333	5111	5093
70°	4605	4413	4413
75°	3964	3907	3850
80°	3496	3533	3454
85°	2731	2985	2985



TEST NUMBER: P563598

CATALOG NUMBER: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.5	1.5
10°-20°	241.2	4.4
20°-30°	361.3	6.6
30°-40°	423.7	7.7
40°-50°	425.1	7.8
50°-60°	362.6	6.6
60°-70°	236.5	4.3
70°-80°	118.6	2.2
80°-90°	33.9	0.6
90°-100°	230.4	4.2
100°-110°	635.9	11.6
110°-120°	655.9	12.0
120°-130°	527.0	9.6
130°-140°	414.2	7.6
140°-150°	317.7	5.8
150°-160°	228.3	4.2
160°-170°	139.6	2.5
170°-180°	47.1	0.9
0°-30°	686.9	12.5
0°-40°	1110.6	20.3
0°-60°	1898.3	34.6
0°-90°	2287.3	41.7
90°-120°	1522.1	27.8
90°-150°	2781.0	50.7
90°-180°	3196.0	58.3
0°-180°	5483.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	893	893	893	893	893	
5°	896	888	891	888	888	85
15°	862	854	857	854	853	243
25°	794	785	788	781	780	365
35°	686	679	681	673	672	428
45°	557	554	554	548	548	429
55°	413	412	408	406	405	367
65°	244	240	234	232	233	244
75°	111	111	110	109	108	121
85°	26	28	28	28	28	30
90°	2	3	6	7	8	3
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	

TEST NUMBER: P563598

CATALOG NUMBER: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	893.3	893.3	893.3	893.3	893.3
2.5°	898.9	891.6	893.3	891.9	888.3
5°	896.4	888.0	890.9	887.8	887.8
7.5°	890.3	881.1	884.0	880.9	880.7
10°	884.7	875.5	878.4	875.3	874.5
12.5°	876.5	867.3	870.9	867.1	867.0
15°	862.0	853.5	857.3	854.1	852.6
17.5°	845.5	836.3	840.8	836.4	835.8
20°	833.0	823.8	828.3	822.0	822.0
22.5°	818.0	808.8	813.9	805.7	805.7
25°	793.8	784.7	788.4	781.3	780.5
27.5°	765.2	756.2	760.0	752.0	751.9
30°	744.5	736.1	740.6	732.0	731.2
32.5°	722.0	714.2	717.4	708.8	708.0
35°	685.8	678.9	681.1	673.3	672.5
37.5°	647.8	640.7	643.2	636.5	636.2
40°	620.8	616.2	616.9	611.4	609.9
42.5°	595.8	590.6	591.2	585.7	585.4
45°	557.4	553.6	553.5	548.0	548.0
47.5°	516.7	513.8	512.9	508.4	508.3
50°	488.5	486.2	485.4	481.5	480.7
52.5°	459.1	458.0	455.3	452.0	451.9
55°	413.4	411.8	407.9	405.5	404.8
57.5°	363.7	360.7	356.2	352.8	353.4
60°	328.0	325.0	318.6	317.1	317.1
62.5°	293.6	289.9	283.6	281.4	282.6
65°	244.3	239.7	234.1	232.5	233.3
67.5°	199.5	195.3	189.3	189.3	188.7
70°	170.7	168.4	163.6	163.6	163.6
72.5°	145.0	143.9	140.4	140.4	139.8
75°	111.2	111.2	109.6	108.8	108.0
77.5°	83.3	83.6	82.8	82.0	80.6
80°	65.8	67.3	66.5	65.7	65.0
82.5°	49.5	51.0	50.9	49.5	49.3
85°	25.8	28.1	28.2	28.2	28.2
87.5°	7.2	10.0	11.3	11.5	12.2
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4



TEST NUMBER: P563598

CATALOG NUMBER: SQ4-PP3-100U-075D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)