

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563646

Luminaire Tested: **SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563646  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-23, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7073.7 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 68.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563646  
CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563646

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	21	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13974	13974	13974
5°	14076	13991	13941
10°	14053	13953	13892
15°	13960	13884	13808
20°	13867	13790	13685
25°	13702	13609	13473
30°	13449	13379	13209
35°	13098	13008	12843
40°	12679	12598	12455
45°	12333	12245	12124
50°	11889	11813	11699
55°	11274	11125	11039
60°	10263	9970	9920
65°	9042	8665	8636
70°	7807	7483	7483
75°	6720	6623	6531
80°	5924	5993	5855
85°	4637	5060	5060



TEST NUMBER: P563646

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.2	2.0
10°-20°	409.0	5.8
20°-30°	612.6	8.7
30°-40°	718.5	10.2
40°-50°	720.7	10.2
50°-60°	614.8	8.7
60°-70°	401.0	5.7
70°-80°	201.2	2.8
80°-90°	56.7	0.8
90°-100°	230.4	3.3
100°-110°	635.9	9.0
110°-120°	655.9	9.3
120°-130°	527.0	7.5
130°-140°	414.2	5.9
140°-150°	317.7	4.5
150°-160°	228.3	3.2
160°-170°	139.6	2.0
170°-180°	47.1	0.7
0°-30°	1164.7	16.5
0°-40°	1883.2	26.6
0°-60°	3218.8	45.5
0°-90°	3877.6	54.8
90°-120°	1522.1	21.5
90°-150°	2781.0	39.3
90°-180°	3196.0	45.2
0°-180°	7073.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1515	1515	1515	1515	1515	
5°	1520	1506	1511	1505	1505	144
15°	1462	1447	1454	1448	1446	412
25°	1346	1330	1337	1325	1324	619
35°	1163	1151	1155	1142	1140	726
45°	945	939	938	929	929	728
55°	701	698	692	688	686	623
65°	414	406	397	394	396	413
75°	188	188	186	184	183	204
85°	44	48	48	48	48	52
90°	2	3	6	7	8	4
95°	34	125	418	172	112	36
105°	113	175	700	1068	1006	121
115°	203	245	564	1116	1269	200
125°	279	317	511	864	1014	248
135°	335	371	497	700	789	259
145°	389	416	490	596	641	243
155°	438	453	486	535	552	202
165°	475	481	489	508	512	134
175°	492	493	490	497	495	47
180°	492	492	492	492	492	

TEST NUMBER: P563646

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1514.6	1514.6	1514.6	1514.6	1514.6
2.5°	1524.2	1511.7	1514.6	1512.4	1506.1
5°	1519.9	1505.7	1510.7	1505.3	1505.3
7.5°	1509.6	1494.0	1499.0	1493.7	1493.4
10°	1500.0	1484.5	1489.4	1484.1	1482.8
12.5°	1486.2	1470.7	1476.7	1470.3	1470.0
15°	1461.5	1447.3	1453.6	1448.2	1445.6
17.5°	1433.7	1418.1	1425.7	1418.2	1417.2
20°	1412.4	1396.8	1404.5	1393.8	1393.8
22.5°	1386.9	1371.4	1380.0	1366.2	1366.2
25°	1346.0	1330.5	1336.8	1324.8	1323.5
27.5°	1297.5	1282.1	1288.7	1275.2	1274.9
30°	1262.4	1248.1	1255.8	1241.2	1239.9
32.5°	1224.2	1210.9	1216.5	1201.9	1200.6
35°	1162.9	1151.2	1154.9	1141.6	1140.3
37.5°	1098.3	1086.4	1090.6	1079.2	1078.7
40°	1052.7	1044.9	1046.0	1036.7	1034.1
42.5°	1010.2	1001.4	1002.5	993.2	992.7
45°	945.2	938.7	938.5	929.2	929.2
47.5°	876.1	871.2	869.8	862.0	861.8
50°	828.3	824.4	823.0	816.4	815.1
52.5°	778.4	776.6	772.1	766.5	766.2
55°	700.9	698.3	691.6	687.6	686.3
57.5°	616.7	611.5	604.0	598.2	599.2
60°	556.2	551.0	540.3	537.6	537.6
62.5°	497.8	491.6	480.8	477.1	479.2
65°	414.2	406.4	396.9	394.3	395.6
67.5°	338.2	331.2	321.0	321.0	319.9
70°	289.4	285.5	277.4	277.4	277.4
72.5°	245.8	244.0	238.1	238.1	237.1
75°	188.5	188.5	185.8	184.5	183.2
77.5°	141.2	141.8	140.4	139.1	136.7
80°	111.5	114.1	112.8	111.5	110.2
82.5°	83.9	86.5	86.3	83.9	83.6
85°	43.8	47.7	47.8	47.8	47.8
87.5°	12.0	16.5	18.3	18.4	19.6
90°	1.6	3.1	6.3	7.1	7.9
92.5°	14.2	58.8	105.1	38.4	29.9
95°	33.8	124.6	417.9	171.8	111.8
97.5°	56.0	139.6	619.1	476.6	345.2
100°	72.4	148.6	693.4	698.3	567.4
102.5°	88.1	158.8	707.8	862.7	738.7
105°	113.3	174.9	699.7	1068.1	1005.8
107.5°	140.1	194.9	660.6	1167.2	1190.0
110°	159.0	208.2	630.4	1188.5	1262.4

TEST NUMBER: P563646

CATALOG NUMBER: SQ4-PP3-100U-125D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	176.0	223.4	602.1	1171.7	1280.6
115°	203.0	245.4	563.5	1115.5	1268.7
117.5°	226.7	268.8	538.2	1036.5	1210.7
120°	242.4	284.0	528.1	983.0	1158.5
122.5°	257.5	297.2	519.9	933.1	1099.3
125°	278.6	317.1	510.8	864.4	1014.5
127.5°	296.5	335.0	505.4	806.3	935.8
130°	308.5	347.0	502.9	770.8	888.5
132.5°	319.8	356.5	500.4	741.0	847.6
135°	335.3	371.4	496.6	700.1	789.4
137.5°	352.6	385.5	494.7	665.8	742.0
140°	362.0	394.3	493.5	642.9	709.9
142.5°	372.7	402.6	492.2	622.6	681.6
145°	388.8	415.7	490.3	596.0	641.4
147.5°	404.2	427.8	488.6	573.6	608.8
150°	415.5	434.8	487.9	560.2	588.7
152.5°	424.4	442.4	487.3	548.8	572.3
155°	438.4	453.0	486.4	534.8	551.7
157.5°	451.3	462.5	486.5	524.6	536.1
160°	458.8	468.8	487.2	518.8	527.3
162.5°	465.1	473.9	487.8	513.8	520.4
165°	474.6	480.7	488.7	507.7	511.6
167.5°	481.8	485.5	489.5	504.0	505.3
170°	485.6	488.7	489.5	502.1	502.1
172.5°	488.7	490.6	489.5	499.6	499.0
175°	491.9	492.7	489.5	496.6	495.0
177.5°	493.1	492.5	489.4	493.7	492.5
180°	491.9	491.9	491.9	491.9	491.9

(END OF REPORT)