

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563742

Luminaire Tested: **SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563742
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7856.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563742
CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P563742

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49	49	49	0			
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42	42	42	0			
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35	35	35	0			
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30	30	30	0			
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26	26	26	0			
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23	23	23	0			
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	0			
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18	18	18	0			
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16	0			
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	0			
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	0			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13974	13974	13974
5°	14076	13991	13941
10°	14053	13953	13892
15°	13960	13884	13808
20°	13867	13790	13685
25°	13702	13609	13473
30°	13449	13379	13209
35°	13098	13008	12843
40°	12679	12598	12455
45°	12333	12245	12124
50°	11889	11813	11699
55°	11274	11125	11039
60°	10263	9970	9920
65°	9042	8665	8636
70°	7807	7483	7483
75°	6720	6623	6531
80°	5924	5993	5855
85°	4637	5060	5060



TEST NUMBER: P563742

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.2	1.8
10°-20°	409.0	5.2
20°-30°	612.6	7.8
30°-40°	718.5	9.1
40°-50°	720.7	9.2
50°-60°	614.8	7.8
60°-70°	401.0	5.1
70°-80°	201.2	2.6
80°-90°	57.1	0.7
90°-100°	288.3	3.7
100°-110°	776.6	9.9
110°-120°	815.0	10.4
120°-130°	661.3	8.4
130°-140°	518.7	6.6
140°-150°	398.2	5.1
150°-160°	286.3	3.6
160°-170°	174.9	2.2
170°-180°	59.0	0.8
0°-30°	1164.7	14.8
0°-40°	1883.2	24.0
0°-60°	3218.8	41.0
0°-90°	3878.1	49.4
90°-120°	1879.8	23.9
90°-150°	3458.0	44.0
90°-180°	3978.0	50.6
0°-180°	7856.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1515	1515	1515	1515	1515	
5°	1520	1506	1511	1505	1505	144
15°	1462	1447	1454	1448	1446	412
25°	1346	1330	1337	1325	1324	619
35°	1163	1151	1155	1142	1140	726
45°	945	939	938	929	929	728
55°	701	698	692	688	686	623
65°	414	406	397	394	396	413
75°	188	188	186	184	183	204
85°	44	48	48	48	48	52
90°	2	5	9	10	10	5
95°	44	157	473	242	167	46
105°	144	224	859	1285	1206	151
115°	254	310	715	1382	1563	250
125°	346	398	642	1085	1277	309
135°	417	465	624	876	992	322
145°	482	520	616	749	804	302
155°	547	567	611	672	693	252
165°	594	600	613	638	641	167
175°	617	616	614	622	621	59
180°	616	616	616	616	616	



TEST NUMBER: P563742

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1514.6	1514.6	1514.6	1514.6	1514.6
2.5°	1524.2	1511.7	1514.6	1512.4	1506.1
5°	1519.9	1505.7	1510.7	1505.3	1505.3
7.5°	1509.6	1494.0	1499.0	1493.7	1493.4
10°	1500.0	1484.5	1489.4	1484.1	1482.8
12.5°	1486.2	1470.7	1476.7	1470.3	1470.0
15°	1461.5	1447.3	1453.6	1448.2	1445.6
17.5°	1433.7	1418.1	1425.7	1418.2	1417.2
20°	1412.4	1396.8	1404.5	1393.8	1393.8
22.5°	1386.9	1371.4	1380.0	1366.2	1366.2
25°	1346.0	1330.5	1336.8	1324.8	1323.5
27.5°	1297.5	1282.1	1288.7	1275.2	1274.9
30°	1262.4	1248.1	1255.8	1241.2	1239.9
32.5°	1224.2	1210.9	1216.5	1201.9	1200.6
35°	1162.9	1151.2	1154.9	1141.6	1140.3
37.5°	1098.3	1086.4	1090.6	1079.2	1078.7
40°	1052.7	1044.9	1046.0	1036.7	1034.1
42.5°	1010.2	1001.4	1002.5	993.2	992.7
45°	945.2	938.7	938.5	929.2	929.2
47.5°	876.1	871.2	869.8	862.0	861.8
50°	828.3	824.4	823.0	816.4	815.1
52.5°	778.4	776.6	772.1	766.5	766.2
55°	700.9	698.3	691.6	687.6	686.3
57.5°	616.7	611.5	604.0	598.2	599.2
60°	556.2	551.0	540.3	537.6	537.6
62.5°	497.8	491.6	480.8	477.1	479.2
65°	414.2	406.4	396.9	394.3	395.6
67.5°	338.2	331.2	321.0	321.0	319.9
70°	289.4	285.5	277.4	277.4	277.4
72.5°	245.8	244.0	238.1	238.1	237.1
75°	188.5	188.5	185.8	184.5	183.2
77.5°	141.2	141.8	140.4	139.1	136.7
80°	111.5	114.1	112.8	111.5	110.2
82.5°	83.9	86.5	86.3	83.9	83.6
85°	43.8	47.7	47.8	47.8	47.8
87.5°	12.0	16.8	18.9	19.1	20.1
90°	1.6	4.6	9.4	10.2	10.2
92.5°	19.2	67.7	133.8	64.4	44.7
95°	44.0	156.8	472.6	241.7	167.2
97.5°	70.2	179.5	741.2	619.2	466.9
100°	90.3	188.5	826.6	864.9	717.5
102.5°	109.7	201.2	854.9	1048.9	927.9
105°	143.7	223.5	858.8	1284.9	1205.8
107.5°	175.7	246.9	822.2	1406.1	1426.6
110°	197.0	264.6	789.0	1443.8	1518.2



TEST NUMBER: P563742

CATALOG NUMBER: SQ4-PP3-125U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	219.7	282.3	756.9	1435.5	1557.8
115°	253.6	310.4	715.2	1381.8	1563.0
117.5°	284.5	337.8	682.8	1296.3	1498.0
120°	304.6	356.0	666.5	1234.8	1442.1
122.5°	322.2	373.0	654.6	1172.0	1378.7
125°	346.2	397.6	642.2	1085.3	1277.2
127.5°	369.3	419.9	634.3	1008.9	1180.2
130°	383.1	433.8	631.2	965.1	1115.5
132.5°	396.9	447.0	628.0	926.5	1064.7
135°	416.9	465.2	624.1	875.6	991.5
137.5°	435.8	482.2	622.1	832.4	927.6
140°	449.0	493.6	620.2	805.8	891.8
142.5°	462.9	504.3	618.9	781.0	853.5
145°	482.0	519.6	616.2	748.6	803.9
147.5°	502.7	535.4	613.6	721.3	764.8
150°	516.5	544.9	612.3	704.2	740.3
152.5°	529.1	553.8	611.7	690.2	719.6
155°	547.2	567.1	610.8	671.7	693.2
157.5°	563.0	578.5	610.9	658.7	673.1
160°	573.1	586.1	611.5	651.0	661.8
162.5°	581.9	592.5	612.2	644.7	652.4
165°	593.5	600.4	613.1	637.5	640.6
167.5°	602.9	606.9	613.9	632.0	633.2
170°	609.2	610.7	613.9	628.8	628.8
172.5°	613.0	613.3	614.5	625.7	625.7
175°	617.0	616.3	613.9	622.5	621.0
177.5°	618.8	617.5	614.4	619.4	618.1
180°	616.2	616.2	616.2	616.2	616.2

(END OF REPORT)