

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563660

Luminaire Tested: **SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563660  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 13121.0 lumens  
Efficiency: N/A  
Efficacy: 135.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 96.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563660  
CATALOG NUMBER: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563660

CATALOG NUMBER: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	55	51	48	44	41	36	34	31	25	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	21	19	15				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	15	11				
7	55	43	36	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10				
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	15	13	12	9				
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6633	6633	6633
5°	6681	6640	6617
10°	6670	6623	6593
15°	6626	6590	6554
20°	6582	6545	6495
25°	6504	6459	6395
30°	6384	6350	6269
35°	6217	6174	6096
40°	6018	5980	5911
45°	5853	5812	5755
50°	5643	5607	5553
55°	5351	5280	5240
60°	4871	4732	4708
65°	4292	4113	4099
70°	3705	3553	3553
75°	3189	3144	3100
80°	2811	2845	2779
85°	2202	2403	2403



TEST NUMBER: P563660

CATALOG NUMBER: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.0	1.0
10°-20°	388.2	3.0
20°-30°	581.5	4.4
30°-40°	682.0	5.2
40°-50°	684.2	5.2
50°-60°	583.6	4.4
60°-70°	380.6	2.9
70°-80°	191.0	1.5
80°-90°	56.3	0.4
90°-100°	683.9	5.2
100°-110°	1842.3	14.0
110°-120°	1933.4	14.7
120°-130°	1568.9	12.0
130°-140°	1230.4	9.4
140°-150°	944.7	7.2
150°-160°	679.2	5.2
160°-170°	415.0	3.2
170°-180°	139.9	1.1
0°-30°	1105.6	8.4
0°-40°	1787.7	13.6
0°-60°	3055.5	23.3
0°-90°	3683.4	28.1
90°-120°	4459.5	34.0
90°-150°	8203.5	62.5
90°-180°	9438.0	71.9
0°-180°	13121.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1438	1438	1438	1438	1438	
5°	1443	1429	1434	1429	1429	137
15°	1387	1374	1380	1375	1372	391
25°	1278	1263	1269	1258	1256	588
35°	1104	1093	1096	1084	1082	690
45°	897	891	891	882	882	691
55°	665	663	656	653	652	591
65°	393	386	377	374	376	392
75°	179	179	176	175	174	194
85°	42	45	45	45	45	49
90°	4	11	22	24	24	9
95°	104	372	1121	573	397	109
105°	341	530	2037	3048	2861	358
115°	602	736	1697	3278	3708	592
125°	821	943	1523	2575	3030	733
135°	989	1104	1481	2077	2352	763
145°	1144	1233	1462	1776	1907	717
155°	1298	1345	1449	1594	1644	598
165°	1408	1424	1454	1512	1520	397
175°	1464	1462	1456	1477	1473	139
180°	1462	1462	1462	1462	1462	

TEST NUMBER: P563660

CATALOG NUMBER: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1437.8	1437.8	1437.8	1437.8	1437.8
2.5°	1446.9	1435.0	1437.8	1435.6	1429.7
5°	1442.8	1429.3	1434.0	1429.0	1429.0
7.5°	1433.0	1418.2	1422.9	1417.9	1417.6
10°	1423.9	1409.1	1413.8	1408.8	1407.5
12.5°	1410.8	1396.0	1401.7	1395.7	1395.4
15°	1387.4	1373.8	1379.8	1374.7	1372.3
17.5°	1360.9	1346.1	1353.4	1346.3	1345.3
20°	1340.8	1326.0	1333.2	1323.1	1323.1
22.5°	1316.6	1301.8	1310.0	1296.9	1296.9
25°	1277.8	1263.0	1268.9	1257.6	1256.3
27.5°	1231.6	1217.1	1223.3	1210.5	1210.2
30°	1198.4	1184.8	1192.1	1178.2	1176.9
32.5°	1162.1	1149.5	1154.8	1140.9	1139.6
35°	1103.9	1092.8	1096.3	1083.7	1082.4
37.5°	1042.6	1031.3	1035.3	1024.5	1024.0
40°	999.3	991.9	993.0	984.1	981.6
42.5°	958.9	950.6	951.6	942.8	942.3
45°	897.2	891.0	890.9	882.1	882.1
47.5°	831.7	827.0	825.6	818.3	818.1
50°	786.3	782.6	781.3	774.9	773.7
52.5°	738.9	737.2	732.9	727.6	727.3
55°	665.3	662.9	656.5	652.7	651.5
57.5°	585.4	580.5	573.4	567.8	568.8
60°	528.0	523.1	512.9	510.3	510.3
62.5°	472.5	466.6	456.4	452.9	454.9
65°	393.2	385.8	376.8	374.3	375.5
67.5°	321.1	314.4	304.7	304.7	303.7
70°	274.7	271.0	263.4	263.4	263.4
72.5°	233.4	231.6	226.1	226.0	225.1
75°	178.9	178.9	176.4	175.1	173.9
77.5°	134.1	134.6	133.3	132.0	129.8
80°	105.8	108.3	107.1	105.8	104.6
82.5°	79.6	82.1	81.9	79.6	79.4
85°	41.6	45.3	45.4	45.4	45.4
87.5°	11.8	17.2	20.6	21.0	22.0
90°	3.7	11.0	22.3	24.2	24.2
92.5°	45.4	160.5	317.3	152.8	106.2
95°	104.3	372.0	1121.1	573.3	396.7
97.5°	166.5	425.8	1758.4	1469.0	1107.7
100°	214.2	447.3	1961.0	2051.8	1702.2
102.5°	260.4	477.4	2028.1	2488.3	2201.3
105°	340.8	530.2	2037.4	3048.1	2860.6
107.5°	416.8	585.8	1950.6	3335.8	3384.2
110°	467.4	627.7	1871.6	3425.1	3601.8



TEST NUMBER: P563660

CATALOG NUMBER: SQ4-PP3-125U-050D-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	521.1	669.7	1795.7	3405.4	3695.6
115°	601.5	736.3	1696.6	3278.2	3707.9
117.5°	674.9	801.3	1619.9	3075.2	3553.7
120°	722.6	844.6	1581.1	2929.5	3421.1
122.5°	764.3	884.9	1552.8	2780.4	3270.6
125°	821.3	943.3	1523.4	2574.8	3030.0
127.5°	876.0	996.2	1504.8	2393.4	2799.8
130°	908.8	1029.0	1497.3	2289.5	2646.4
132.5°	941.6	1060.3	1489.9	2197.9	2525.7
135°	988.9	1103.6	1480.6	2077.2	2352.1
137.5°	1034.0	1144.0	1475.7	1974.7	2200.5
140°	1065.3	1170.9	1471.2	1911.7	2115.6
142.5°	1098.0	1196.4	1468.3	1852.8	2024.7
145°	1143.5	1232.7	1461.9	1775.9	1907.0
147.5°	1192.6	1270.2	1455.6	1711.2	1814.3
150°	1225.4	1292.8	1452.6	1670.6	1756.2
152.5°	1255.2	1313.9	1451.1	1637.5	1707.0
155°	1298.0	1345.4	1448.9	1593.5	1644.4
157.5°	1335.7	1372.5	1449.3	1562.5	1596.8
160°	1359.5	1390.5	1450.8	1544.5	1570.0
162.5°	1380.4	1405.5	1452.3	1529.4	1547.6
165°	1407.9	1424.3	1454.5	1512.4	1519.7
167.5°	1430.3	1439.7	1456.3	1499.2	1502.2
170°	1445.2	1448.8	1456.3	1491.7	1491.7
172.5°	1454.1	1454.8	1457.8	1484.3	1484.3
175°	1463.8	1462.0	1456.3	1476.8	1473.1
177.5°	1467.9	1465.0	1457.5	1469.3	1466.4
180°	1461.9	1461.9	1461.9	1461.9	1461.9

(END OF REPORT)