

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563766

Luminaire Tested: **SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563766  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6346.3 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563766  
CATALOG NUMBER: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P563766

CATALOG NUMBER: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	26	24	23	18
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	42	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5592	5592	5592
5°	5633	5599	5578
10°	5623	5584	5558
15°	5586	5555	5525
20°	5549	5518	5476
25°	5483	5445	5391
30°	5381	5353	5285
35°	5241	5205	5139
40°	5073	5042	4984
45°	4935	4899	4851
50°	4758	4727	4681
55°	4512	4451	4417
60°	4108	3989	3969
65°	3617	3467	3456
70°	3124	2994	2994
75°	2688	2652	2613
80°	2370	2396	2343
85°	1853	2022	2022



TEST NUMBER: P563766

CATALOG NUMBER: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.3	0.9
10°-20°	163.6	2.6
20°-30°	245.1	3.9
30°-40°	287.5	4.5
40°-50°	288.4	4.5
50°-60°	246.0	3.9
60°-70°	160.4	2.5
70°-80°	80.5	1.3
80°-90°	23.8	0.4
90°-100°	345.5	5.4
100°-110°	934.2	14.7
110°-120°	982.2	15.5
120°-130°	797.8	12.6
130°-140°	625.8	9.9
140°-150°	480.3	7.6
150°-160°	345.4	5.4
160°-170°	211.0	3.3
170°-180°	71.1	1.1
0°-30°	466.1	7.3
0°-40°	753.5	11.9
0°-60°	1288.0	20.3
0°-90°	1552.7	24.5
90°-120°	2262.0	35.6
90°-150°	4166.0	65.6
90°-180°	4794.0	75.5
0°-180°	6346.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	608	602	604	602	602	58
15°	585	579	582	580	578	165
25°	539	532	535	530	530	248
35°	465	461	462	457	456	291
45°	378	376	376	372	372	291
55°	280	279	277	275	275	249
65°	166	163	159	158	158	165
75°	75	75	74	74	73	82
85°	18	19	19	19	19	21
90°	2	5	10	11	10	4
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	



TEST NUMBER: P563766

CATALOG NUMBER: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	606.1	606.1	606.1	606.1	606.1
2.5°	609.9	604.9	606.1	605.2	602.7
5°	608.2	602.5	604.5	602.3	602.3
7.5°	604.0	597.8	599.8	597.7	597.6
10°	600.2	594.0	596.0	593.8	593.3
12.5°	594.7	588.5	590.9	588.3	588.2
15°	584.8	579.1	581.6	579.5	578.4
17.5°	573.7	567.4	570.5	567.5	567.1
20°	565.2	558.9	562.0	557.7	557.7
22.5°	555.0	548.7	552.2	546.7	546.7
25°	538.6	532.4	534.9	530.1	529.6
27.5°	519.2	513.0	515.7	510.2	510.1
30°	505.1	499.4	502.5	496.6	496.1
32.5°	489.8	484.5	486.8	480.9	480.4
35°	465.3	460.6	462.1	456.8	456.3
37.5°	439.5	434.7	436.4	431.8	431.6
40°	421.2	418.1	418.6	414.8	413.8
42.5°	404.2	400.7	401.1	397.4	397.2
45°	378.2	375.6	375.5	371.8	371.8
47.5°	350.6	348.6	348.0	344.9	344.8
50°	331.5	329.9	329.3	326.7	326.1
52.5°	311.5	310.8	308.9	306.7	306.6
55°	280.5	279.4	276.7	275.1	274.6
57.5°	246.8	244.7	241.7	239.4	239.8
60°	222.6	220.5	216.2	215.1	215.1
62.5°	199.2	196.7	192.4	190.9	191.8
65°	165.7	162.6	158.8	157.8	158.3
67.5°	135.3	132.5	128.4	128.4	128.0
70°	115.8	114.2	111.0	111.0	111.0
72.5°	98.4	97.6	95.3	95.3	94.9
75°	75.4	75.4	74.4	73.8	73.3
77.5°	56.5	56.7	56.2	55.6	54.7
80°	44.6	45.7	45.1	44.6	44.1
82.5°	33.6	34.6	34.5	33.6	33.5
85°	17.5	19.1	19.1	19.1	19.1
87.5°	5.0	7.3	8.9	9.0	9.3
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1



TEST NUMBER: P563766

CATALOG NUMBER: SQ4-PP3-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)