

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563732

Luminaire Tested: **SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P563732
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18637.7 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 152.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P563732
CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P563732

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16576	16576	16576
5°	16697	16596	16537
10°	16669	16551	16477
15°	16559	16469	16378
20°	16449	16356	16233
25°	16254	16141	15981
30°	15953	15869	15668
35°	15536	15429	15234
40°	15039	14944	14773
45°	14628	14525	14381
50°	14103	14013	13877
55°	13373	13196	13094
60°	12174	11825	11767
65°	10725	10278	10244
70°	9259	8878	8878
75°	7971	7858	7746
80°	7027	7112	6944
85°	5499	6002	6002



TEST NUMBER: P563732

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.8	1.8
10°-20°	970.2	5.2
20°-30°	1453.2	7.8
30°-40°	1704.5	9.1
40°-50°	1709.8	9.2
50°-60°	1458.6	7.8
60°-70°	951.3	5.1
70°-80°	477.3	2.6
80°-90°	135.5	0.7
90°-100°	683.9	3.7
100°-110°	1842.3	9.9
110°-120°	1933.4	10.4
120°-130°	1568.9	8.4
130°-140°	1230.4	6.6
140°-150°	944.7	5.1
150°-160°	679.2	3.6
160°-170°	415.0	2.2
170°-180°	139.9	0.8
0°-30°	2763.1	14.8
0°-40°	4467.6	24.0
0°-60°	7636.0	41.0
0°-90°	9200.1	49.4
90°-120°	4459.5	23.9
90°-150°	8203.5	44.0
90°-180°	9438.0	50.6
0°-180°	18637.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3593	3593	3593	3593	3593	
5°	3606	3572	3584	3571	3571	342
15°	3467	3433	3448	3436	3429	978
25°	3193	3156	3171	3143	3140	1468
35°	2759	2731	2740	2708	2705	1723
45°	2242	2227	2226	2204	2204	1726
55°	1663	1657	1641	1631	1628	1478
65°	982	964	942	935	938	981
75°	447	447	441	438	435	485
85°	104	113	113	113	113	122
90°	4	11	22	24	24	11
95°	104	372	1121	573	397	109
105°	341	530	2037	3048	2861	358
115°	602	736	1697	3278	3708	592
125°	821	943	1523	2575	3030	733
135°	989	1104	1481	2077	2352	763
145°	1144	1233	1462	1776	1907	717
155°	1298	1345	1449	1594	1644	598
165°	1408	1424	1454	1512	1520	397
175°	1464	1462	1456	1477	1473	139
180°	1462	1462	1462	1462	1462	

TEST NUMBER: P563732

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3593.2	3593.2	3593.2	3593.2	3593.2
2.5°	3615.9	3586.3	3593.2	3587.8	3573.0
5°	3605.8	3571.9	3583.8	3571.2	3571.2
7.5°	3581.2	3544.3	3556.0	3543.4	3542.8
10°	3558.6	3521.6	3533.4	3520.7	3517.6
12.5°	3525.8	3488.9	3503.1	3488.0	3487.4
15°	3467.2	3433.4	3448.3	3435.6	3429.4
17.5°	3401.1	3364.2	3382.2	3364.5	3362.1
20°	3350.7	3313.8	3331.8	3306.6	3306.6
22.5°	3290.3	3253.3	3273.9	3241.1	3241.1
25°	3193.3	3156.3	3171.2	3142.8	3139.7
27.5°	3078.0	3041.7	3057.2	3025.1	3024.5
30°	2994.9	2961.0	2979.1	2944.4	2941.3
32.5°	2904.2	2872.8	2885.9	2851.2	2848.1
35°	2758.7	2731.0	2739.8	2708.2	2705.1
37.5°	2605.6	2577.3	2587.4	2560.2	2559.0
40°	2497.3	2478.8	2481.5	2459.4	2453.2
42.5°	2396.5	2375.6	2378.3	2356.2	2354.9
45°	2242.2	2226.8	2226.5	2204.4	2204.4
47.5°	2078.5	2066.8	2063.3	2045.1	2044.4
50°	1965.1	1955.8	1952.5	1936.7	1933.6
52.5°	1846.7	1842.4	1831.6	1818.3	1817.7
55°	1662.8	1656.6	1640.7	1631.2	1628.1
57.5°	1463.1	1450.8	1432.9	1419.1	1421.5
60°	1319.5	1307.2	1281.7	1275.4	1275.4
62.5°	1180.9	1166.2	1140.6	1131.9	1136.9
65°	982.5	964.1	941.6	935.4	938.5
67.5°	802.4	785.8	761.5	761.4	759.0
70°	686.5	677.3	658.2	658.2	658.2
72.5°	583.2	578.9	565.0	564.9	562.4
75°	447.2	447.2	440.9	437.7	434.6
77.5°	335.1	336.3	333.2	329.9	324.4
80°	264.5	270.7	267.7	264.5	261.4
82.5°	199.0	205.2	204.7	199.0	198.4
85°	103.9	113.2	113.4	113.4	113.4
87.5°	28.5	39.8	44.8	45.2	47.7
90°	3.7	11.0	22.3	24.2	24.2
92.5°	45.4	160.5	317.3	152.8	106.2
95°	104.3	372.0	1121.1	573.3	396.7
97.5°	166.5	425.8	1758.4	1469.0	1107.7
100°	214.2	447.3	1961.0	2051.8	1702.2
102.5°	260.4	477.4	2028.1	2488.3	2201.3
105°	340.8	530.2	2037.4	3048.1	2860.6
107.5°	416.8	585.8	1950.6	3335.8	3384.2
110°	467.4	627.7	1871.6	3425.1	3601.8



TEST NUMBER: P563732

CATALOG NUMBER: SQ4-PP3-125U-125D-830-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	521.1	669.7	1795.7	3405.4	3695.6
115°	601.5	736.3	1696.6	3278.2	3707.9
117.5°	674.9	801.3	1619.9	3075.2	3553.7
120°	722.6	844.6	1581.1	2929.5	3421.1
122.5°	764.3	884.9	1552.8	2780.4	3270.6
125°	821.3	943.3	1523.4	2574.8	3030.0
127.5°	876.0	996.2	1504.8	2393.4	2799.8
130°	908.8	1029.0	1497.3	2289.5	2646.4
132.5°	941.6	1060.3	1489.9	2197.9	2525.7
135°	988.9	1103.6	1480.6	2077.2	2352.1
137.5°	1034.0	1144.0	1475.7	1974.7	2200.5
140°	1065.3	1170.9	1471.2	1911.7	2115.6
142.5°	1098.0	1196.4	1468.3	1852.8	2024.7
145°	1143.5	1232.7	1461.9	1775.9	1907.0
147.5°	1192.6	1270.2	1455.6	1711.2	1814.3
150°	1225.4	1292.8	1452.6	1670.6	1756.2
152.5°	1255.2	1313.9	1451.1	1637.5	1707.0
155°	1298.0	1345.4	1448.9	1593.5	1644.4
157.5°	1335.7	1372.5	1449.3	1562.5	1596.8
160°	1359.5	1390.5	1450.8	1544.5	1570.0
162.5°	1380.4	1405.5	1452.3	1529.4	1547.6
165°	1407.9	1424.3	1454.5	1512.4	1519.7
167.5°	1430.3	1439.7	1456.3	1499.2	1502.2
170°	1445.2	1448.8	1456.3	1491.7	1491.7
172.5°	1454.1	1454.8	1457.8	1484.3	1484.3
175°	1463.8	1462.0	1456.3	1476.8	1473.1
177.5°	1467.9	1465.0	1457.5	1469.3	1466.4
180°	1461.9	1461.9	1461.9	1461.9	1461.9

(END OF REPORT)