

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564150

Luminaire Tested: **SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564150
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1542.1 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564150
CATALOG NUMBER: SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564150

CATALOG NUMBER: SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5691	5691	5691
5°	5742	5698	5669
10°	5724	5684	5655
15°	5699	5663	5633
20°	5670	5634	5593
25°	5631	5593	5528
30°	5570	5530	5450
35°	5487	5439	5361
40°	5362	5304	5209
45°	5143	5053	4949
50°	4758	4645	4553
55°	4153	4060	3975
60°	3500	3471	3403
65°	3028	3039	3015
70°	2781	2795	2795
75°	2670	2670	2688
80°	2513	2540	2513
85°	2022	2255	2255



TEST NUMBER: P564150

CATALOG NUMBER: SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	3.8
10°-20°	166.9	10.8
20°-30°	251.7	16.3
30°-40°	299.9	19.5
40°-50°	295.7	19.2
50°-60°	226.0	14.7
60°-70°	139.9	9.1
70°-80°	79.4	5.2
80°-90°	24.2	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.0	30.9
0°-40°	776.9	50.4
0°-60°	1298.6	84.2
0°-90°	1542.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1542.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	617	617	617	617	617	
5°	620	613	615	613	612	59
15°	597	590	593	591	590	168
25°	553	546	549	544	543	255
35°	487	482	483	477	476	304
45°	394	389	387	380	379	302
55°	258	254	252	248	247	231
65°	139	138	139	138	138	140
75°	75	75	75	75	75	79
85°	19	20	21	21	21	23
90°	0	0	0	0	0	



TEST NUMBER: P564150

CATALOG NUMBER: SQ4-PR1-0U-050D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	616.8	616.8	616.8	616.8	616.8
2.5°	620.7	615.3	616.8	615.5	612.6
5°	620.0	613.3	615.2	613.1	612.1
7.5°	615.2	608.6	610.6	608.4	607.8
10°	611.0	604.8	606.7	604.6	603.6
12.5°	606.3	599.7	602.1	599.5	598.5
15°	596.6	590.4	592.9	590.8	589.7
17.5°	586.0	579.4	581.9	579.4	578.1
20°	577.5	571.3	573.8	570.1	569.6
22.5°	568.2	561.9	564.5	559.5	559.3
25°	553.1	546.3	549.4	543.5	543.0
27.5°	535.1	528.9	531.4	525.4	524.8
30°	522.8	516.6	519.1	512.7	511.6
32.5°	508.8	503.0	505.1	498.7	498.0
35°	487.2	481.5	482.9	476.6	476.0
37.5°	462.7	457.5	458.3	451.3	450.8
40°	445.2	440.0	440.4	433.0	432.5
42.5°	426.1	420.9	420.5	413.0	412.5
45°	394.2	389.0	387.3	380.4	379.3
47.5°	357.9	352.7	349.5	343.8	343.1
50°	331.5	326.3	323.6	318.7	317.2
52.5°	303.1	297.9	295.5	291.1	289.6
55°	258.2	254.1	252.4	248.1	247.1
57.5°	215.6	212.8	212.3	208.2	207.7
60°	189.7	188.1	188.1	184.4	184.4
62.5°	167.6	166.4	167.3	164.8	164.4
65°	138.7	137.6	139.2	138.1	138.1
67.5°	115.8	115.8	116.8	116.4	116.4
70°	103.1	103.1	103.6	103.6	103.6
72.5°	91.6	91.2	92.6	92.5	92.1
75°	74.9	74.9	74.9	75.4	75.4
77.5°	58.3	58.4	58.9	58.8	58.3
80°	47.3	47.8	47.8	47.3	47.3
82.5°	36.2	36.8	36.8	36.7	36.2
85°	19.1	20.2	21.3	21.3	21.3
87.5°	5.5	7.2	8.5	8.5	8.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)