

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564222

Luminaire Tested: **SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564222
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-4)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3853.7 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 43.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564222
CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564222

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	75	72
3	92	82	74	68	90	80	73	68	78	71	66	75	70	65	72	68	64	62
4	85	73	65	58	82	72	64	58	69	63	57	67	61	56	65	60	56	54
5	78	66	57	51	76	65	57	50	63	55	50	61	54	49	59	53	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	41
7	67	54	46	40	65	53	45	39	52	44	39	50	44	39	49	43	39	37
8	63	49	41	35	61	49	41	35	47	40	35	46	40	35	45	39	35	33
9	58	45	37	32	57	45	37	32	44	37	32	43	36	32	42	36	31	30
10	55	42	34	29	54	41	34	29	40	34	29	40	33	29	39	33	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14222	14222	14222
5°	14351	14240	14166
10°	14305	14206	14131
15°	14242	14154	14077
20°	14171	14079	13975
25°	14071	13976	13814
30°	13919	13820	13622
35°	13714	13593	13400
40°	13401	13257	13017
45°	12855	12629	12369
50°	11892	11606	11378
55°	10380	10145	9931
60°	8746	8673	8501
65°	7564	7595	7536
70°	6949	6984	6984
75°	6673	6673	6720
80°	6280	6349	6280
85°	5060	5621	5621



TEST NUMBER: P564222

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.8	3.8
10°-20°	417.1	10.8
20°-30°	629.1	16.3
30°-40°	749.6	19.5
40°-50°	739.0	19.2
50°-60°	564.8	14.7
60°-70°	349.5	9.1
70°-80°	198.5	5.2
80°-90°	60.4	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.9	30.9
0°-40°	1941.5	50.4
0°-60°	3245.3	84.2
0°-90°	3853.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3853.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1542	1542	1542	1542	1542	
5°	1550	1533	1538	1532	1530	147
15°	1491	1476	1482	1476	1474	421
25°	1382	1365	1373	1358	1357	636
35°	1218	1203	1207	1191	1190	760
45°	985	972	968	951	948	755
55°	645	635	631	620	617	578
65°	346	344	348	345	345	351
75°	187	187	187	188	188	198
85°	48	50	53	53	53	57
90°	0	0	0	0	0	



TEST NUMBER: P564222

CATALOG NUMBER: SQ4-PR1-0U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1541.5	1541.5	1541.5	1541.5	1541.5
2.5°	1551.1	1537.6	1541.5	1538.2	1530.9
5°	1549.5	1532.6	1537.6	1532.2	1529.6
7.5°	1537.6	1520.9	1525.9	1520.5	1519.0
10°	1526.9	1511.4	1516.3	1511.0	1508.4
12.5°	1515.3	1498.6	1504.6	1498.2	1495.6
15°	1491.1	1475.5	1481.8	1476.4	1473.8
17.5°	1464.5	1447.9	1454.2	1448.0	1444.6
20°	1443.3	1427.7	1434.0	1424.7	1423.4
22.5°	1419.9	1404.3	1410.6	1398.1	1397.9
25°	1382.2	1365.3	1372.9	1358.3	1357.0
27.5°	1337.3	1321.8	1328.0	1313.1	1311.6
30°	1306.5	1291.0	1297.2	1281.2	1278.6
32.5°	1271.5	1256.9	1262.2	1246.2	1244.7
35°	1217.6	1203.3	1206.9	1191.0	1189.7
37.5°	1156.2	1143.2	1145.3	1127.8	1126.5
40°	1112.7	1099.7	1100.7	1082.1	1080.8
42.5°	1064.9	1051.9	1050.8	1032.2	1030.9
45°	985.2	972.2	967.9	950.6	948.0
47.5°	894.4	881.4	873.4	859.3	857.5
50°	828.5	815.5	808.6	796.6	792.7
52.5°	757.4	744.4	738.5	727.5	723.6
55°	645.3	634.9	630.7	620.0	617.4
57.5°	538.8	531.8	530.6	520.2	519.2
60°	474.0	470.1	470.0	460.7	460.7
62.5°	418.8	415.9	418.0	411.9	410.8
65°	346.5	344.0	347.9	345.2	345.2
67.5°	289.5	289.5	291.8	290.8	290.8
70°	257.6	257.6	258.9	258.9	258.9
72.5°	228.9	227.9	231.3	231.3	230.2
75°	187.2	187.2	187.2	188.5	188.5
77.5°	145.8	146.0	147.1	146.8	145.8
80°	118.2	119.5	119.5	118.2	118.2
82.5°	90.6	91.9	91.9	91.6	90.6
85°	47.8	50.4	53.1	53.1	53.1
87.5°	13.8	18.0	21.2	21.2	20.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)