

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564390

Luminaire Tested: **SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564390  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6999.5 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 64.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564390  
CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564390

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	96	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36	31
3	80	71	64	59	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11145	11145	11145
5°	11245	11159	11101
10°	11209	11132	11074
15°	11160	11091	11031
20°	11105	11033	10951
25°	11026	10952	10825
30°	10907	10829	10675
35°	10746	10653	10501
40°	10501	10388	10200
45°	10073	9897	9693
50°	9320	9094	8916
55°	8134	7949	7782
60°	6853	6796	6661
65°	5929	5951	5905
70°	5446	5473	5473
75°	5229	5229	5265
80°	4920	4973	4920
85°	3970	4404	4404



TEST NUMBER: P564390

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.2	1.6
10°-20°	326.8	4.7
20°-30°	493.0	7.0
30°-40°	587.4	8.4
40°-50°	579.1	8.3
50°-60°	442.6	6.3
60°-70°	273.9	3.9
70°-80°	155.5	2.2
80°-90°	48.8	0.7
90°-100°	288.3	4.1
100°-110°	776.6	11.1
110°-120°	815.0	11.6
120°-130°	661.3	9.4
130°-140°	518.7	7.4
140°-150°	398.2	5.7
150°-160°	286.3	4.1
160°-170°	174.9	2.5
170°-180°	59.0	0.8
0°-30°	934.0	13.3
0°-40°	1521.4	21.7
0°-60°	2543.1	36.3
0°-90°	3021.3	43.2
90°-120°	1879.8	26.9
90°-150°	3458.0	49.4
90°-180°	3978.0	56.8
0°-180°	6999.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1208	1208	1208	1208	1208	
5°	1214	1201	1205	1201	1199	115
15°	1168	1156	1161	1157	1155	330
25°	1083	1070	1076	1064	1063	498
35°	954	943	946	933	932	595
45°	772	762	758	745	743	591
55°	506	498	494	486	484	453
65°	272	270	273	270	270	275
75°	147	147	147	148	148	155
85°	38	40	42	42	42	44
90°	2	5	9	10	10	5
95°	44	157	473	242	167	46
105°	144	224	859	1285	1206	151
115°	254	310	715	1382	1563	250
125°	346	398	642	1085	1277	309
135°	417	465	624	876	992	322
145°	482	520	616	749	804	302
155°	547	567	611	672	693	252
165°	594	600	613	638	641	167
175°	617	616	614	622	621	59
180°	616	616	616	616	616	



TEST NUMBER: P564390

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1208.0	1208.0	1208.0	1208.0	1208.0
2.5°	1215.5	1204.9	1208.0	1205.4	1199.7
5°	1214.2	1201.0	1204.9	1200.7	1198.6
7.5°	1204.9	1191.8	1195.7	1191.5	1190.3
10°	1196.5	1184.3	1188.2	1184.0	1182.0
12.5°	1187.4	1174.4	1179.1	1174.0	1172.0
15°	1168.4	1156.2	1161.2	1157.0	1154.9
17.5°	1147.6	1134.6	1139.5	1134.7	1132.0
20°	1131.0	1118.8	1123.7	1116.4	1115.4
22.5°	1112.7	1100.5	1105.4	1095.6	1095.4
25°	1083.1	1069.9	1075.8	1064.4	1063.4
27.5°	1048.0	1035.8	1040.7	1029.0	1027.8
30°	1023.8	1011.6	1016.5	1004.0	1002.0
32.5°	996.4	985.0	989.1	976.6	975.3
35°	954.1	942.9	945.8	933.3	932.3
37.5°	906.0	895.9	897.5	883.8	882.7
40°	871.9	861.7	862.5	848.0	846.9
42.5°	834.5	824.3	823.4	808.8	807.8
45°	772.0	761.9	758.5	744.9	742.9
47.5°	700.9	690.7	684.4	673.4	671.9
50°	649.3	639.1	633.6	624.2	621.2
52.5°	593.5	583.3	578.7	570.1	567.1
55°	505.7	497.5	494.2	485.9	483.8
57.5°	422.2	416.7	415.8	407.6	406.8
60°	371.4	368.4	368.3	361.0	361.0
62.5°	328.2	325.9	327.5	322.7	321.9
65°	271.6	269.5	272.6	270.5	270.5
67.5°	226.8	226.8	228.7	227.9	227.9
70°	201.9	201.9	202.9	202.9	202.9
72.5°	179.4	178.6	181.2	181.2	180.4
75°	146.7	146.7	146.7	147.7	147.7
77.5°	114.2	114.4	115.3	115.1	114.2
80°	92.6	93.6	93.6	92.6	92.6
82.5°	71.0	72.0	72.0	71.8	71.0
85°	37.5	39.5	41.6	41.6	41.6
87.5°	11.1	15.0	18.5	18.7	17.9
90°	1.6	4.6	9.4	10.2	10.2
92.5°	19.2	67.7	133.8	64.4	44.7
95°	44.0	156.8	472.6	241.7	167.2
97.5°	70.2	179.5	741.2	619.2	466.9
100°	90.3	188.5	826.6	864.9	717.5
102.5°	109.7	201.2	854.9	1048.9	927.9
105°	143.7	223.5	858.8	1284.9	1205.8
107.5°	175.7	246.9	822.2	1406.1	1426.6
110°	197.0	264.6	789.0	1443.8	1518.2



TEST NUMBER: P564390

CATALOG NUMBER: SQ4-PR1-125U-100D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	219.7	282.3	756.9	1435.5	1557.8
115°	253.6	310.4	715.2	1381.8	1563.0
117.5°	284.5	337.8	682.8	1296.3	1498.0
120°	304.6	356.0	666.5	1234.8	1442.1
122.5°	322.2	373.0	654.6	1172.0	1378.7
125°	346.2	397.6	642.2	1085.3	1277.2
127.5°	369.3	419.9	634.3	1008.9	1180.2
130°	383.1	433.8	631.2	965.1	1115.5
132.5°	396.9	447.0	628.0	926.5	1064.7
135°	416.9	465.2	624.1	875.6	991.5
137.5°	435.8	482.2	622.1	832.4	927.6
140°	449.0	493.6	620.2	805.8	891.8
142.5°	462.9	504.3	618.9	781.0	853.5
145°	482.0	519.6	616.2	748.6	803.9
147.5°	502.7	535.4	613.6	721.3	764.8
150°	516.5	544.9	612.3	704.2	740.3
152.5°	529.1	553.8	611.7	690.2	719.6
155°	547.2	567.1	610.8	671.7	693.2
157.5°	563.0	578.5	610.9	658.7	673.1
160°	573.1	586.1	611.5	651.0	661.8
162.5°	581.9	592.5	612.2	644.7	652.4
165°	593.5	600.4	613.1	637.5	640.6
167.5°	602.9	606.9	613.9	632.0	633.2
170°	609.2	610.7	613.9	628.8	628.8
172.5°	613.0	613.3	614.5	625.7	625.7
175°	617.0	616.3	613.9	622.5	621.0
177.5°	618.8	617.5	614.4	619.4	618.1
180°	616.2	616.2	616.2	616.2	616.2

(END OF REPORT)