

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564438

Luminaire Tested: **SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564438  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE RIPPLE CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6337.2 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 55.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564438  
CATALOG NUMBER: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564438

CATALOG NUMBER: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	28	28	21
2	84	77	71	66	75	69	64	60	53	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	28	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5691	5691	5691
5°	5742	5698	5669
10°	5724	5684	5655
15°	5699	5663	5633
20°	5670	5634	5593
25°	5631	5593	5528
30°	5570	5530	5450
35°	5487	5439	5361
40°	5362	5304	5209
45°	5143	5053	4949
50°	4758	4645	4553
55°	4153	4060	3975
60°	3500	3471	3403
65°	3028	3039	3015
70°	2781	2795	2795
75°	2670	2670	2688
80°	2513	2540	2513
85°	2022	2255	2255



TEST NUMBER: P564438

CATALOG NUMBER: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.3	0.9
10°-20°	166.9	2.6
20°-30°	251.7	4.0
30°-40°	299.9	4.7
40°-50°	295.7	4.7
50°-60°	226.0	3.6
60°-70°	139.9	2.2
70°-80°	79.4	1.3
80°-90°	25.7	0.4
90°-100°	345.5	5.5
100°-110°	934.2	14.7
110°-120°	982.2	15.5
120°-130°	797.8	12.6
130°-140°	625.8	9.9
140°-150°	480.3	7.6
150°-160°	345.4	5.5
160°-170°	211.0	3.3
170°-180°	71.1	1.1
0°-30°	477.0	7.5
0°-40°	776.9	12.3
0°-60°	1298.6	20.5
0°-90°	1543.6	24.4
90°-120°	2262.0	35.7
90°-150°	4166.0	65.7
90°-180°	4794.0	75.6
0°-180°	6337.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	617	617	617	617	617	
5°	620	613	615	613	612	59
15°	597	590	593	591	590	168
25°	553	546	549	544	543	255
35°	487	482	483	477	476	304
45°	394	389	387	380	379	302
55°	258	254	252	248	247	231
65°	139	138	139	138	138	140
75°	75	75	75	75	75	79
85°	19	20	21	21	21	22
90°	2	5	10	11	10	4
95°	54	188	575	297	177	56
105°	174	268	1036	1529	1466	183
115°	306	374	860	1664	1878	302
125°	419	480	775	1307	1536	373
135°	502	561	754	1056	1195	388
145°	583	627	744	904	972	365
155°	659	684	737	810	837	304
165°	717	724	740	769	773	202
175°	744	744	741	751	749	71
180°	744	744	744	744	744	

TEST NUMBER: P564438

CATALOG NUMBER: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	616.8	616.8	616.8	616.8	616.8
2.5°	620.7	615.3	616.8	615.5	612.6
5°	620.0	613.3	615.2	613.1	612.1
7.5°	615.2	608.6	610.6	608.4	607.8
10°	611.0	604.8	606.7	604.6	603.6
12.5°	606.3	599.7	602.1	599.5	598.5
15°	596.6	590.4	592.9	590.8	589.7
17.5°	586.0	579.4	581.9	579.4	578.1
20°	577.5	571.3	573.8	570.1	569.6
22.5°	568.2	561.9	564.5	559.5	559.3
25°	553.1	546.3	549.4	543.5	543.0
27.5°	535.1	528.9	531.4	525.4	524.8
30°	522.8	516.6	519.1	512.7	511.6
32.5°	508.8	503.0	505.1	498.7	498.0
35°	487.2	481.5	482.9	476.6	476.0
37.5°	462.7	457.5	458.3	451.3	450.8
40°	445.2	440.0	440.4	433.0	432.5
42.5°	426.1	420.9	420.5	413.0	412.5
45°	394.2	389.0	387.3	380.4	379.3
47.5°	357.9	352.7	349.5	343.8	343.1
50°	331.5	326.3	323.6	318.7	317.2
52.5°	303.1	297.9	295.5	291.1	289.6
55°	258.2	254.1	252.4	248.1	247.1
57.5°	215.6	212.8	212.3	208.2	207.7
60°	189.7	188.1	188.1	184.4	184.4
62.5°	167.6	166.4	167.3	164.8	164.4
65°	138.7	137.6	139.2	138.1	138.1
67.5°	115.8	115.8	116.8	116.4	116.4
70°	103.1	103.1	103.6	103.6	103.6
72.5°	91.6	91.2	92.6	92.5	92.1
75°	74.9	74.9	74.9	75.4	75.4
77.5°	58.3	58.4	58.9	58.8	58.3
80°	47.3	47.8	47.8	47.3	47.3
82.5°	36.2	36.8	36.8	36.7	36.2
85°	19.1	20.2	21.3	21.3	21.3
87.5°	5.8	8.1	10.6	10.7	10.2
90°	1.6	4.7	10.4	11.2	10.4
92.5°	22.7	82.8	163.4	70.9	51.4
95°	53.6	188.2	574.6	297.4	176.9
97.5°	86.1	215.9	895.7	741.3	544.4
100°	110.4	227.0	995.6	1038.3	839.5
102.5°	132.9	242.6	1030.8	1263.5	1114.8
105°	173.7	268.4	1036.4	1528.8	1466.2
107.5°	211.4	297.8	991.1	1694.3	1715.1
110°	240.9	319.1	950.8	1738.7	1827.1



TEST NUMBER: P564438

CATALOG NUMBER: SQ4-PR1-150U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	267.1	340.4	913.6	1729.8	1878.3
115°	305.7	373.8	859.5	1663.9	1878.3
117.5°	343.5	407.4	823.8	1563.3	1806.3
120°	366.5	429.1	802.7	1491.0	1739.1
122.5°	388.3	449.7	789.9	1413.6	1663.5
125°	418.6	479.6	774.7	1307.3	1535.8
127.5°	446.4	506.4	765.7	1220.6	1421.5
130°	461.8	523.6	761.9	1167.0	1348.5
132.5°	477.8	539.0	758.1	1118.6	1285.8
135°	501.8	561.3	753.9	1055.6	1194.9
137.5°	526.0	582.2	750.4	1004.4	1117.9
140°	542.6	595.0	749.1	971.5	1072.4
142.5°	558.6	607.9	746.5	941.7	1030.2
145°	583.4	627.3	743.5	903.5	972.4
147.5°	606.0	644.8	740.0	868.9	921.8
150°	622.6	657.1	738.7	850.1	892.4
152.5°	638.0	668.1	738.1	832.6	867.4
155°	658.7	684.5	737.1	810.5	837.1
157.5°	680.1	698.1	737.3	795.1	812.6
160°	692.3	707.1	737.9	785.4	797.9
162.5°	701.9	714.2	738.5	777.6	787.0
165°	717.1	724.1	740.3	769.2	773.1
167.5°	727.5	732.3	740.5	761.9	763.8
170°	733.9	736.2	741.1	758.7	758.7
172.5°	739.0	739.5	741.1	754.8	754.2
175°	744.3	743.5	741.1	750.7	749.1
177.5°	746.1	744.2	740.9	747.3	745.4
180°	743.5	743.5	743.5	743.5	743.5

(END OF REPORT)