

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564558

Luminaire Tested: **SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564558
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3030.6 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 29.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564558
CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564558

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	75
1	103	99	95	91	98	94	91	88	86	83	80	77	75	73	70	68	67	63
2	94	87	80	75	89	83	77	72	75	71	67	68	65	62	62	59	57	53
3	86	76	69	63	82	73	66	60	66	61	56	60	56	52	55	51	48	45
4	79	68	59	53	75	65	57	51	59	53	48	54	49	45	49	45	42	39
5	73	61	52	46	69	58	50	44	53	47	42	48	43	39	44	40	36	34
6	67	54	46	40	64	52	44	39	48	41	37	44	38	34	40	36	32	30
7	62	49	41	35	59	47	40	34	44	37	32	40	35	30	37	32	29	26
8	58	45	37	31	55	43	36	31	40	33	29	37	31	27	34	29	26	23
9	54	41	33	28	51	40	32	27	37	30	26	34	28	25	31	27	23	21
10	50	38	30	25	48	37	30	25	34	28	24	31	26	22	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8200	8200	8200
5°	8253	8188	8152
10°	8187	8122	8078
15°	8101	8011	7980
20°	8004	7880	7865
25°	7892	7748	7725
30°	7725	7609	7559
35°	7506	7400	7356
40°	7271	7159	7130
45°	6988	6897	6866
50°	6699	6643	6598
55°	6386	6386	6286
60°	5997	6111	5896
65°	5488	5761	5351
70°	4837	5303	4710
75°	4132	4745	4021
80°	3204	3995	3246
85°	2075	3070	2731



TEST NUMBER: P564558

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	2.8
10°-20°	236.3	7.8
20°-30°	350.5	11.6
30°-40°	410.1	13.5
40°-50°	408.3	13.5
50°-60°	352.6	11.6
60°-70°	253.8	8.4
70°-80°	133.1	4.4
80°-90°	33.6	1.1
90°-100°	57.8	1.9
100°-110°	151.9	5.0
110°-120°	157.6	5.2
120°-130°	126.4	4.2
130°-140°	99.2	3.3
140°-150°	76.1	2.5
150°-160°	54.8	1.8
160°-170°	33.5	1.1
170°-180°	11.3	0.4
0°-30°	670.5	22.1
0°-40°	1080.6	35.7
0°-60°	1841.4	60.8
0°-90°	2261.9	74.6
90°-120°	367.3	12.1
90°-150°	669.0	22.1
90°-180°	769.0	25.4
0°-180°	3030.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	889	889	889	889	889	
5°	891	881	884	882	880	84
15°	848	837	839	837	836	239
25°	775	762	761	756	759	356
35°	666	657	657	651	653	417
45°	536	531	529	527	526	413
55°	397	396	397	392	391	354
65°	251	259	264	254	245	249
75°	116	127	133	124	113	124
85°	20	26	29	27	26	26
90°	1	2	6	3	3	1
95°	8	30	100	51	35	8
105°	27	42	168	255	238	29
115°	49	59	135	268	306	48
125°	68	76	122	207	244	60
135°	81	89	119	167	189	62
145°	94	99	117	142	154	59
155°	106	109	117	129	132	49
165°	114	116	117	122	123	32
175°	119	119	118	119	119	11
180°	119	119	119	119	119	



TEST NUMBER: P564558

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	888.8	888.8	888.8	888.8	888.8
2.5°	893.8	886.4	888.8	886.8	882.5
5°	891.1	881.2	884.1	881.7	880.2
7.5°	882.1	872.9	875.0	872.5	871.6
10°	873.9	864.7	866.9	863.7	862.2
12.5°	864.5	854.7	856.8	853.7	852.8
15°	848.1	837.3	838.7	837.1	835.5
17.5°	829.0	818.1	818.3	815.8	815.5
20°	815.2	803.7	802.6	799.6	801.1
22.5°	800.1	788.0	787.0	782.7	784.8
25°	775.2	762.2	761.1	756.5	758.8
27.5°	746.4	733.6	733.6	727.1	729.5
30°	725.1	712.9	714.2	706.4	709.5
32.5°	702.6	691.5	692.2	684.5	687.5
35°	666.4	657.2	657.0	650.8	653.1
37.5°	629.4	621.3	620.0	616.4	617.1
40°	603.7	596.9	594.4	592.0	592.0
42.5°	576.8	570.5	568.0	566.3	565.7
45°	535.6	531.0	528.6	527.0	526.2
47.5°	494.9	490.6	488.5	487.4	486.6
50°	466.7	463.6	462.8	460.4	459.7
52.5°	438.5	436.7	435.9	432.9	432.1
55°	397.0	396.3	397.0	391.5	390.8
57.5°	353.8	355.0	357.6	350.1	348.3
60°	325.0	328.0	331.2	322.6	319.5
62.5°	295.5	300.4	304.9	295.0	290.7
65°	251.4	259.0	263.9	253.5	245.1
67.5°	208.8	218.3	224.1	212.9	203.4
70°	179.3	190.0	196.6	185.3	174.6
72.5°	153.6	165.6	170.9	160.3	149.6
75°	115.9	126.6	133.1	124.2	112.8
77.5°	82.2	92.3	97.7	90.0	80.5
80°	60.3	71.0	75.2	68.7	61.1
82.5°	42.8	51.6	54.5	50.6	45.4
85°	19.6	25.7	29.0	27.4	25.8
87.5°	5.2	9.7	13.1	12.5	13.1
90°	0.8	2.2	6.1	3.0	3.0
92.5°	3.2	15.4	34.1	15.1	9.7
95°	7.6	29.9	99.6	51.3	35.0
97.5°	13.2	32.8	149.0	118.5	87.3
100°	17.5	35.3	164.2	166.4	129.2
102.5°	21.1	37.8	168.5	207.3	175.4
105°	27.4	41.5	168.0	255.0	237.9
107.5°	33.8	46.8	158.4	279.8	284.0
110°	38.0	49.9	150.5	286.2	304.1

TEST NUMBER: P564558

CATALOG NUMBER: SQ4-PW1-025U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	42.3	53.6	143.2	282.2	309.5
115°	48.7	59.1	134.6	268.4	306.4
117.5°	54.9	64.4	128.6	249.4	291.5
120°	58.5	67.5	126.2	236.6	277.5
122.5°	62.2	71.1	124.4	223.8	264.1
125°	67.7	75.8	122.4	206.9	244.0
127.5°	72.1	80.4	120.7	193.2	224.6
130°	74.5	83.4	120.1	184.6	213.6
132.5°	76.9	85.8	119.5	177.3	203.3
135°	80.6	88.8	118.6	167.0	189.3
137.5°	84.4	92.4	118.4	159.3	177.6
140°	87.4	94.9	117.8	153.2	170.3
142.5°	89.9	96.7	117.8	148.9	163.6
145°	93.5	99.4	117.1	142.4	153.6
147.5°	97.2	102.9	117.1	137.0	146.3
150°	99.6	104.8	117.1	134.0	141.4
152.5°	102.0	106.0	117.1	131.5	137.1
155°	105.7	108.6	117.1	128.6	132.3
157.5°	108.4	111.2	117.1	125.9	128.6
160°	110.2	112.5	117.1	124.7	126.2
162.5°	112.0	113.7	117.1	123.5	125.0
165°	114.0	115.5	117.1	121.7	123.1
167.5°	115.9	116.6	117.8	120.9	121.5
170°	117.1	117.8	117.8	120.9	120.9
172.5°	117.7	117.8	117.8	120.2	119.7
175°	118.6	118.6	117.8	119.3	119.3
177.5°	118.6	118.6	118.0	119.2	118.6
180°	118.6	118.6	118.6	118.6	118.6

(END OF REPORT)