

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564606

Luminaire Tested: **SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564606
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4603.6 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 49.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564606
CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564606

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71
2	96	88	82	77	92	85	79	74	79	74	70	73	69	66	68	65	62	59
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50
4	81	69	61	54	77	67	59	53	62	56	51	58	53	48	54	50	46	43
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	49	44	40	38
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33
7	63	51	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29
8	59	46	38	32	57	45	37	32	42	35	31	40	34	29	37	32	28	26
9	55	42	34	29	53	41	34	29	39	32	28	36	31	27	34	29	26	24
10	52	39	31	26	50	38	31	26	36	29	25	34	28	24	32	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13904	13904	13904
5°	13994	13884	13822
10°	13882	13771	13696
15°	13735	13583	13532
20°	13571	13363	13336
25°	13382	13138	13098
30°	13098	12900	12816
35°	12726	12547	12473
40°	12329	12138	12090
45°	11850	11695	11643
50°	11359	11263	11187
55°	10829	10829	10658
60°	10167	10365	9996
65°	9304	9769	9073
70°	8203	8991	7987
75°	7005	8046	6816
80°	5430	6774	5504
85°	3515	5198	4637



TEST NUMBER: P564606

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.9	3.1
10°-20°	400.7	8.7
20°-30°	594.3	12.9
30°-40°	695.4	15.1
40°-50°	692.3	15.0
50°-60°	597.8	13.0
60°-70°	430.3	9.3
70°-80°	225.7	4.9
80°-90°	56.6	1.2
90°-100°	57.8	1.3
100°-110°	151.9	3.3
110°-120°	157.6	3.4
120°-130°	126.4	2.7
130°-140°	99.2	2.2
140°-150°	76.1	1.7
150°-160°	54.8	1.2
160°-170°	33.5	0.7
170°-180°	11.3	0.2
0°-30°	1136.9	24.7
0°-40°	1832.3	39.8
0°-60°	3122.4	67.8
0°-90°	3834.9	83.3
90°-120°	367.3	8.0
90°-150°	669.0	14.5
90°-180°	769.0	16.7
0°-180°	4603.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1507	1507	1507	1507	1507	
5°	1511	1494	1499	1495	1492	143
15°	1438	1420	1422	1419	1417	405
25°	1314	1292	1291	1283	1287	604
35°	1130	1114	1114	1104	1107	706
45°	908	900	896	894	892	701
55°	673	672	673	664	663	601
65°	426	439	448	430	416	422
75°	196	215	226	211	191	211
85°	33	44	49	46	44	44
90°	1	2	6	3	3	2
95°	8	30	100	51	35	8
105°	27	42	168	255	238	29
115°	49	59	135	268	306	48
125°	68	76	122	207	244	60
135°	81	89	119	167	189	62
145°	94	99	117	142	154	59
155°	106	109	117	129	132	49
165°	114	116	117	122	123	32
175°	119	119	118	119	119	11
180°	119	119	119	119	119	

TEST NUMBER: P564606

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1507.0	1507.0	1507.0	1507.0	1507.0
2.5°	1515.5	1503.1	1507.0	1503.7	1496.4
5°	1511.0	1494.1	1499.1	1495.0	1492.4
7.5°	1495.6	1480.0	1483.7	1479.4	1477.8
10°	1481.8	1466.2	1469.9	1464.5	1461.9
12.5°	1465.9	1449.3	1452.9	1447.5	1446.0
15°	1438.0	1419.8	1422.1	1419.3	1416.7
17.5°	1405.6	1387.2	1387.5	1383.3	1382.8
20°	1382.2	1362.7	1361.0	1355.7	1358.3
22.5°	1356.7	1336.2	1334.4	1327.1	1330.7
25°	1314.5	1292.4	1290.6	1282.7	1286.6
27.5°	1265.6	1243.8	1243.9	1232.8	1237.0
30°	1229.5	1208.8	1210.9	1197.8	1203.0
32.5°	1191.3	1172.6	1173.8	1160.6	1165.8
35°	1129.9	1114.4	1114.0	1103.5	1107.4
37.5°	1067.3	1053.5	1051.3	1045.3	1046.3
40°	1023.7	1012.0	1007.8	1003.8	1003.8
42.5°	978.0	967.4	963.2	960.2	959.2
45°	908.2	900.4	896.3	893.6	892.3
47.5°	839.2	831.9	828.3	826.4	825.1
50°	791.4	786.2	784.7	780.7	779.4
52.5°	743.6	740.4	739.0	734.0	732.7
55°	673.2	671.9	673.2	663.9	662.6
57.5°	599.9	602.0	606.3	593.7	590.6
60°	551.0	556.2	561.7	546.9	541.7
62.5°	501.1	509.4	517.0	500.1	492.9
65°	426.2	439.2	447.5	429.9	415.6
67.5°	354.0	370.1	380.0	361.1	345.0
70°	304.1	322.2	333.3	314.3	296.1
72.5°	260.5	280.8	289.7	271.8	253.6
75°	196.5	214.7	225.7	210.7	191.2
77.5°	139.4	156.6	165.7	152.6	136.5
80°	102.2	120.4	127.5	116.5	103.6
82.5°	72.5	87.6	92.4	85.8	77.0
85°	33.2	43.6	49.1	46.4	43.8
87.5°	8.6	16.2	21.4	20.8	21.9
90°	0.8	2.2	6.1	3.0	3.0
92.5°	3.2	15.4	34.1	15.1	9.7
95°	7.6	29.9	99.6	51.3	35.0
97.5°	13.2	32.8	149.0	118.5	87.3
100°	17.5	35.3	164.2	166.4	129.2
102.5°	21.1	37.8	168.5	207.3	175.4
105°	27.4	41.5	168.0	255.0	237.9
107.5°	33.8	46.8	158.4	279.8	284.0
110°	38.0	49.9	150.5	286.2	304.1

TEST NUMBER: P564606

CATALOG NUMBER: SQ4-PW1-025U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	42.3	53.6	143.2	282.2	309.5
115°	48.7	59.1	134.6	268.4	306.4
117.5°	54.9	64.4	128.6	249.4	291.5
120°	58.5	67.5	126.2	236.6	277.5
122.5°	62.2	71.1	124.4	223.8	264.1
125°	67.7	75.8	122.4	206.9	244.0
127.5°	72.1	80.4	120.7	193.2	224.6
130°	74.5	83.4	120.1	184.6	213.6
132.5°	76.9	85.8	119.5	177.3	203.3
135°	80.6	88.8	118.6	167.0	189.3
137.5°	84.4	92.4	118.4	159.3	177.6
140°	87.4	94.9	117.8	153.2	170.3
142.5°	89.9	96.7	117.8	148.9	163.6
145°	93.5	99.4	117.1	142.4	153.6
147.5°	97.2	102.9	117.1	137.0	146.3
150°	99.6	104.8	117.1	134.0	141.4
152.5°	102.0	106.0	117.1	131.5	137.1
155°	105.7	108.6	117.1	128.6	132.3
157.5°	108.4	111.2	117.1	125.9	128.6
160°	110.2	112.5	117.1	124.7	126.2
162.5°	112.0	113.7	117.1	123.5	125.0
165°	114.0	115.5	117.1	121.7	123.1
167.5°	115.9	116.6	117.8	120.9	121.5
170°	117.1	117.8	117.8	120.9	120.9
172.5°	117.7	117.8	117.8	120.2	119.7
175°	118.6	118.6	117.8	119.3	119.3
177.5°	118.6	118.6	118.0	119.2	118.6
180°	118.6	118.6	118.6	118.6	118.6

(END OF REPORT)