

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564630

Luminaire Tested: **SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P564630  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3120.3 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 28.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P564630  
CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P564630

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49
1	98	93	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	42
2	89	82	76	70	82	75	70	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	32	29	26
5	68	57	49	43	63	53	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	20
7	58	46	38	32	53	43	36	31	37	31	27	31	27	23	26	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	15
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5563	5563	5563
5°	5599	5555	5531
10°	5555	5510	5481
15°	5496	5435	5415
20°	5431	5347	5336
25°	5355	5257	5241
30°	5242	5162	5129
35°	5092	5021	4991
40°	4933	4857	4838
45°	4742	4679	4658
50°	4546	4507	4477
55°	4333	4333	4264
60°	4069	4146	4000
65°	3722	3908	3631
70°	3283	3599	3197
75°	2802	3219	2727
80°	2173	2710	2200
85°	1408	2085	1853



TEST NUMBER: P564630

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.8	1.8
10°-20°	160.3	5.1
20°-30°	237.8	7.6
30°-40°	278.3	8.9
40°-50°	277.0	8.9
50°-60°	239.2	7.7
60°-70°	172.2	5.5
70°-80°	90.3	2.9
80°-90°	23.3	0.7
90°-100°	116.5	3.7
100°-110°	316.6	10.1
110°-120°	325.5	10.4
120°-130°	260.2	8.3
130°-140°	204.5	6.6
140°-150°	156.8	5.0
150°-160°	112.8	3.6
160°-170°	69.0	2.2
170°-180°	23.2	0.7
0°-30°	454.9	14.6
0°-40°	733.2	23.5
0°-60°	1249.4	40.0
0°-90°	1535.2	49.2
90°-120°	758.6	24.3
90°-150°	1380.1	44.2
90°-180°	1585.0	50.8
0°-180°	3120.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	603	603	603	603	603	
5°	605	598	600	598	597	57
15°	575	568	569	568	567	162
25°	526	517	516	513	515	242
35°	452	446	446	442	443	283
45°	363	360	359	358	357	280
55°	269	269	269	266	265	240
65°	170	176	179	172	166	169
75°	79	86	90	84	76	84
85°	13	17	20	19	18	18
90°	1	3	6	7	7	2
95°	17	64	203	88	59	18
105°	56	88	348	530	499	60
115°	100	121	279	554	632	99
125°	137	156	252	425	501	122
135°	166	184	245	346	390	128
145°	191	205	242	294	316	120
155°	216	224	240	264	272	100
165°	234	237	241	251	252	66
175°	243	244	242	245	244	23
180°	243	243	243	243	243	

TEST NUMBER: P564630

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	603.0	603.0	603.0	603.0	603.0
2.5°	606.4	601.4	603.0	601.7	598.8
5°	604.6	597.9	599.8	598.2	597.2
7.5°	598.5	592.2	593.7	592.0	591.3
10°	592.9	586.7	588.1	586.0	585.0
12.5°	586.6	579.9	581.3	579.2	578.6
15°	575.4	568.1	569.0	567.9	566.9
17.5°	562.4	555.1	555.2	553.5	553.3
20°	553.1	545.3	544.6	542.5	543.5
22.5°	542.9	534.7	534.0	531.0	532.5
25°	526.0	517.2	516.4	513.3	514.8
27.5°	506.4	497.7	497.7	493.3	495.0
30°	492.0	483.7	484.5	479.3	481.4
32.5°	476.7	469.2	469.7	464.4	466.5
35°	452.1	445.9	445.8	441.5	443.1
37.5°	427.1	421.6	420.7	418.2	418.7
40°	409.6	405.0	403.3	401.7	401.7
42.5°	391.4	387.1	385.4	384.2	383.8
45°	363.4	360.3	358.6	357.6	357.0
47.5°	335.8	332.9	331.4	330.7	330.1
50°	316.7	314.6	314.0	312.4	311.9
52.5°	297.5	296.3	295.7	293.7	293.2
55°	269.4	268.8	269.4	265.6	265.1
57.5°	240.0	240.9	242.6	237.6	236.3
60°	220.5	222.6	224.7	218.8	216.8
62.5°	200.5	203.8	206.9	200.1	197.2
65°	170.5	175.7	179.0	172.0	166.3
67.5°	141.6	148.1	152.1	144.5	138.0
70°	121.7	128.9	133.4	125.8	118.5
72.5°	104.2	112.3	115.9	108.8	101.5
75°	78.6	85.9	90.3	84.3	76.5
77.5°	55.8	62.6	66.3	61.1	54.6
80°	40.9	48.2	51.0	46.6	41.4
82.5°	29.0	35.0	37.0	34.3	30.8
85°	13.3	17.4	19.7	18.6	17.5
87.5°	3.6	6.9	9.2	9.5	9.9
90°	0.8	3.1	5.5	7.0	7.0
92.5°	7.0	31.9	55.4	23.8	20.1
95°	17.2	63.7	203.0	88.3	59.3
97.5°	28.4	70.4	311.1	242.1	170.0
100°	35.9	74.8	344.2	349.0	281.8
102.5°	43.4	79.3	353.0	431.6	372.3
105°	56.2	87.5	348.1	530.1	498.8
107.5°	69.5	97.1	328.0	581.0	589.7
110°	78.8	104.0	313.0	591.0	628.4

TEST NUMBER: P564630

CATALOG NUMBER: SQ4-PW1-050U-050D-930-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	87.0	110.9	298.0	582.7	639.0
115°	99.9	121.3	278.7	554.4	631.5
117.5°	112.1	132.5	266.3	514.4	601.2
120°	120.2	140.1	260.7	487.5	573.7
122.5°	127.1	146.9	257.0	460.6	543.8
125°	137.4	156.5	252.1	424.8	501.1
127.5°	146.6	165.5	249.5	397.7	463.2
130°	152.2	170.5	248.2	380.7	439.5
132.5°	157.8	176.2	247.0	366.2	418.2
135°	165.5	183.8	245.1	346.0	390.3
137.5°	173.8	190.4	244.2	328.2	365.5
140°	178.8	194.8	243.5	316.9	350.5
142.5°	183.8	198.6	242.9	308.0	336.1
145°	191.2	205.0	242.0	294.0	316.1
147.5°	199.7	211.4	241.2	283.0	300.4
150°	205.3	215.2	241.2	276.6	290.4
152.5°	209.7	218.4	240.6	271.0	282.3
155°	216.2	223.9	240.4	264.0	271.6
157.5°	222.6	228.6	240.4	259.3	265.1
160°	226.4	231.7	240.4	256.1	260.7
162.5°	230.1	234.2	241.0	253.6	257.0
165°	234.2	237.2	241.2	251.4	252.1
167.5°	238.4	239.9	242.0	248.7	249.3
170°	239.6	241.2	242.0	247.4	247.4
172.5°	240.9	241.8	242.0	246.2	246.2
175°	242.8	243.5	242.0	245.1	244.3
177.5°	243.4	243.4	241.5	244.0	242.8
180°	242.8	242.8	242.8	242.8	242.8

(END OF REPORT)