

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519691

Luminaire Tested: **SQ4-075U-0D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519691
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-075U-0D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8477.4 lumens
Efficiency: N/A
Efficacy: 157.0 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 54
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519691
CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519691

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	3225	38296	10455
100°	3383	32511	26773
105°	3586	22108	31418
110°	3760	15062	30174
115°	3889	10859	24540
120°	3968	8600	18937
125°	3949	7259	14385
130°	3895	6359	11286
135°	3866	5720	9116
140°	3857	5246	7558
145°	3856	4865	6382
150°	3893	4582	5536
155°	3946	4369	4951
160°	3978	4214	4567
165°	4002	4117	4311
170°	4012	4047	4150
175°	4017	4000	4043



TEST NUMBER: P519691

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	613.7	7.2
100°-110°	1688.6	19.9
110°-120°	1742.9	20.6
120°-130°	1396.4	16.5
130°-140°	1096.8	12.9
140°-150°	840.5	9.9
150°-160°	604.3	7.1
160°-170°	369.5	4.4
170°-180°	124.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4045.3	47.7
90°-150°	7379.0	87.0
90°-180°	8477.0	100.0
0°-180°	8477.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	3	11	19	25	25	
95°	91	335	1085	464	296	102
105°	302	464	1861	2834	2644	318
115°	534	651	1492	2972	3372	527
125°	736	839	1354	2290	2683	657
135°	889	986	1315	1852	2096	686
145°	1027	1098	1296	1578	1700	644
155°	1163	1201	1288	1418	1459	534
165°	1257	1273	1293	1346	1354	354
175°	1301	1304	1296	1312	1310	124
180°	1301	1301	1301	1301	1301	



TEST NUMBER: P519691

CATALOG NUMBER: SQ4-075U-0D-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	2.8	10.9	19.4	24.9	24.9
92.5°	38.2	163.3	283.0	108.6	89.2
95°	91.4	335.0	1085.3	464.1	296.3
97.5°	149.0	371.5	1656.2	1276.1	900.4
100°	191.0	394.1	1835.7	1852.8	1511.7
102.5°	230.9	421.0	1882.2	2298.7	1985.7
105°	301.8	464.2	1860.6	2833.6	2644.1
107.5°	369.3	517.7	1754.8	3095.6	3151.9
110°	418.1	553.4	1675.1	3160.8	3355.7
112.5°	462.4	593.4	1595.3	3118.8	3415.5
115°	534.4	650.8	1492.3	2971.6	3372.3
117.5°	603.0	710.2	1427.0	2765.2	3218.4
120°	645.1	748.0	1398.2	2610.5	3078.8
122.5°	682.8	785.6	1378.3	2474.8	2919.3
125°	736.5	839.4	1353.9	2290.3	2682.9
127.5°	787.4	885.4	1337.8	2136.4	2480.8
130°	814.0	914.2	1329.0	2044.9	2358.9
132.5°	845.0	945.2	1322.3	1964.5	2248.2
135°	888.8	986.2	1315.1	1852.3	2095.9
137.5°	929.7	1020.2	1309.0	1761.6	1962.5
140°	960.7	1044.7	1306.8	1701.3	1882.7
142.5°	987.3	1064.7	1302.4	1647.6	1803.0
145°	1027.2	1097.6	1295.8	1578.2	1700.0
147.5°	1069.8	1130.5	1292.4	1516.7	1614.2
150°	1096.4	1150.6	1290.2	1483.0	1558.8
152.5°	1120.8	1170.6	1288.0	1453.9	1516.7
155°	1162.9	1200.8	1287.5	1418.5	1459.1
157.5°	1193.3	1224.2	1287.5	1389.4	1417.6
160°	1215.5	1239.8	1287.5	1373.8	1395.4
162.5°	1233.2	1253.2	1289.7	1360.4	1377.7
165°	1257.0	1273.2	1293.0	1345.8	1353.9
167.5°	1273.6	1286.1	1295.8	1333.5	1335.6
170°	1284.7	1292.8	1295.8	1329.0	1329.0
172.5°	1293.5	1297.3	1295.8	1322.3	1320.1
175°	1301.3	1304.0	1295.8	1312.3	1309.6
177.5°	1303.5	1303.5	1294.7	1307.8	1303.5
180°	1301.3	1301.3	1301.3	1301.3	1301.3

(END OF REPORT)