

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P564846

Luminaire Tested: **SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P564846
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE WAVES CONTINUOUS LENS.
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2261.3 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P564846
CATALOG NUMBER: SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P564846

CATALOG NUMBER: SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8200	8200	8200
5°	8253	8188	8152
10°	8187	8122	8078
15°	8101	8011	7980
20°	8004	7880	7865
25°	7892	7748	7725
30°	7725	7609	7559
35°	7506	7400	7356
40°	7271	7159	7130
45°	6988	6897	6866
50°	6699	6643	6598
55°	6386	6386	6286
60°	5997	6111	5896
65°	5488	5761	5351
70°	4837	5303	4710
75°	4132	4745	4021
80°	3204	3995	3246
85°	2075	3070	2731



TEST NUMBER: P564846

CATALOG NUMBER: SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	3.7
10°-20°	236.3	10.4
20°-30°	350.5	15.5
30°-40°	410.1	18.1
40°-50°	408.3	18.1
50°-60°	352.6	15.6
60°-70°	253.8	11.2
70°-80°	133.1	5.9
80°-90°	33.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.5	29.7
0°-40°	1080.6	47.8
0°-60°	1841.4	81.4
0°-90°	2261.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2261.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	889	889	889	889	889	
5°	891	881	884	882	880	84
15°	848	837	839	837	836	239
25°	775	762	761	756	759	356
35°	666	657	657	651	653	417
45°	536	531	529	527	526	413
55°	397	396	397	392	391	354
65°	251	259	264	254	245	249
75°	116	127	133	124	113	124
85°	20	26	29	27	26	27
90°	0	0	0	0	0	



TEST NUMBER: P564846

CATALOG NUMBER: SQ4-PW1-0U-075D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	888.8	888.8	888.8	888.8	888.8
2.5°	893.8	886.4	888.8	886.8	882.5
5°	891.1	881.2	884.1	881.7	880.2
7.5°	882.1	872.9	875.0	872.5	871.6
10°	873.9	864.7	866.9	863.7	862.2
12.5°	864.5	854.7	856.8	853.7	852.8
15°	848.1	837.3	838.7	837.1	835.5
17.5°	829.0	818.1	818.3	815.8	815.5
20°	815.2	803.7	802.6	799.6	801.1
22.5°	800.1	788.0	787.0	782.7	784.8
25°	775.2	762.2	761.1	756.5	758.8
27.5°	746.4	733.6	733.6	727.1	729.5
30°	725.1	712.9	714.2	706.4	709.5
32.5°	702.6	691.5	692.2	684.5	687.5
35°	666.4	657.2	657.0	650.8	653.1
37.5°	629.4	621.3	620.0	616.4	617.1
40°	603.7	596.9	594.4	592.0	592.0
42.5°	576.8	570.5	568.0	566.3	565.7
45°	535.6	531.0	528.6	527.0	526.2
47.5°	494.9	490.6	488.5	487.4	486.6
50°	466.7	463.6	462.8	460.4	459.7
52.5°	438.5	436.7	435.9	432.9	432.1
55°	397.0	396.3	397.0	391.5	390.8
57.5°	353.8	355.0	357.6	350.1	348.3
60°	325.0	328.0	331.2	322.6	319.5
62.5°	295.5	300.4	304.9	295.0	290.7
65°	251.4	259.0	263.9	253.5	245.1
67.5°	208.8	218.3	224.1	212.9	203.4
70°	179.3	190.0	196.6	185.3	174.6
72.5°	153.6	165.6	170.9	160.3	149.6
75°	115.9	126.6	133.1	124.2	112.8
77.5°	82.2	92.3	97.7	90.0	80.5
80°	60.3	71.0	75.2	68.7	61.1
82.5°	42.8	51.6	54.5	50.6	45.4
85°	19.6	25.7	29.0	27.4	25.8
87.5°	5.0	9.3	11.9	11.9	12.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)