

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519763

Luminaire Tested: **SQ4-150U-0D-830-1D-UNV-STD-W-12**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519763
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-150U-0D-830-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17057.9 lumens
Efficiency: N/A
Efficacy: 147.7 lumens/watt
N/A
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')
CIE Type: Indirect

Input Watts (W): 115.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519763
CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P519763

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20								20				20				20				20
RC	80								50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10				0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
95°	6733	72153	22209
100°	6960	62745	52910
105°	7343	43822	61995
110°	7708	30422	58463
115°	7917	22258	48640
120°	8022	17570	38064
125°	7986	14781	29303
130°	7862	12972	22959
135°	7766	11668	18493
140°	7752	10701	15321
145°	7794	9933	12991
150°	7868	9335	11276
155°	7953	8900	10108
160°	8062	8594	9293
165°	8124	8387	8759
170°	8155	8236	8431
175°	8177	8141	8229



TEST NUMBER: P519763

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	1229.6	7.2
100°-110°	3324.5	19.5
110°-120°	3495.2	20.5
120°-130°	2839.1	16.6
130°-140°	2227.0	13.1
140°-150°	1709.2	10.0
150°-160°	1229.3	7.2
160°-170°	750.9	4.4
170°-180°	253.2	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	8049.2	47.2
90°-150°	14824.5	86.9
90°-180°	17058.0	100.0
0°-180°	17057.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
90°	6	17	37	40	37	
95°	191	670	2045	1058	629	212
105°	618	955	3688	5440	5217	651
115°	1088	1330	3059	5921	6684	1074
125°	1490	1707	2757	4652	5465	1328
135°	1786	1997	2683	3756	4252	1380
145°	2076	2232	2646	3215	3460	1299
155°	2344	2436	2623	2884	2979	1081
165°	2552	2577	2634	2737	2751	719
175°	2649	2646	2637	2671	2666	251
180°	2646	2646	2646	2646	2646	



TEST NUMBER: P519763

CATALOG NUMBER: SQ4-150U-OD-830-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
90°	5.7	16.8	37.0	39.8	37.0
92.5°	80.9	294.7	581.5	252.5	182.8
95°	190.8	669.8	2044.8	1058.2	629.4
97.5°	306.4	768.1	3187.4	2637.8	1937.2
100°	393.0	807.9	3542.8	3694.8	2987.5
102.5°	472.8	863.2	3668.1	4496.2	3967.1
105°	618.0	954.9	3688.0	5440.1	5217.4
107.5°	752.4	1059.8	3526.9	6029.0	6103.1
110°	857.2	1135.7	3383.3	6187.1	6501.8
112.5°	950.6	1211.3	3251.2	6155.5	6684.1
115°	1087.9	1330.2	3058.7	5921.1	6684.1
117.5°	1222.3	1449.6	2931.6	5562.8	6427.7
120°	1304.3	1527.1	2856.5	5305.8	6188.5
122.5°	1381.8	1600.1	2810.9	5030.3	5919.7
125°	1489.5	1706.7	2756.8	4652.0	5465.1
127.5°	1588.6	1801.9	2724.9	4343.4	5058.5
130°	1643.2	1863.2	2711.2	4152.7	4798.7
132.5°	1700.2	1918.0	2697.5	3980.7	4575.5
135°	1785.6	1997.3	2682.7	3756.3	4251.9
137.5°	1871.6	2071.6	2670.2	3574.2	3978.0
140°	1930.9	2117.5	2665.6	3457.0	3816.2
142.5°	1987.8	2163.3	2656.5	3351.2	3665.8
145°	2076.1	2232.1	2645.7	3215.2	3460.2
147.5°	2156.4	2294.6	2633.2	3092.0	3280.2
150°	2215.7	2338.2	2628.6	3025.1	3175.4
152.5°	2270.4	2377.3	2626.3	2962.9	3086.6
155°	2343.8	2435.7	2622.9	2884.2	2978.9
157.5°	2420.2	2484.2	2623.5	2829.4	2891.8
160°	2463.4	2516.4	2625.8	2794.8	2839.4
162.5°	2497.6	2541.6	2628.1	2767.2	2800.6
165°	2551.7	2576.8	2634.3	2737.2	2751.1
167.5°	2588.8	2606.0	2634.9	2711.4	2718.0
170°	2611.5	2619.9	2637.2	2699.8	2699.8
172.5°	2629.8	2631.4	2637.2	2686.1	2683.9
175°	2648.6	2645.8	2637.2	2671.2	2665.6
177.5°	2654.8	2648.1	2636.6	2659.2	2652.5
180°	2645.7	2645.7	2645.7	2645.7	2645.7

(END OF REPORT)