

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P519248

Luminaire Tested: **SQ4-WB-075U-125D-930-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

Test Information

Test Method: LM-79-2019
Report Number: P519248
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-22, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 4/29/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5649.8 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P519248
CATALOG NUMBER: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P519248

CATALOG NUMBER: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58				58
1	101	97	94	90	94	91	88	85	79	77	75	68	66	65	58	57	56	51				51
2	93	86	81	76	87	81	76	72	71	67	64	61	59	57	53	51	49	45				45
3	86	77	70	65	80	72	67	62	64	59	56	56	52	50	48	46	44	40				40
4	79	69	62	57	74	65	59	54	58	53	49	51	47	44	44	41	39	36				36
5	73	63	55	50	68	59	52	47	52	47	43	46	42	39	40	37	35	32				32
6	68	57	49	44	64	54	47	42	48	42	38	42	38	35	37	34	31	29				29
7	63	52	44	39	59	49	42	38	44	39	35	39	35	32	34	31	29	26				26
8	59	48	40	35	55	45	39	34	40	35	31	36	32	29	32	29	26	24				24
9	55	44	37	32	52	42	35	31	37	32	29	34	29	26	30	26	24	22				22
10	52	41	34	29	49	39	32	28	35	30	26	31	27	24	28	25	22	20				20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20682	20682	20682
5°	20424	20351	20470
10°	19296	19472	19923
15°	17814	18226	19044
20°	16177	16784	17896
25°	14510	15301	16672
30°	12973	13822	15404
35°	11344	12164	13903
40°	9548	10307	12037
45°	7880	8561	10049
50°	6580	7172	8372
55°	5585	6154	6914
60°	4774	5336	5517
65°	3801	4488	3565
70°	3369	3501	2177
75°	3119	2841	1333
80°	2874	2614	1148
85°	2604	2392	942



TEST NUMBER: P519248

CATALOG NUMBER: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.6	3.6
10°-20°	534.8	9.5
20°-30°	692.7	12.3
30°-40°	678.4	12.0
40°-50°	519.3	9.2
50°-60°	346.0	6.1
60°-70°	188.8	3.3
70°-80°	78.7	1.4
80°-90°	23.2	0.4
90°-100°	172.5	3.1
100°-110°	474.5	8.4
110°-120°	489.8	8.7
120°-130°	392.4	6.9
130°-140°	308.2	5.5
140°-150°	236.2	4.2
150°-160°	169.8	3.0
160°-170°	103.8	1.8
170°-180°	35.0	0.6
0°-30°	1433.2	25.4
0°-40°	2111.5	37.4
0°-60°	2976.8	52.7
0°-90°	3267.5	57.8
90°-120°	1136.8	20.1
90°-150°	2073.6	36.7
90°-180°	2382.0	42.2
0°-180°	5649.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2242	2242	2242	2242	2242	
5°	2205	2183	2197	2202	2210	205
15°	1865	1858	1908	1960	1994	521
25°	1425	1429	1503	1568	1638	655
35°	1007	1012	1080	1153	1234	626
45°	604	616	656	706	770	471
55°	347	362	383	397	430	315
65°	174	188	206	180	163	181
75°	88	88	80	55	37	93
85°	25	25	23	15	9	27
90°	1	3	5	7	7	3
95°	26	94	305	130	83	27
105°	85	130	523	796	743	89
115°	150	183	419	835	948	148
125°	207	236	380	644	754	185
135°	250	277	370	520	589	193
145°	289	308	364	444	478	181
155°	327	337	362	399	410	150
165°	353	358	363	378	380	100
175°	366	366	364	369	368	35
180°	366	366	366	366	366	

TEST NUMBER: P519248

CATALOG NUMBER: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2241.7	2241.7	2241.7	2241.7	2241.7
2.5°	2247.2	2227.2	2232.2	2232.1	2225.9
5°	2205.3	2183.2	2197.4	2202.5	2210.2
7.5°	2123.4	2106.7	2132.7	2151.9	2167.5
10°	2059.7	2045.3	2078.4	2106.4	2126.6
12.5°	1985.7	1973.6	2014.7	2052.2	2078.6
15°	1865.0	1858.2	1908.2	1960.1	1993.8
17.5°	1735.7	1732.4	1789.8	1850.4	1893.5
20°	1647.6	1646.6	1709.5	1772.6	1822.7
22.5°	1558.7	1560.8	1626.9	1692.5	1749.5
25°	1425.3	1429.1	1503.0	1568.5	1637.7
27.5°	1301.9	1303.7	1380.0	1449.2	1523.0
30°	1217.7	1222.5	1297.4	1369.0	1445.9
32.5°	1133.5	1139.1	1212.4	1286.4	1364.9
35°	1007.2	1012.0	1080.0	1152.7	1234.4
37.5°	877.0	883.5	943.9	1012.6	1093.0
40°	792.8	802.4	855.8	920.5	999.4
42.5°	711.8	723.7	773.1	834.6	905.7
45°	603.9	615.5	656.1	705.7	770.2
47.5°	511.1	524.4	555.6	598.3	653.3
50°	458.4	470.9	499.7	531.4	583.3
52.5°	411.9	424.4	450.1	474.5	518.8
55°	347.2	361.6	382.6	397.1	429.8
57.5°	294.1	308.0	324.6	331.1	351.0
60°	258.7	274.1	289.2	288.4	299.0
62.5°	226.4	239.5	254.6	244.1	244.7
65°	174.1	188.5	205.6	179.6	163.3
67.5°	140.7	143.7	161.3	125.3	105.8
70°	124.9	124.9	129.8	97.0	80.7
72.5°	110.0	110.0	105.4	78.9	61.8
75°	87.5	87.5	79.7	54.7	37.4
77.5°	67.5	66.7	61.0	40.8	27.1
80°	54.1	54.1	49.2	32.2	21.6
82.5°	42.3	42.3	38.2	25.2	16.1
85°	24.6	24.6	22.6	14.6	8.9
87.5°	8.8	9.3	9.0	6.1	5.3
90°	0.8	3.1	5.4	7.0	7.0
92.5°	10.7	45.9	79.5	30.5	25.1
95°	25.7	94.1	305.0	130.4	83.3
97.5°	41.9	104.4	465.4	358.6	253.0
100°	53.7	110.7	515.9	520.7	424.8
102.5°	64.9	118.3	528.9	646.0	558.0
105°	84.8	130.5	522.9	796.3	743.0
107.5°	103.8	145.5	493.1	869.9	885.7
110°	117.5	155.5	470.7	888.2	943.0

TEST NUMBER: P519248

CATALOG NUMBER: SQ4-WB-075U-125D-930-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	129.9	166.8	448.3	876.4	959.8
115°	150.2	182.9	419.4	835.1	947.7
117.5°	169.5	199.6	401.0	777.1	904.4
120°	181.3	210.2	392.9	733.6	865.2
122.5°	191.9	220.8	387.3	695.5	820.4
125°	207.0	235.9	380.5	643.6	753.9
127.5°	221.3	248.8	376.0	600.4	697.1
130°	228.8	256.9	373.5	574.7	662.9
132.5°	237.5	265.6	371.6	552.1	631.8
135°	249.8	277.1	369.6	520.5	589.0
137.5°	261.3	286.7	367.9	495.0	551.5
140°	270.0	293.6	367.2	478.1	529.1
142.5°	277.5	299.2	366.0	463.0	506.7
145°	288.7	308.4	364.1	443.5	477.7
147.5°	300.6	317.7	363.2	426.2	453.6
150°	308.1	323.3	362.6	416.7	438.0
152.5°	315.0	329.0	362.0	408.6	426.2
155°	326.8	337.4	361.8	398.6	410.0
157.5°	335.3	344.0	361.8	390.5	398.4
160°	341.6	348.4	361.8	386.1	392.1
162.5°	346.5	352.2	362.4	382.3	387.2
165°	353.2	357.8	363.4	378.2	380.5
167.5°	357.9	361.4	364.1	374.7	375.3
170°	361.0	363.3	364.1	373.5	373.5
172.5°	363.5	364.6	364.1	371.6	371.0
175°	365.7	366.4	364.1	368.8	368.0
177.5°	366.3	366.3	363.8	367.5	366.3
180°	365.7	365.7	365.7	365.7	365.7

(END OF REPORT)